

# Surface Mount Fuse 2410



Fast Blow with Holder


## Features

- Ceramic construction SMD fuses
- Silver end caps, copper plated
- 2410 foot print
- Fast blow and slow blow options
- Supplied taped on reel
- Fuse and holder option
- UL Approved (UL248-14)

## Specifications

|                     |  |
|---------------------|--|
| Voltage Rating      | : Fast Blow - 250V AC/125V DC<br>250mA - 15A<br>Slow Blow - 250V AC/125V DC<br>375mA - 12A |
| Breaking Capacity   | : 50A or 10In @ 125V DC<br>50A or 10In @ 125V AC   |
| Soldering Parameter | : Wave Soldering - 260°C ≤ 10 seconds<br>Hand Soldering - 300°C ≤ 2 seconds                |

## Diagram



Dimensions : Millimetres

## Part Number Table

| Description                      | I <sup>2</sup> T | Part Number      |
|----------------------------------|------------------|------------------|
| SMD Fuse, 2410, Fast Blow, 1A    | 0.9              | MCCFB2410TFF/1   |
| SMD Fuse, 2410, Fast Blow, 1.5A  | 0.8              | MCCFB2410TFF/1.5 |
| SMD Fuse, 2410, Fast Blow, 10A   | 35               | MCCFB2410TFF/10  |
| SMD Fuse, 2410, Fast Blow, 12A   | 40               | MCCFB2410TFF/12  |
| SMD Fuse, 2410, Fast Blow, 15A   | 55               | MCCFB2410TFF/15  |
| SMD Fuse, 2410, Fast Blow, 2A    | 0.8              | MCCFB2410TFF/2   |
| SMD Fuse, 2410, Fast Blow, 2.5A  | 1.95             | MCCFB2410TFF/2.5 |
| SMD Fuse, 2410, Fast Blow, 250mA | 0.042            | MCCFB2410TFF/250 |
| SMD Fuse, 2410, Fast Blow, 3A    | 1.95             | MCCFB2410TFF/3   |
| SMD Fuse, 2410, Fast Blow, 315mA | 0.042            | MCCFB2410TFF/315 |

www.element14.com  
www.farnell.com  
www.newark.com



# Surface Mount Fuse 2410



| Description                                  | I <sup>2</sup> T | Part Number        |
|--|------------------|--------------------|
| SMD Fuse, 2410, Fast Blow, 4A                | 4                | MCCFB2410TFF/4     |
| SMD Fuse, 2410, Fast Blow, 5A                | 7.5              | MCCFB2410TFF/5     |
| SMD Fuse, 2410, Fast Blow, 500mA             | 0.045            | MCCFB2410TFF/500   |
| SMD Fuse, 2410, Fast Blow, 6.3A              | 13               | MCCFB2410TFF/6.3   |
| SMD Fuse, 2410, Fast Blow, 7A                | 16               | MCCFB2410TFF/7     |
| SMD Fuse, 2410, Fast Blow, 750mA             | 0.9              | MCCFB2410TFF/750   |
| SMD Fuse, 2410, Fast Blow, 8A                | 20               | MCCFB2410TFF/8     |
| SMD Fuse, 2410, Fast Blow, 800mA             | 0.9              | MCCFB2410TFF/800   |
| SMD Fuse with Holder, 2410, Fast Blow, 1A    | 0.9              | MCCFB2410TFF/C/1   |
| SMD Fuse with Holder, 2410, Fast Blow, 1.5A  | 0.9              | MCCFB2410TFF/C/1.5 |
| SMD Fuse with Holder, 2410, Fast Blow, 10A   | 35               | MCCFB2410TFF/C/10  |
| SMD Fuse with Holder, 2410, Fast Blow, 2.5A  | 1.95             | MCCFB2410TFF/C/2.5 |
| SMD Fuse with Holder, 2410, Fast Blow, 3A    | 1.95             | MCCFB2410TFF/C/3   |
| SMD Fuse with Holder, 2410, Fast Blow, 3.5A  | 2.5              | MCCFB2410TFF/C/3.5 |
| SMD Fuse with Holder, 2410, Fast Blow, 375mA | 0.042            | MCCFB2410TFF/C/375 |
| SMD Fuse with Holder, 2410, Fast Blow, 4A    | 4                | MCCFB2410TFF/C/4   |
| SMD Fuse with Holder, 2410, Fast Blow, 5A    | 7.5              | MCCFB2410TFF/C/5   |
| SMD Fuse with Holder, 2410, Fast Blow, 500mA | 0.045            | MCCFB2410TFF/C/500 |
| SMD Fuse with Holder, 2410, Fast Blow, 6.3A  | 13               | MCCFB2410TFF/C/6.3 |
| SMD Fuse with Holder, 2410, Fast Blow, 7A    | 16               | MCCFB2410TFF/C/7   |
| SMD Fuse with Holder, 2410, Fast Blow, 8A    | 20               | MCCFB2410TFF/C/8   |
| SMD Fuse, 2410, Slow Blow, 1A                | 0.87             | MCCFB2410TTT/1     |
| SMD Fuse, 2410, Slow Blow, 1.6A              | 1.69             | MCCFB2410TTT/1.6   |
| SMD Fuse, 2410, Slow Blow, 12A               | 13               | MCCFB2410TTT/12    |
| SMD Fuse, 2410, Slow Blow, 2A                | 3.48             | MCCFB2410TTT/2     |
| SMD Fuse, 2410, Slow Blow, 2.5A              | 2.06             | MCCFB2410TTT/2.5   |
| SMD Fuse, 2410, Slow Blow, 3A                | 2.16             | MCCFB2410TTT/3     |
| SMD Fuse, 2410, Slow Blow, 3.5A              | 2.9              | MCCFB2410TTT/3.5   |
| SMD Fuse, 2410, Slow Blow, 375mA             | 0.6              | MCCFB2410TTT/375   |
| SMD Fuse, 2410, Slow Blow, 4A                | 3.84             | MCCFB2410TTT/4     |
| SMD Fuse, 2410, Slow Blow, 5A                | 7.5              | MCCFB2410TTT/5     |
| SMD Fuse, 2410, Slow Blow, 500mA             | 0.055            | MCCFB2410TTT/500   |
| SMD Fuse, 2410, Slow Blow, 7A                | 12.74            | MCCFB2410TTT/7     |
| SMD Fuse, 2410, Slow Blow, 8A                | 13               | MCCFB2410TTT/8     |
| SMD Fuse, 2410, Slow Blow, 800mA             | 0.512            | MCCFB2410TTT/800   |
| SMD Fuse with Holder, 2410, Slow Blow, 1A    | 0.87             | MCCFB2410TTT/C/1   |
| SMD Fuse with Holder, 2410, Slow Blow, 1.5A  | 1.69             | MCCFB2410TTT/C/1.5 |

# Surface Mount Fuse 2410



| Description                                  | I <sup>2</sup> T | Part Number        |
|--|------------------|--------------------|
| SMD Fuse with Holder, 2410, Slow Blow, 2A    | 3.48             | MCCFB2410TTT/C/2   |
| SMD Fuse with Holder, 2410, Slow Blow, 2.5A  | 2.06             | MCCFB2410TTT/C/2.5 |
| SMD Fuse with Holder, 2410, Slow Blow, 3A    | 2.16             | MCCFB2410TTT/C/3   |
| SMD Fuse with Holder, 2410, Slow Blow, 3.5A  | 2.9              | MCCFB2410TTT/C/3.5 |
| SMD Fuse with Holder, 2410, Slow Blow, 4A    | 3.84             | MCCFB2410TTT/C/4   |
| SMD Fuse with Holder, 2410, Slow Blow, 5A    | 7.5              | MCCFB2410TTT/C/5   |
| SMD Fuse with Holder, 2410, Slow Blow, 750mA | 0.306            | MCCFB2410TTT/C/750 |

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)

