



### Main

Range	TeSys
Product name	TeSys VARIO
Device short name	VCCF
Product or component type	Emergency stop switch disconnecter
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Network type	DC AC
Control type	Rotary handle
Rotary handle mounting style	Extended
Handle colour	Red
Handle front plate colour	Yellow
Suitability for isolation	Yes

### Complementary

Rotary handle padlocking	1 to 3 padlocks 4...8 mm
Marking	0 - 1
Mounting support	Handle mounting on door Switch mounting on symmetrical rail Switch mounting on plate
Fixing mode	By clips for switch By screws for switch By 4 screws for handle
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	80 A

[Ithe] conventional enclosed thermal current	63 A
[Ie] rated operational current	57 A (AC-23) at 400 V
Rated operational power in W	15 kW at 230...240 V (AC-3) 22 kW at 400...415 V (AC-3) 30 kW at 500 V (AC-3) 30 kW at 690 V (AC-23A) 37 kW at 500 V (AC-23A) 18.5 kW at 690 V (AC-3) 18.5 kW at 230...240 V (AC-23A) 30 kW at 400...415 V (AC-23A)
Intermittent duty class	30
Making capacity	800 A at 400 V (AC-21A) 800 A at 400 V (AC-22A) 800 A at 400 V (AC-23A)
[Icm] rated short-circuit making capacity	2.1 kA at 400 V at Ipeak
[Icw] rated short-time withstand current	960 A at 400 V during 1 s
Rated conditional short-circuit current	10 kA at 400 V - associated fuse 80 A aM 10 kA at 400 V - associated fuse 80 A gG
Breaking capacity	640 A at 400 V AC-21A 640 A at 400 V AC-22A 640 A at 400 V AC-23A
Device composition	Shaft extension Handle Switch
Mechanical durability	30000 cycles
Electrical durability	30000 cycles DC-1...5 30000 cycles AC-21
Connections - terminals	Power circuit : screw clamp terminals cable 16 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals cable 25 mm <sup>2</sup> - cable stiffness: solid
Tightening torque	Power circuit : 4 N.m - on screw clamp terminals
Base dimension	60 x 60 mm
Height	83 mm
Width	60 mm
Product weight	0.68 kg

## Environment

Standards	IEC 60947-3
Product certifications	UL CSA CCC GL
Protective treatment	TC
IP degree of protection	IP65 IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz 1 gn IEC 60068-2-6 Shocks 11 ms 30 Gn IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0733 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---