



### Main

Range	TeSys
Product name	TeSys Mini-VARIO
Device short name	VCFN
Product or component type	Emergency stop switch disconnecter
Performance level	Standard
Poles description	3P
Control type	Rotary handle
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks with 4...8 mm

### Complementary

Marking	0 - 1
[Ue] rated operational voltage	690 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ithe] conventional enclosed thermal current	32 A
Rated operational power in W	11 kW at 400 V AC-3 15 kW at 400 V AC-23
Intermittent duty class	30
Making capacity	400 A at 400 V AC-21A
[Icw] rated short-time withstand current	960 A at 400 V during 1 s
Rated conditional short-circuit current	10 kA at 400 V
Suitability for isolation	Yes
Fire resistance	960 °C conforming to IEC 60595-2-1
Base dimension	60 x 60 mm
Height	131 mm
Width	82.5 mm

Depth	106 mm
Product weight	0.512 kg

### Environment

Standards	IEC 60947-4-1
Protective treatment	TC
Mechanical robustness	Vibrations 10...150 Hz 1 gn IEC 60068-2-6 Shocks 11 ms 30 Gn IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0738 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------