



OUTDOOR.CASES

type 1000

- type 1000 is the smallest size for which there is also in insert with variable padded dividers (RPD). The case provides space for a camera with lens or a small digital camera.
- case shell made of polypropylene (PP)
- certified with the STANAG 4280, DEF STAN 81-41 and ATA 300 standards
- automatic air pressure compensation valve
- strong, dustproof, waterproof (IP67 certified)
- temperature resistant from -30° up to +80° C
- rubberized handle
- stackable
- two eyelets for padlocks (Ø 0.2 inch)
- 30 year warranty
- optional accessories: carrying strap (item no. CS/500), lid pocket (item no. LP/1000), mesh bag (item no. MB/1000) and panel frame (item no. PF/1000) available

Dimensions (metric)

Internal Dimensions:	9.8 x 6.9 x 3.7 inches
External Dimensions:	10.6 x 8.5 x 4.1 inches
Package Dimensions:	11 x 8.9 x 4.3 inches
Weight without packaging:	1.5 lb
Volume:	4.1 L
Payload:	22 lb

The dimensions are length x width x height. The weight specied is for each product and does not include any additional inserts. Technical changes are subject to modifications without notice.