



NOTES:

1. MATERIALS

- 1.1 CABLE: (7/0.12BC)*1P+(7/0.20BC+PVC)*2C+AL
+7/0.12BC+64/0.12ALM+BLACK PVC JACKET.
OD=∅4.5±0.15MM.

CABLE MARKING:USB 2.0 CABLE FULLY RATED 30V 80°C

- 1.2 CONNECTOR: P1: USB A TYPE MALE: SOLDER TYPE,
GOLD FLASH CONTACTS, NICKEL PLATED SHELL.

- 1.3 P2: USB2.0 MINI 5P B MALE: SOLDER TYPE,
GOLD FLASH CONTACTS, NICKEL PLATED SHELL.

- 1.4 ALL HOOD: MOLDED BLACK PVC.

2. 100% OPEN AND SHORT TEST.

3. PACKING: 1PCS/PE BAG.

4. ALL MATERIAL BE RoHS COMPLIANT.

PIN OUT

P1 ——— P2

- 1 ——— 1 RED
2 ——— 2 WHITE
3 ——— 3 GREEN
4 ——— 4 BLACK

SHELL ——— SHELL (BRAID+DRAIN)

——— > PAIR



LENGTH TOLERANCE:		SCALE:	CUS. NAME:		ENG:	
X. ± 0.5		FREE				
.X ± 0.2		UNIT:	CPC		PRODUCT NO:	
.XX ± 0.1						
ANGLE TOLERANCE:		VERSION:			CUSTOMER NO:	
X° ± 3°						
.X° ± 1°		00	PAGE:	1/1	DRAWING NO:	
					PRODUCT DESCRIPTION:	
					APPROVED:	

00	NEW ISSUE	2018-1-3
REV.	MODIFY DESCRIPTION	DATE