

OC10G04PNBN00NST41



Products → Low Voltage Products and Systems → Switches → Cam Switches

General Information

| | |
|-------------------------------|--|
| Extended Product Type: | OC10G04PNBN00NST41 |
| Product ID: | 1SCA126592R1001 |
| EAN: | 6417019565620 |
| Catalog Description: | OC10G04PNBN00NST41 Cam switch |
| Long Description: | OC10 Cam switch, I _{th} =10A, Multi-Step, 4-contacts, Snap-on door mounting, Black Basic handle. Black handle and frontplate with standard text are included. Special engraved frontplates to be ordered as separate items. |

Additional Information

| | |
|--|-------------------------------|
| Ampere Rating UL/CSA: | 600 V AC 10 A |
| Color: | Black |
| Conventional Free-air Thermal Current (I_{th}): | q = 40 °C 10 A |
| Conventional Thermal Current (I_{the}): | Fully Enclosed 10 A |
| Country of Origin: | Finland (FI) |
| Customs Tariff Number: | 85365080 |
| Data Sheet, Technical Information: | 1SCC302009C0201 |
| Declaration of Conformity - CE: | 1SCC302005D0201 |
| EAN: | 6417019565620 |
| ETIM 5: | EC002611 - Control switch |
| ETIM 6: | EC002611 - Control switch |
| Enclosure Type: | Not enclosed |
| Function: | ST41 |
| Handle Type: | Basic handle |
| IIT Publishing Status: | Level 0 - Information enabled |
| Industrial IT Certification Level: | 0 |
| Instructions and Manuals: | 1SCC302013F0006 |
| Invoice Description: | OC10G04PNBN00NST41 Cam switch |
| Minimum Order Quantity: | 1 piece |
| Mounting Type: | Snap-on door mounting |
| Number of Contacts: | 4 |
| Number of Poles: | 1 |
| Object Classification Code: | Q |
| Order Multiple: | 1 piece |
| Package Level 1 EAN: | 6417019565620 |
| Package Level 1 Gross Weight: | 0.05 kg |
| Package Level 1 Height: | 50 mm |
| Package Level 1 Length: | 108 mm |
| Package Level 1 Units: | 1 piece |
| Package Level 1 Width: | 50 mm |
| Pollution Degree: | 3 |
| Power Loss: | 0.6 W |
| Price Category: | Standard |
| Product Main Type: | OC10 |
| Product Name: | Cam switch |
| Product Net Depth: | 81 mm |

| | |
|--|---|
| Product Net Depth: | 32 mm |
| Product Net Height: | 32 mm |
| Product Net Weight: | 0.05 kg |
| Product Net Width: | 32 mm |
| Rated Continuous Thermal Current: | 10 A |
| Rated Impulse Withstand Voltage (U_{imp}): | 2.5 kV |
| Rated Insulation Voltage (U_i): | 500 V |
| Rated Operational Current AC-22A (I_e): | (500 V) 10 A |
| Rated Operational Current AC-23A (I_e): | (230 V) Three Phase 7.6 A (400 V) Three Phase 6.5 A |
| Rated Operational Power AC-23A (P_e): | (230 V) Three Phase 1.8 kW (400 V) Three Phase 3 kW |
| Rated Operational Voltage: | 500 V |
| Rated Short-time Withstand Current (I_{cw}): | for 1 s 0.12 kiloampere rms |
| Selling Unit of Measure: | piece |
| Short Description: | OC10 Cam switch, Ith=10A, Multi-Step, 4-contacts, Snap-on door mounting, Black Basic handle |
| Special Functions: | Multistep switch: 4-step, without 0-position, step angle 30°, front plate 1-2-3-4 |
| Terminal Type: | Screw Terminals |
| Wiring Diagram: | 1SCC302014M0201 |

