

Metal-Content Spiral Binding

SBPEMC

SBPEMC is designed for applications in food-processing plants and machines.

Features and Benefits

- High metal-content for reliable detection with standard detection equipment
- Stainless steel preserves resistance to corrosion
- Blue colour for enhanced visibility
- Ideal solution for bundling and protecting cables and hoses
- Highly flexible
- Suitable for retro-fitting
- Branching off cable at any point




SBPEMC metal-content spiral binding.



One Step to the Web!



Detectable, metal-content spiral binding protects cables on food-processing machines.



Spiral binding

MATERIAL	Polyethylene (PE), Stainless Steel (SS)
Operating Temperature	-60 °C to +80 °C, intermittent +120 °C
Flammability	UL94 HB
Specifications	FDA



TYPE	Nominal Ø	Wall (WT)	Pitch (P)	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Article-No.
SBPEMC1.5	1.5	0.80	6.0	1.6	8.0	Blue (BU)	30 m	161-46000
SBPEMC4	4	1.40	12.5	5.0	20.0	Blue (BU)	30 m	161-46100
SBPEMC9	9	1.60	16.0	10.0	100.0	Blue (BU)	30 m	161-46200
SBPEMC16	16	1.00	7.8	20.0	150.0	Blue (BU)	30 m	161-46300

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.