

Cable marker - LS-WMTB-V4A (100X15) - 0831519

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Cable marker, Stainless steel label, silver, unlabeled, can be labeled with: TOPMARK LASER, mounting type: Assembly with cable binders, cable diameter: > 4.6 mm, lettering field size: 100 x 15 mm



Why buy this product

- Stainless steel cable marking for assembly with cable binders
- High-quality appearance
- Suitable for large-surface marking of conductors and cables > 4.6 mm in diameter

Key Commercial Data

Packing unit	5 STK
Minimum order quantity	5 STK
GTIN	 4 046356 925297
GTIN	4046356925297
Weight per Piece (excluding packing)	105.210 g
Custom tariff number	73269098
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	118 mm
Width (a)	15 mm
Material thickness (g)	0.50 mm

Ambient conditions

Ambient temperature (operation)	-80 °C ... 400 °C
---------------------------------	-------------------

General

Color	silver
-------	--------

Cable marker - LS-WMTB-V4A (100X15) - 0831519

Technical data

General

Type	Card form
Components	free from silicone, halogen, and cadmium
Material	V4A
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	8
Printability	Direct laser marking
Device	0831831 TOPMARK LASER
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	Assembly with cable binders

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 5.1	27400401
eCl@ss 6.0	27149103
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530

UNSPSC

UNSPSC 13.2	39131504
-------------	----------

Cable marker - LS-WMTB-V4A (100X15) - 0831519

Accessories

Accessories

Magazine

Magazine - TOPMARK LASER-MAG SHEET - 0831836

Sheet magazine for TOPMARK LASER



Printing system

Laser marker - TOPMARK LASER - 0831831



Laser marker and MARKING NOTEBOOK with German operating system and German keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit