

Label - MM-EML (EX10)R C1 WH/BK - 0803970

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Product Description

The MM-EML... polyamide self-adhesive labels are available as continuous media for equipment marking.



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 212463
GTIN	4055626212463
Weight per Piece (excluding packing)	56.600 g
Custom tariff number	39199080
Country of origin	China

Technical data

Dimensions

Length (b)	8 m
Width (a)	10 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 149 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.

General

Color	white
Components	free from silicone, halogen, and cadmium
Material	Polyester
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Label - MM-EML (EX10)R C1 WH/BK - 0803970

Technical data

General

Adhesive	Acrylic
Printability	Thermal transfer
Device	0803984 THERMOFOX
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 4.1	24190219
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 5.0	EC001288
ETIM 6.0	EC001288

UNSPSC

UNSPSC 13.2	39131504
-------------	----------