

Products → Low Voltage Products and Systems → Enclosed Switches → Enclosed Cam Switches

General Information

| | |
|-------------------------------|---|
| Extended Product Type: | ONA3EPB |
| Product ID: | 1SCA022662R3500 |
| EAN: | 4034656524005 |
| Catalog Description: | ONA3EPB Enclosed cam switch |
| Long Description: | Enclosed cam switch 3-p.400V AC23A 7.5kW AC22A 20A Plastic enclosure IP65 Black Selector handle |

Additional Information

| | |
|---|-------------------------------|
| Ampere Rating UL/CSA: | 600 V AC 25 A |
| Cable Entry Position: | Up/Down |
| Cable Outlets Per Side: | M knock-outs |
| Color: | Black |
| Conventional Free-air Thermal Current (I_{th}): | q = 40 °C 25 A |
| Conventional Thermal Current (I_{the}): | Fully Enclosed 25 A |
| Country of Origin: | Germany (DE) |
| Customs Tariff Number: | 85371099 |
| Data Sheet, Technical Information: | 1SCC302003C0201 |
| Declaration of Conformity - CE: | 1SCC302001D0204 |
| Degree of Protection: | IP54 IP65 |
| EAN: | 4034656524005 |
| ETIM 5: | EC002611 - Control switch |
| ETIM 6: | EC002611 - Control switch |
| Enclosure Material: | Plastic |
| Enclosure Type: | Enclosed |
| Environmental Information: | 1SCC302003D0201 |
| Function: | A3 |
| Handle Type: | Basic handle |
| IIT Publishing Status: | Level 0 - Information enabled |
| Industrial IT Certification Level: | 0 |
| Instructions and Manuals: | 1SCC302004M0203 |
| Invoice Description: | ONA3EPB Enclosed cam switch |
| Minimum Order Quantity: | 1 piece |
| Mounting Type: | Switch in enclosure |
| Number of Contacts: | 3 |
| Number of Poles: | 3 |
| Object Classification Code: | Q |
| Order Multiple: | 1 piece |
| Package Level 1 EAN: | 4034656524005 |
| Package Level 1 Gross Weight: | 0.4 kg |
| Package Level 1 Height: | 120 mm |
| Package Level 1 Length: | 157 mm |
| Package Level 1 Units: | 1 piece |
| Package Level 1 Width: | 132 mm |
| Pollution Degree: | 2 |

| | |
|--|---|
| Protection Degree: | 3 |
| Price Category: | Standard |
| Product Main Type: | ON |
| Product Name: | Cam switch |
| Product Net Depth: | 70 mm |
| Product Net Height: | 96 mm |
| Product Net Weight: | 0.3 kg |
| Product Net Width: | 96 mm |
| Rated Continuous Thermal Current: | FullyEnclosed 25 A |
| Rated Impulse Withstand Voltage (U_{imp}): | 4 kV |
| Rated Insulation Voltage (U_i): | 690 V |
| Rated Operational Current AC-22A (I_e): | (500 V) 20 A (690 V) 20 A |
| Rated Operational Power AC-23A (P_e): | (220 ... 240 V) 2,6 kW (400 V) 7,5 kW (500 V) 4,8 kW (690 V) 4,8 kW |
| Rated Operational Voltage: | 690 V |
| RoHS Information: | 1SCC302004D0201 |
| Selling Unit of Measure: | piece |
| Short Description: | Enclosed cam switch 3-p.400V AC23A 7.5kW AC22A 20A |
| Special Functions: | ON - OFF switch: 0-position: 9 o'clock, basic handle, step angle 90°, front plate 0-1 |
| Terminal Type: | Screw Terminals |

