

minimate*

IPL1-106-01-L-D-RE1-K IPL1-110-02-L-S-K-TR IPL1-105-02-L-D-K-TR IPL1-120-01-L-D-RA-K **IPL1 SERIES**

(2.54 mm) .100"

CRETE WIRE HEADER

SPECIFICATIONS

For complete specifications www.samtec.com?IPL1

Insulator Material: Natural LCP Terminal Material: Phosphor Bronze Plating:

Sn or Au over 50 μ" (1.27 μm) Ni Operating Temp Range: -55 °C to +125 °C Voltage Rating: 675 VAC/954 VDC **RoHS Compliant:** Yes

PROCESSING

Lead-Free Solderable:

Yes —S & -D (-02 Lead Style)
SMT Lead Coplanarity:
(0.10 mm) .004" max (02-05)
(0.13 mm) .005" max (06-10)*
(0.15 mm) .006" max (11-25)* (.004" sténcil solution (.004 stencil solution may be available; contact IPG@samtec.com)

-SH SMT Lead Coplanarity:
(0.15 mm) .006" max (02-25)*
*(.004" stencil solution

*(.004" stencil solution may be available; contact IPG@samtec.com)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




ALSO AVAILABLE (MOQ Required)

- · Other sizes
- With or without plug polarization
- · Guide post holes
- · Other platings
- Weld tab

Contact Samtec.

Some lengths, styles and options are non-standard, non-returnable.

(5.44) .214



-01-S-RA

-01-D-RA

-01-D-RE1

-01

(0.64) .025 SQ

-02

-RA

Due to technical progress, all designs, specifications and components are subject to change without notice