

DHR171RMJ

Battery Type	Lithium-ion
Voltage	18 v
Battery quantity (4.0Ah)	2
Capacity in Concrete	17 mm
Capacity in Steel	10 mm
Capacity in Wood	13 mm
Impact energy	1.2 J
Shank	SDS PLUS
Impacts per Minute	0 - 4,800 ipm
Noise sound pressure	86 dB(A)
Noise sound power	97 dB(A)
Noise K factor	3 dB(A)
No Load Speed	0 - 680 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Hammer Drilling	9.0 m/sec ²
Vibration: Drilling into metal	2.5 m/sec ²
Net weight	2.8 kg



STANDARD EQUIPMENT: 196399-0 BATTERY BL1840 18V Li-ion, 821551-8 MAKPAC CONNECTOR CASE (TYPE 3), DC18RC DC18RC COMPACT CHARGER, Side handle, Depth stop

- Brushless motor
- One touch sliding chuck for easy bit installation and removal.
- 2-mode operation: Rotary only and Rotary hammer
- Electric brake
- Variable speed control by trigger
- Constant speed control
- Forward/reverse rotation
- LED job light
- Compact and lightweight design
- Vibration absorbing housing.