


PCB hybrid connector - LPCH 6/ 4+4-STL4-7,62 - 1716987

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Plug component, nominal current: 41 A, rated voltage (III/2): 1000 V, number of positions: 8, pitch: 7.62 mm, connection method: Push-in spring connection, color: green, contact surface: Tin

Why buy this product



Key Commercial Data

Packing unit	25 STK
GTIN	 4 055626 514925
GTIN	4055626514925
Weight per Piece (excluding packing)	38.000 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Item properties

Brief article description	PCB hybrid connector
Range of articles	LPCH 6/..-STL
Pitch	7.62 mm
Type of contact	Female connector
Plug-in system	POWER COMBICON 6 Hybrid
Number of positions	8
Connection method	Push-in spring connection
Number of levels	1

Electrical parameters

Rated current	41 A
Rated insulation voltage (III/2)	1000 V
Rated surge voltage (III/2)	8 kV

PCB hybrid connector - LPCH 6/ 4+4-STL4-7,62 - 1716987

Technical data

Power connection capacity

Conductor cross section solid	0.75 mm ² ... 6 mm ²
Conductor cross section flexible	0.75 mm ² ... 6 mm ²
Conductor cross section AWG / kcmil	18 ... 10
Conductor cross section flexible, with ferrule without plastic sleeve	0.75 mm ² ... 6 mm ²
Stripping length	18 mm

Connection capacity signal

Conductor cross section solid	0.2 mm ² ... 1.5 mm ²
Conductor cross section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section AWG / kcmil	24 ... 16
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/ JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	hot-dip tin-plated
Metal surface terminal point (top layer)	Tin (4 - 8 µm Sn)
Metal surface contact area (top layer)	Tin (4 - 8 µm Sn)

Dimensions for the product

Length [l]	48 mm
Width [w]	47.92 mm
Height [h]	27.5 mm
Pitch	7.62 mm

Packaging information

Type of packaging	packed in cardboard
Pieces per package	25
Denomination packing units	Pcs.

Mechanical tests according to standard

Test specification	IEC 61984
--------------------	-----------

Air clearances and creepage distances

Insulating material group	I
Voltage	800 V
Rated insulation voltage (III/3)	800 V
Rated insulation voltage (III/2)	1000 V
Rated insulation voltage (II/2)	1000 V
Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV

Electrical tests - Function

PCB hybrid connector - LPCH 6/ 4+4-STL4-7,62 - 1716987

Technical data

Electrical tests - Function

Specification	IEC 61984
---------------	-----------

Temperature cycles

Specification	IEC 61984
---------------	-----------

Current carrying capacity / derating curves

Specification	IEC 61984
---------------	-----------

Mechanical tests (A)

Test specification	IEC 61984
--------------------	-----------

Classifications

eCl@ss

eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 5.0	EC002638
----------	----------