

SAFETY DATA SHEET

Contact Treatment Grease 2X

According to Regulation (EC) No 1907/2006, Annex II, as amended. Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Contact Treatment Grease 2X
Product number SGB-b, ESGB20S, ESGB35SL, ESGB01K, ESGB05K, ESGB12.5K, ESGB25K, ZE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Lubricant.
Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier
ELECTROLUBE. A division of HK WENTWORTH LTD
ASHBY PARK, COALFIELD WAY,
ASHBY DE LA ZOUCH, LEICESTERSHIRE LE65 1JR
UNITED KINGDOM
+44 (0)1530 419600
+44 (0)1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

Emergency telephone +44 1865 407333

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified
Health hazards Not Classified
Environmental hazards Not Classified

2.2. Label elements

Hazard statements NC Not Classified

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Contact Treatment Grease 2X

| | | | |
|----------------------------|----------------------|--|-------------|
| Propylene carbonate | | | 1-5% |
| CAS number: 108-32-7 | EC number: 203-572-1 | REACH registration number: 01-2119537232-48-XXXX | |
| Classification | | | |
| Eye Irrit. 2 - H319 | | | |

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

| | |
|-----------------------------------|---|
| General information | Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel. |
| Inhalation | Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. |
| Ingestion | Rinse mouth thoroughly with water. Remove any dentures. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. |
| Skin contact | Remove affected person from source of contamination. Rinse immediately with plenty of water. |
| Eye contact | Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes. |
| Protection of first aiders | First aid personnel should wear appropriate protective equipment during any rescue. |

4.2. Most important symptoms and effects, both acute and delayed

| | |
|----------------------------|--|
| General information | See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure. |
| Inhalation | Prolonged inhalation of high concentrations may damage respiratory system. |
| Ingestion | Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation. |
| Skin contact | Prolonged contact may cause dryness of the skin. |
| Eye contact | May cause temporary eye irritation. |

4.3. Indication of any immediate medical attention and special treatment needed

| | |
|-----------------------------|--------------------------------|
| Notes for the doctor | Treat symptomatically. |
| Specific treatments | No special treatment required. |

SECTION 5: Firefighting measures

5.1. Extinguishing media

| | |
|---------------------------------------|--|
| Suitable extinguishing media | The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire. |
| Unsuitable extinguishing media | Do not use water jet as an extinguisher, as this will spread the fire. |

5.2. Special hazards arising from the substance or mixture

Contact Treatment Grease 2X

| | |
|--|---|
| Specific hazards | Containers can burst violently or explode when heated, due to excessive pressure build-up. |
| Hazardous combustion products | Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours. |
| 5.3. Advice for firefighters | |
| Protective actions during firefighting | Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. |
| Special protective equipment for firefighters | Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents. |

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

| | |
|-----------------------------|---|
| Personal precautions | No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage. |
|-----------------------------|---|

6.2. Environmental precautions

| | |
|----------------------------------|--|
| Environmental precautions | Avoid discharge to the aquatic environment. Large Spillages: Inform the relevant authorities if environmental pollution occurs (sewers, waterways, soil or air). |
|----------------------------------|--|

6.3. Methods and material for containment and cleaning up

| | |
|--------------------------------|---|
| Methods for cleaning up | Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Reuse or recycle products wherever possible. Approach the spillage from upwind. Small Spillages: If the product is soluble in water, dilute the spillage with water and mop it up. Alternatively, or if it is not water-soluble, absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. Large Spillages: If leakage cannot be stopped, evacuate area. Flush spilled material into an effluent treatment plant, or proceed as follows. Contain and absorb spillage with sand, earth or other non-combustible material. Place waste in labelled, sealed containers. Clean contaminated objects and areas thoroughly, observing environmental regulations. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. |
|--------------------------------|---|

6.4. Reference to other sections

| | |
|------------------------------------|---|
| Reference to other sections | For personal protection, see Section 8. For waste disposal, see Section 13. |
|------------------------------------|---|

SECTION 7: Handling and storage

7.1. Precautions for safe handling

| | |
|---|---|
| Usage precautions | Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. |
| Advice on general occupational hygiene | Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace. |

Contact Treatment Grease 2X

7.2. Conditions for safe storage, including any incompatibilities

| | |
|----------------------------|--|
| Storage precautions | Store away from incompatible materials (see Section 10). Store in accordance with local regulations. |
| Storage class | Unspecified storage. |

7.3. Specific end use(s)

| | |
|----------------------------|---|
| Specific end use(s) | The identified uses for this product are detailed in Section 1.2. |
|----------------------------|---|

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Good general ventilation should be adequate to control worker exposure to airborne contaminants.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with European Standard EN166. The following protection should be worn: Chemical splash goggles.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with European Standard EN374. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

Hygiene measures

Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke.

Respiratory protection

Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.

Environmental exposure controls

Not regarded as dangerous for the environment.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

| | |
|-------------------|-----------|
| Appearance | Grease. |
| Colour | Beige. |
| Odour | Oil-like. |

Contact Treatment Grease 2X

| | |
|---|---|
| pH | Not available. |
| Melting point | Not available. |
| Initial boiling point and range | Not available. |
| Flash point | Not available. |
| Evaporation rate | Not available. |
| Flammability (solid, gas) | Not available. |
| Upper/lower flammability or explosive limits | Not available. |
| Vapour pressure | 0.001 mm Hg @ 20°C/68°F |
| Vapour density | Not available. |
| Bulk density | 1.11 kg/l |
| Solubility(ies) | Not available. |
| Partition coefficient | Not available. |
| Auto-ignition temperature | Not available. |
| Decomposition Temperature | Not available. |
| Viscosity | Not available. |
| Explosive properties | Not considered to be explosive. |
| Oxidising properties | Does not meet the criteria for classification as oxidising. |

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity See the other subsections of this section for further details.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions No potentially hazardous reactions known.

10.4. Conditions to avoid

Conditions to avoid There are no known conditions that are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Contact Treatment Grease 2X

| | |
|--|---|
| Toxicological effects | Not regarded as a health hazard under current legislation. |
| <u>Acute toxicity - oral</u> | |
| Notes (oral LD₅₀) | Based on available data the classification criteria are not met. |
| <u>Acute toxicity - dermal</u> | |
| Notes (dermal LD₅₀) | Based on available data the classification criteria are not met. |
| <u>Acute toxicity - inhalation</u> | |
| Notes (inhalation LC₅₀) | Based on available data the classification criteria are not met. |
| <u>Skin corrosion/irritation</u> | |
| Animal data | Based on available data the classification criteria are not met. |
| <u>Serious eye damage/irritation</u> | |
| Serious eye damage/irritation | Based on available data the classification criteria are not met. |
| <u>Respiratory sensitisation</u> | |
| Respiratory sensitisation | Based on available data the classification criteria are not met. |
| <u>Skin sensitisation</u> | |
| Skin sensitisation | Based on available data the classification criteria are not met. |
| <u>Germ cell mutagenicity</u> | |
| Genotoxicity - in vitro | Based on available data the classification criteria are not met. |
| <u>Carcinogenicity</u> | |
| Carcinogenicity | Based on available data the classification criteria are not met. |
| IARC carcinogenicity | Contains a substance/a group of substances which may cause cancer. IARC Group 1 Carcinogenic to humans. |
| <u>Reproductive toxicity</u> | |
| Reproductive toxicity - fertility | Based on available data the classification criteria are not met. |
| Reproductive toxicity - development | Based on available data the classification criteria are not met. |
| <u>Specific target organ toxicity - single exposure</u> | |
| STOT - single exposure | Not classified as a specific target organ toxicant after a single exposure. |
| <u>Specific target organ toxicity - repeated exposure</u> | |
| STOT - repeated exposure | Not classified as a specific target organ toxicant after repeated exposure. |
| <u>Aspiration hazard</u> | |
| Aspiration hazard | Based on available data the classification criteria are not met. |
| General information | No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure. |
| Inhalation | Prolonged inhalation of high concentrations may damage respiratory system. |
| Ingestion | Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation. |
| Skin contact | Prolonged contact may cause dryness of the skin. |
| Eye contact | May cause temporary eye irritation. |
| Route of entry | Ingestion Inhalation Skin and/or eye contact |

Contact Treatment Grease 2X

Target organs No specific target organs known.

Propylene carbonate

Acute toxicity - oral

Acute toxicity oral (LD₅₀ mg/kg) 33,520.0

Species Rat

ATE oral (mg/kg) 33,520.0

Quartz (SiO₂)

Carcinogenicity

IARC carcinogenicity IARC Group 1 Carcinogenic to humans.

Benzotriazole

Acute toxicity - oral

Acute toxicity oral (LD₅₀ mg/kg) 560.0

Species Rat

ATE oral (mg/kg) 560.0

Acute toxicity - dermal

Notes (dermal LD₅₀) LD₅₀ > 2000 mg/kg, Dermal, Rabbit

Skin corrosion/irritation

Skin corrosion/irritation Not irritating.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Data lacking.

Carcinogenicity

Carcinogenicity There is no evidence that the product can cause cancer.

Reproductive toxicity

Reproductive toxicity - fertility Data lacking.

Specific target organ toxicity - single exposure

STOT - single exposure Data lacking.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Data lacking.

Aspiration hazard

Contact Treatment Grease 2X

| | |
|--------------------------|---|
| Aspiration hazard | Not anticipated to present an aspiration hazard, based on chemical structure. |
| Inhalation | Dust in high concentrations may irritate the respiratory system. |
| Ingestion | Harmful if swallowed. |
| Skin contact | Skin irritation should not occur when used as recommended. |
| Eye contact | Irritating to eyes. |

SECTION 12: Ecological Information

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

Benzotriazole

Ecotoxicity Toxic to aquatic life with long lasting effects.

12.1. Toxicity

Toxicity Based on available data the classification criteria are not met.

Benzotriazole

Acute toxicity - fish LC₅₀, 96 hours: 180 mg/l, Brachydanio rerio (Zebra Fish)

Acute toxicity - aquatic invertebrates EC₅₀, 48 hours: 15.8 mg/l, Daphnia magna

Acute toxicity - microorganisms EC₅₀, 3 hours: 1060 mg/l, Activated sludge

12.2. Persistence and degradability

Persistence and degradability The degradability of the product is not known.

Benzotriazole

Persistence and degradability The product is not expected to be biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not available.

Benzotriazole

Bioaccumulative potential The product is not bioaccumulating.

12.4. Mobility in soil

Mobility No data available.

Benzotriazole

Mobility The product is soluble in water.

Contact Treatment Grease 2X

12.5. Results of PBT and vPvB assessment

Benzotriazole

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects None known.

Benzotriazole

Other adverse effects Not determined.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements.

Disposal methods Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste packaging should be collected for reuse or recycling. Incineration or landfill should only be considered when recycling is not feasible. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of the local water authority.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

Transport labels

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Contact Treatment Grease 2X

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

| | |
|-----------------------------|--|
| National regulations | Health and Safety at Work etc. Act 1974 (as amended). The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"]. EH40/2005 Workplace exposure limits. |
| EU legislation | Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Commission Regulation (EU) No 2015/830 of 28 May 2015. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended). |

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

Inventories

EU - EINECS/ELINCS

None of the ingredients are listed or exempt.

SECTION 16: Other information

| | |
|---|---|
| Abbreviations and acronyms used in the safety data sheet | ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road. ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways. RID: European Agreement concerning the International Carriage of Dangerous Goods by Rail. IATA: International Air Transport Association. ICAO-TI: Technical Instructions for the Safe Transport of Dangerous Goods by Air. IMDG: International Maritime Dangerous Goods. CAS: Chemical Abstracts Service. ATE: Acute Toxicity Estimate. LC ₅₀ : Lethal Concentration to 50 % of a test population. LD ₅₀ : Lethal Dose to 50% of a test population (Median Lethal Dose). EC ₅₀ : 50% of maximal Effective Concentration. PBT: Persistent, Bioaccumulative and Toxic substance. vPvB: Very Persistent and Very Bioaccumulative. |
| Training advice | Read and follow manufacturer's recommendations. Only trained personnel should use this material. |
| Issued by | Bethan Massey |
| Revision date | 21/02/2017 |
| Revision | 0 |
| SDS number | 1052 |
| Hazard statements in full | H319 Causes serious eye irritation. |

Contact Treatment Grease 2X

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.