

Heavy Wall Tubing

Adhesive-Lined, Flame-Retardant, Polyolefin, Heat Shrink

pro-POWER

RoHS
Compliant



Application

Rugged, heavy wall tubing is specially designed for insulating, protecting and sealing electrical connections and joints in low-voltage cables where flame-retardant, electrical insulation and waterproof are required.

Specifications

Operating Temperature	: -45°C to +125°C
Fully Shrink Temperature	: 125°C
Shrink Ratio	: 3:1
Colour	: Black
Resistant to UV	

Technical Data

Property	Test Method	Typical Data
Tensile Strength	ASTM D2671	≥14 MPa
Elongation	ASTM D2671	≥400%
Density	ASTM D792	1.2g/cm ³
Longitudinal Change	UL 224	≤±10%
Elongation after Aging	UL224 158°C × 168hrs	≥300%
Heat Shock	UL224 225°C × 4hrs	No cracking
Dielectric Strength	IEC 243	≥20kV/mm
Volume Resistivity	IEC 93	≥1×10 ¹⁴ Ω·cm
Water absorption (%)	ASTM-D570	≤0.5
Flammability	VW-1	Self-extinguish in 30 seconds

Hot Melting Adhesive Property

Property	Test Method	Typical Data
Water Absorption	ASTM D570	≤0.2%
Softening Point	ASTM E28	95°C
Peel Strength (PE)	ASTM D1000	120N/25mm
Peel Strength (AL)	ASTM D1000	80N/25mm

Product Dimensions

Part Number	Size	As Supplied	After Recovery			
	mm	Internal Diameter (mm)	Internal Diameter	Out layer Wall Thickness	Adhesive Layer Wall Thickness	Total Wall Thickness
PP001869	9/3	≥9	≤3	2.03 ±0.3	0.48 ±0.2	2.5 ±0.4
PP001870	13/4	≥13	≤4	2.33 ±0.4	0.48 ±0.2	2.78 ±0.5
PP001871	20/6	≥20	≤6	2.33 ±0.4	0.63 ±0.2	2.95 ±0.5

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER

Heavy Wall Tubing
Adhesive-Lined, Flame-Retardant, Polyolefin, Heat Shrink



Part Number	Size	As Supplied	After Recovery			
	mm	Internal Diameter (mm)	Internal Diameter	Out layer Wall Thickness	Adhesive Layer Wall Thickness	Total Wall Thickness
PP001872	28/9	≥28	≤9	2.33 ±0.4	0.73 ±0.2	3.05 ±0.5
PP001873	38.1/12	≥38.1	≤12	3.13 ±0.5	0.73 ±0.4	3.55 ±0.5
PP001874	51/16	≥51	≤16	3.85 ±0.5	0.73 ±0.4	4.58 ±0.7
PP001875	70/21	≥70	≤21	3.65 ±0.5	-	-

Part Number Table

Description	Part Number
Tubing, Heat Shrink, Heavy Wall, W/ Adhesive, 3:1, 9mm, Black, 1.22m	PP001869
Tubing, Heat Shrink, Heavy Wall, W/ Adhesive, 3:1, 13mm, Black, 1.22m	PP001870
Tubing, Heat Shrink, Heavy Wall, W/ Adhesive, 3:1, 20mm, Black, 1.22m	PP001871
Tubing, Heat Shrink, Heavy Wall, W/ Adhesive, 3:1, 28mm, Black, 1.22m	PP001872
Tubing, Heat Shrink, Heavy Wall, W/ Adhesive, 3:1, 38.1mm, Black, 1.22m	PP001873
Tubing, Heat Shrink, Heavy Wall, W/ Adhesive, 3:1, 51mm, Black, 1.22m	PP001874
Tubing, Heat Shrink, Heavy Wall, W/ Adhesive, 3:1, 70mm, Black, 1.22m	PP001875

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.