

Triple/Quad Output Power Management ICs

The [ISL91212AR5770](#) is a 4-phase, three output programmable Power Management IC (PMIC) and the [ISL91212BR5771](#), [ISL91212BR5769](#), [ISL91212BR5775](#), and [ISL91212BR5772](#) are 4-phase, four output programmable PMICs. They are optimized with highly efficient, synchronous buck converters capable of multiphase and single-phase operations that can deliver up to 5A per phase continuous output current. They feature four buck controllers and can reconfigure their power stages to these controllers. This flexibility allows seamless design-in for a wide range of applications requiring high output power and small solution size.

These ISL91212 PMICs integrate low ON-resistance MOSFETs and programmable PWM frequency, allowing the use of very small external inductors and capacitors. They feature automatic Diode Emulation and Pulse Skipping modes under light-load conditions to further improve efficiency and maximize battery life. These PMICs deliver highly robust power solutions by using a controller based on Intersil’s proprietary R5 Technology, which provides tight output accuracy and load regulation, ultra-fast transient response, seamless DCM/CCM transitions, and require no external compensation.

In addition to the standard interrupt, chip enable, and watchdog reset functions, these ISL91212 PMICs feature three MPIOs and two GPIOs capable of supporting I<sup>2</sup>C communication and various other pin mode functions.

**Related Literature**

- For a full list of related documents, visit our website
- [ISL91212AR5770](#), [ISL91212BR5771](#), [ISL91212BR5769](#), [ISL91212BR5775](#), and [ISL91212BR5772](#) product pages

**Features**

- Triple output 2+1+1 phases (ISL91212AR5770) or quad output single phase (ISL91212BR5771, ISL91212BR5769, ISL91212BR5775, and ISL91212BR5772)
- 2.5V to 5.5V supply voltage
- 5A per phase output current capability
- Small solution size (7x10mm<sup>2</sup> for four phase design)
- High efficiency (94.7% for 3.8V<sub>IN</sub>/1.8V<sub>OUT</sub>)
- Low I<sub>Q</sub> in low power mode
- Patented control scheme reduces output capacitor and supports fast load transient (such as 50A/μs/phase)
- ±0.7% system accuracy, remote voltage sensing
- Programmable PWM frequency from 2MHz to 6MHz
- I<sup>2</sup>C programmable output from 0.3V to 2V
- Independent Dynamic Voltage Scaling (DVS) for each output
- Soft-start and fault detection (UV, OV, OC, OT), short circuit protection
- 2.551x3.67mm 35 ball WLCSP with 0.5mm pin pitch

**Applications**

- FPGA power
- Industrial MPU power, human machine interface
- Optical transceivers
- SSD




Figure 1. Dual Phase Efficiency




Figure 2. Single Phase Efficiency

© Copyright Intersil Americas LLC 2017. All Rights Reserved.  
All trademarks and registered trademarks are the property of their respective owners.

For additional products, see [www.intersil.com/en/products.html](http://www.intersil.com/en/products.html)

---

Intersil products are manufactured, assembled and tested utilizing ISO9001 quality systems as noted  
in the quality certifications found at [www.intersil.com/en/support/qualandreliability.html](http://www.intersil.com/en/support/qualandreliability.html)

---

*Intersil products are sold by description only. Intersil may modify the circuit design and/or specifications of products at any time without notice, provided that such modification does not, in Intersil's sole judgment, affect the form, fit or function of the product. Accordingly, the reader is cautioned to verify that datasheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.*

---

For information regarding Intersil Corporation and its products, see [www.intersil.com](http://www.intersil.com)