



Wireless Microphone System with (2) Body-Pack Transmitters, Headset & Lavalier Mics, UHF Selectable Frequency, LCD Display, Rack Mountable

PDWM3365



Features:

- UHF Band Receiver System
- 16 Channel Frequency Design
- PLL-Synthesized Control Technique
- Double Noise Squelch Operation Circuitry
- Up to 165' Feet Wireless Communication Range
- Broad Frequency Response Range & Low Distortion
- Integrated Noise Filtration System
- High Signal/Noise Ratio Performance
- AF and RF Signal LED Indicators
- Independent Channel Adjustable Volume Controls
- LCD Digital Display with Channel & Frequency Readout
- (2) XLR Mixed Balanced Output Jack Connectors
- 1/4" Unbalanced Audio Output Jack Connector
- Easy-to-Use Touch Button Controls
- Detachable Dual Antennas
- Rack Mountable System

What's in the Box:

- Receiver Base
- (2) Body-Pack Transmitters
- (2) Headset Microphones
- (2) Lavalier Microphones
- Detachable Rack Mount Brackets
- 1/4" Audio Cable
- Power Adapter
- Travel Case

Bodypack Transmitters:

- Includes (2) Bodypack Transmitters
- RF Output: 10dBm
- Modulation Type: FM
- Max Deviation: $\pm 70\text{KHz}$
- Spurious Emission: $> 55\text{dB}$
- Power Requirements: (2) 'AA' Batteries
- Dimensions (L x W x H): 4.0" x 2.5" x 1.0"

Receiver Base:

- Audio Frequency Response: 100-18 kHz
- Mobile State Range: 100dB
- Receiving Sensitivity: -105dBm
- Signal/Noise Ratio: >85dB
- Image & Spurious Rejection: >70dB
- Audio Output Level: +/- 300mV
- Frequency Stability: +/- 0.005%
- Maximum Deviation: +/- 15kHz
- T.H.D.: <1%
- Dimensions: 8.5" x 6.7" x 2.0" -inches
- Power Supply: DC 13-15V
- Sold as: Unit
- Weight: 6.34 lbs.