

101057 STEP DRILL 6-32mm



Technical data

Ø	6,0 - 32,0 mm
Total length L1	75,0 mm
Shank Ø	10,0 mm
Size no.	6
Steps	8

Material	HSS
Surface	bright
Cutting direction	right hand cut
Shank	3-way clamping surface
Point cut	Shape C: Split point
Point angle	118°
Point cut	work's specification
Step angle	90°
Tolerance	work's specification

Application areas

Steel (N/mm2) < 900	
Steel (N/mm2) < 1100	
Steel (N/mm2) < 1300	
Rust-resistant steel	
Aluminium	
Brass	
Bronze	
Plastics	
Cast iron	0
Titanium alloyed	

lacktriangle Main application \Box Other application