

# Current Transformer

## Round Style



### Features

- Designed for use with Wattmeter & Ammeters
- Fully Encapsulated Rubber Molding for Indoor & Outdoor Applications
- Round Style with 24" Long 16 AWG Flexible Leads

### Specifications

Mounting Type	: Panel
Frequency Range	: 50Hz to 400Hz
Output Current	: 0-5A
Insulation Class	: 0.6kV, 10kV BIL Full Wave
Linearity	: $\pm 1.5\%$
Thermal Rating	: 1.33VA @ 30°C, 1VA @ 55°C
Inside Diameter	: 1.5lb

### Part Number Table

Description	Current Ratio	Accuracy @ 60Hz	Burden VA @ 60Hz	Part Number
Current Transformer, Donut Type, 0-5A	800:5	$\pm 1\%$	35	SPC21631
Current Transformer, Donut Type, 0-5A	1000:5		30	SPC21632

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)

