

## FEATURES AND SPECIFICATIONS



## PowerCat C5E FTP Patch Cords PVC

### Features and Benefits

Molex Premise Networks PowerCat C5E FTP patch cords are manufactured using high quality shielded four pair Category C5E stranded cable. Available in a range of colours and lengths, PowerCat C5E FTP patch cords are pre-terminated with RJ45 shielded plugs and feature cable strain relief boots with a plug latch protection cap.

Suitable for high speed data transmission, PowerCat C5E FTP patch cords have been designed to exceed the highest electrical performance standards in the industry and are Category 5E component compliant.

- Shielded 4 pair stranded cable
- Pre-terminated with WEBW shielded plugs
- Strain relief boots
- C5E component compliant

### Compliant With

TIA/EIA-568-B.2-1, FCC Part 68 (Plug dimensions and tolerances), ISO 60603-7, ISO 11801:2002, EN 50173:2002

### Approvals

UL

### Technical Information

#### Mechanical Characteristics - Cable

Conductor size: 26 AWG stranded bare copper  
Screen Material: Aluminium/polyester shield with tinned copper drain wire  
Max O.D.: 5.5mm  
Jacket: PVC  
Temperature range: -20°C to +60°C


#### Mechanical Characteristics - Plug

Operating life: Minimum 750 insertion cycles  
Contact material: Copper alloy  
Contact plating: 1.25 micrometres Au/Ni

Plug dimensions & tolerances compliant with FCC Part 68 and IEC 60603-7

#### Electrical Characteristics - Plug

Max voltage: 150 VAC (max)  
Max current: 1.5A @ 25°C  
Operating temperature: -40°C to 85°C



## ORDERING INFORMATION

Order No.	Description
PCD-00341-0*	Patch Cord FTP 568A/B - 1m C5E
PCD-00342-0*	Patch Cord FTP 568A/B - 2m C5E
PCD-00343-0*	Patch Cord FTP 568A/B - 3m C5E
PCD-00344-0*	Patch Cord FTP 568A/B - 5m C5E
PCD-00345-0*	Patch Cord FTP 568A/B - 7m C5E
PCD-00346-0*	Patch Cord FTP 568A/B - 10m C5E

\* Colour Options: C=Red, E=Grey, H=Blue, J=Green, K=Yellow

## MOLEX PREMISE NETWORKS

Corporate Headquarters  
Tel: 1-866-733-6659  
www.molexpn.com

European Headquarters  
Tel: 44 (0) 1489 527111  
www.molexpn.co.uk

Pac Rim Headquarters  
Tel: 61 3 9971 7111  
www.molexpn.com.au



2 metre Category 6 FTP Patch Cord Typical (dB)

NEXT

Return Loss

Frequency (MHz)	NEXT Limit (dB)	NEXT	Return Loss Limit (dB)	Return Loss
1	65	82	19.8	42.1
4	62.3	72.6	21.6	32.4
8	56.3	66.3	22.5	31.1
10	54.4	65	22.8	30.7
16	50.4	62.3	23.4	29.9
20	48.6	61.5	23.7	28.9
25	46.7	61.3	23.9	27
31.3	44.8	61	23.1	24.6
62.6	38.9	63.1	20	28.3
100	35	50.8	18	23.4

**MOLEX PREMISE NETWORKS**

Corporate Headquarters  
Tel: 1-866-733-6659  
www.molexpn.com

European Headquarters  
Tel: 44 (0) 1489 527111  
www.molexpn.co.uk

Pac Rim Headquarters  
Tel: 61 3 9971 7111  
www.molexpn.com.au