

# KPTB-1612LVSURKCGKC

1.6 x 1.25 mm Bi-Color SMD Chip LED Lamp



## DESCRIPTIONS

- The Hyper Red source color devices are made with AIGaInP on GaAs substrate Light Emitting Diode
- The Green source color devices are made with AIGaInP on GaAs substrate Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- · It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

## **FEATURES**

- 1.6 mm x 1.25 mm SMD LED. 0.65 mm thickness
- · Bi-color, low power consumption
- Wide viewing angle
- · Ideal for backlight and indicator
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- RoHS compliant

## **APPLICATIONS**


- Backlight
- Status indicator
- Home and smart appliances
- · Wearable and portable devices
- Healthcare applications


## **ATTENTION**


Observe precautions for handling electrostatic discharge sensitive devices





## PACKAGE DIMENSIONS












### **RECOMMENDED SOLDERING PATTERN**

(units : mm; tolerance :  $\pm 0.1$ )



Notes

1. All dimensions are in millimeters (inches)

Tolerance is ±0.2(0.008") unless otherwise noted.
The specifications, characteristics and technical data described in the datasheet are subject to

change without prior notice. The device has a single mounting surface. The device must be mounted according to the specifications 4.

## **SELECTION GUIDE**

Part Number	Emitting Color (Material)	Lens Type	lv (mcd) @ 2mA <sup>[2]</sup>		Viewing Angle <sup>[1]</sup>	
			Min.	Тур.	201/2	
KPTB-1612LVSURKCGKC	Hyper Red (AlGaInP)	Water Clear	10	20		
			*4	*9	4500	
	Green (AlGaInP)		1.2	3	150°	
			*1.2	*3		

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value 2. Luminous intensity / luminous flux: +/-15%.
- Luminous intensity value is traceable to CIE127-2007 standards.

# **Kingbright**

## ELECTRICAL / OPTICAL CHARACTERISTICS at T<sub>A</sub>=25°C

Parameter	Symbol	Emitting Color	Value			Unit
			Min.	Тур.	Max.	
Wavelength at Peak Emission $I_F$ = 2mA	$\lambda_{peak}$	Hyper Red Green	-	645 574	-	nm
Dominant Wavelength $I_F = 2mA$	$\lambda_{dom}$ <sup>[1]</sup>	Hyper Red Green	-	630 570	-	nm
Spectral Bandwidth at 50% $\Phi$ REL MAX I <sub>F</sub> = 2mA	Δλ	Hyper Red Green	-	28 20	-	nm
Capacitance	С	Hyper Red Green	-	35 15	-	pF
Forward Voltage I <sub>F</sub> = 2mA	V <sub>F</sub> <sup>[2]</sup>	Hyper Red Green	1.5 1.5	1.75 1.9	2.1 2.1	V
Reverse Current (V <sub>R</sub> = 5V)	I <sub>R</sub>	Hyper Red Green	-	-	10 10	uA

Notes:

The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd : ±1nm.)
Forward voltage: ±0.1V.
Wavelength value is traceable to CIE127-2007 standards.
Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

## ABSOLUTE MAXIMUM RATINGS at T<sub>A</sub>=25°C


Parameter	Symbol	Va	Unit	
i arameter		Hyper Red	Green	
Power Dissipation	P <sub>D</sub>	75	75	mW
Reverse Voltage	V <sub>R</sub>	5	5	V
Junction Temperature	TJ	115	115	°C
Operating Temperature	T <sub>op</sub>	-40 To +85		
Storage Temperature	T <sub>stg</sub>	-40 To +85		
DC Forward Current	I <sub>F</sub>	30	30	mA
Peak Forward Current	I <sub>FM</sub> <sup>[1]</sup>	185	150	mA
Electrostatic Discharge Threshold (HBM)	-	3000	3000	v

Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.


# Kingbright

## **KPTB-1612LVSURKCGKC**


## **TECHNICAL DATA**




### SPATIAL DISTRIBUTION



**HYPER RED** 





€ 2017 Kingbright. All Rights Reserved. Spec No: DSAP3541 / 1203003040 Rev No: V.1A Date: 12/15/2017

# **Kingbright**


## **KPTB-1612LVSURKCGKC**

2

本

## **TECHNICAL DATA**


### **REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS**



#### TAPE <u>4±</u>0.1 2±0.1 φ1.5±0.1 0.23±0.1 4±0.1 1.75±0. 4 $0.92 \pm 0.1$ 厶 $3.5\pm 0.$ 4 8±0.2 1 F 1.85<u>+</u>0.1 \φ1Typ. 1.47±0.1 A-A Section

**REEL DIMENSION** (units : mm)


TAPE SPECIFICATIONS (units : mm)



#### Notes

 Don't cause stress to the LEDs while it is exposed to high temperature.
The maximum number of reflow soldering passes is 2 times.
Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product

## **PACKING & LABEL SPECIFICATIONS**



#### PRECAUTIONARY NOTES

- 1. 2.
- The information included in this document reflects representative usage scenarios and is intended for technical reference only. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening
- 4 liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright 5
- 6. All design applications should refer to Kingbright application notes available at http://www.kingl aht.com