



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay to be ordered separately Contactor
Control type	Push-button start green I Push-button stop/reset red O

Complementary

[Ie] rated operational current	40 A AC-3
Motor power kW	11 kW at 220/230 V AC 50/60 Hz 22 kW at 415 V AC 50/60 Hz 22 kW at 440 V AC 50/60 Hz 22 kW at 500 V AC 50/60 Hz 30 kW at 660/690 V AC 50/60 Hz 18.5 kW at 380/400 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	40 A
[Uc] control circuit voltage	115 V AC 50/60 Hz
Cable entry number	1 cable entry : ISO32 top 3 cable entry : 1 ISO20 + 2 ISO32 bottom
Width	200 mm
Height	300 mm
Depth	158.4 mm
Product weight	4.82 kg
Compatibility code	LE1D

Environment

Material	Sheet steel
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529

Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
