



### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay to be ordered separately Contactor
Control type	Without

### Complementary

[Ie] rated operational current	65 A AC-3
Motor power kW	30 kW at 380/400 V AC 50/60 Hz 37 kW at 415 V AC 50/60 Hz 37 kW at 440 V AC 50/60 Hz 37 kW at 500 V AC 50/60 Hz 37 kW at 660/690 V AC 50/60 Hz 18.5 kW at 220/230 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	65 A
[Uc] control circuit voltage	230 V AC 50/60 Hz
Cable entry number	1 cable entry : ISO32 top 3 cable entry : 1 ISO20 + 2 ISO32 bottom
Width	200 mm
Height	300 mm
Depth	150 mm
Product weight	4.85 kg
Compatibility code	LE1D

### Environment

Material	Sheet steel
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529

---

Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C

---

### Offer Sustainability

---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

---