



Main

| | |
|---|---|
| Range of product | TeSys D |
| Range | TeSys |
| Product name | TeSys D Green |
| Product or component type | Contactor |
| Device short name | LC1D |
| Device short name | LC1D38 |
| Contactor application | Motor control Resistive load |
| Utilisation category | AC-1 AC-3 |
| Poles description | 3P |
| Pole contact composition | 3 NO |
| [Ue] rated operational voltage | ≤ 690 V AC 25...400 Hz for power circuit |
| [Ie] rated operational current | 38 A (≤ 60 °C) at ≤ 440 V AC AC-3 for power circuit 50 A (≤ 60 °C) at ≤ 440 V AC AC-1 for power circuit |
| Motor power kW | 18.5 kW at 380...400 V AC 50/60 Hz 18.5 kW at 500 V AC 50/60 Hz 18.5 kW at 660...690 V AC 50/60 Hz 18.5 kW at 415...440 V AC 50/60 Hz 9 kW at 220...230 V AC 50/60 Hz |
| Control circuit type | AC/DC 50/60 Hz AC/DC electronic |
| [Uc] control circuit voltage | 24...60 V AC 50/60 Hz 24...60 V DC |
| Coil type | AC/DC electronic |
| Auxiliary contact composition | 1 NO + 1 NC |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947 |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 50 A at ≤ 60 °C for power circuit 10 A at ≤ 60 °C for signalling circuit |
| Irms rated making capacity | 550 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 |

| | |
|--|---|
| | 250 A DC for signalling circuit conforming to IEC 60947-5-1 |
| Rated breaking capacity | 550 A at 440 V for power circuit conforming to IEC 60947 |
| [Icw] rated short-time withstand current | 150 A <= 40 °C 1 min power circuit 310 A <= 40 °C 10 s power circuit 430 A <= 40 °C 1 s power circuit 60 A <= 40 °C 10 min power circuit 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit |
| Associated fuse rating | 63 A gG at <= 690 V coordination type 1 for power circuit 63 A gG at <= 690 V coordination type 2 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1 |
| Average impedance | 2 mOhm at 50 Hz - Ith 50 A for power circuit |
| [Ui] rated insulation voltage | 690 V for power circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-1 |
| Electrical durability | 23000 cycles AC-4 at Ue <= 440 V (date code >= 17221) 2 Mcycles 38 A AC-3 at Ue <= 440 V (date code >= 17221) 650000 cycles 50 A AC-1 at Ue <= 440 V (date code >= 17221) |
| Power dissipation per pole | 3 W AC-3 5 W AC-1 |
| Protective cover | With |
| Mounting support | Plate Rail |
| Standards | EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 EN/IEC 60947-5-1 |
| Product certifications | UL CSA CCC EAC KC |
| Connections - terminals | Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 1 cable(s) 1.5...10 mm ² - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Power circuit : screw clamp terminals 1 cable(s) 2.5...10 mm ² - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 2 cable(s) 2.5...10 mm ² - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 1 cable(s) 1...10 mm ² - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 2 cable(s) 1.5...6 mm ² - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 2 cable(s) 2.5...10 mm ² - cable stiffness: solid - without cable end |
| Tightening torque | Control circuit : 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit : 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit : 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit : 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2 |
| Operating time | 45...55 ms closing 20...90 ms opening (date code >= 17221) |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical durability | 15 Mcycles (date code >= 17221) |
| Operating rate | 3600 cyc/h at <= 60 °C |

Complementary

| | |
|--------------------------------|---|
| Coil technology | Built-in bidirectional peak limiting |
| Control circuit voltage limits | <= 0.1 Uc drop-out at 60 °C 0.85...1.1 Uc operational at 60 °C, AC |

0.8...1.2 Uc operational at 60 °C, DC

| | |
|---------------------------------|--|
| Inrush power in VA | 15 VA at 20 °C 50/60 Hz |
| Inrush power in W | 14 W at 20 °C |
| Hold-in power consumption in VA | 0.9 VA at 20 °C 50/60 Hz |
| Hold-in power consumption in W | 0.6 W at 20 °C |
| Heat dissipation | 0.6 W at 50/60 Hz |
| Auxiliary contacts type | Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1 |
| Signalling circuit frequency | 25...400 Hz |
| Minimum switching current | 5 mA for signalling circuit |
| Minimum switching voltage | 17 V for signalling circuit |
| Non-overlap time | 1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact) |
| Insulation resistance | > 10 MOhm for signalling circuit |
| Compatibility code | LC1D |

Environment

| | |
|---|---|
| IP degree of protection | IP20 front face conforming to IEC 60529 |
| Protective treatment | TH conforming to IEC 60068-2-30 |
| Pollution degree | 3 |
| Ambient air temperature for operation | -25...60 °C |
| Ambient air temperature for storage | -60...80 °C |
| Permissible ambient air temperature around the device | -40...70 °C at Uc |
| Operating altitude | 3000 m without derating in temperature |
| Fire resistance | 850 °C conforming to IEC 60695-2-1 |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 8 Gn for 11 ms |
| Height | 85 mm |
| Width | 45 mm |
| Depth | 92 mm |
| Product weight | 0.442 kg |
| Colour | Grey SE GREY 6 Green SE GREEN 2 |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1640 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product environmental |
| Product end of life instructions | Available End of life manual |