




Suppliers of Quality Assured Cables

# Flexible Wiring Cable - Test Leads



**Product Type:**  
Flexible Cable

**Application:**  
Flexible leads used mainly as a flexible connection to or from test equipment.

**Standards / Conformances:**  
REACH and RoHS Compliant

**Construction:**

Conductor:	Tinned annealed copper to EN60228 Class 5
Insulation:	Silicone rubber to EN50363-1, Type EI2 Various colours

**Electrical Characteristics:**

Rated Voltage 300/500V

**Physical Characteristics:**

Maximum temperature 180°C  
Flame propagation IEC 60332-1-2

Part Number	Colour	Length	Conductor Strand	Nom cable diameter /mm	Max. Conductor DC Resistance at 20°C (Ω/Km)
6001840	Black	25m	128/0.05mm	2.0	80.1
4002483	Black	1000m	128/0.05mm	2.0	80.1
6001895	Red	25m	128/0.05mm	2.0	80.1
4002484	Red	1000m	128/0.05mm	2.0	80.1
6001156	Black	25m	256/0.05mm	2.5	40.1
	Black	1000m	256/0.05mm	2.5	40.1
6001157	Red	25m	256/0.05mm	2.5	40.1
6012437	Red	1000m	256/0.05mm	2.5	40.1
6001897	Black	25m	384/0.05mm	3.3	26.7
6001898	Red	25m	384/0.05mm	3.3	26.7
6001159	Black	25m	504/0.05mm	3.8	20.0
6001160	Red	25m	504/0.05mm	3.8	20.0
6011295	Black	1000m	332/0.06mm	3.8	20.0
6011205	Red	1000m	332/0.06mm	3.8	20.0
6001555	Black	25m	462/0.08mm	3.9	8.21
6011204	Black	1000m	462/0.08mm	3.9	8.21
6001556	Red	25m	462/0.08mm	3.9	8.21
6011092	Red	1000m	462/0.08mm	3.9	8.21
6011093	Yellow	25m	462/0.08mm	3.9	8.21
4001605	Yellow	1000m	462/0.08mm	3.9	8.21
6011940	Green	25m	462/0.08mm	3.9	8.21
6011296	Green	1000m	462/0.08mm	3.9	8.21