



Revision Number: 004.0

Issue date: 04/24/2017

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: LOCTITE NC-AA WICK known as NC-AA NO CLEAN 1.5M WICK 10-REL **IDH number:** 1756009
Product type: Desoldering wick
Restriction of Use: None identified **Region:** United States
Company address: **Contact information:**
 Henkel AG & Co. KGaA Telephone: +49 (211) 797 0
 Henkelstr. 67
 Düsseldorf 40589

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: CAUSES SKIN AND EYE IRRITATION.
 MAY CAUSE AN ALLERGIC SKIN REACTION.
 MAY CAUSE DROWSINESS OR DIZZINESS.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2B
SKIN SENSITIZATION	1
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3

PICTOGRAM(S)



Precautionary Statements

Prevention: Avoid breathing dust or fumes. Wash affected area thoroughly after handling. Use only outdoors or in a well-ventilated area. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves.
Response: IF ON SKIN: Wash with plenty of water. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
Storage: Store in a well-ventilated place. Keep container tightly closed. Store locked up.
Disposal: Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Copper	7440-50-8	90 - 100
1,3-Propanediol, 2,2-bis[(benzoyloxy)methyl]-, dibenzoate	4196-86-5	1 - 5
Rosin, maleated, polymer with Pentaerythritol	68333-69-7	1 - 5

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
Skin contact:	Remove contaminated clothing and footwear. Immediately flush skin with plenty of water (using soap, if available). If symptoms develop and persist, get medical attention. Wash clothing before reuse.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Ingestion:	Induce vomiting as directed by medical personnel if person is conscious. Never give anything by mouth to an unconscious person. Get medical attention. Wire strands could cause internal injury
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear a self-contained breathing apparatus with a full face piece operated in pressure-demand or other positive pressure mode. Do not use water on fires where molten metal is present.
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon. Oxides of Metals in Section 3. High temperatures may produce heavy metal dust, fumes or vapors. The flux medium will give rise to irritating fumes.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Scrape up as much material as possible.

7. HANDLING AND STORAGE

Handling:	Use only in well-ventilated areas. Avoid contact with eyes, skin and clothing. Do not wear contact lenses. Wash thoroughly after handling.
Storage:	Store in a cool, dry, well-ventilated area. Store in original container until ready to use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Copper	0.2 mg/m ³ TWA (as Cu) Fume. 1 mg/m ³ TWA (as Cu) Dust and mist.	1 mg/m ³ PEL (as Cu) Dust and mist. 0.1 mg/m ³ PEL (as Cu) Fume.	None	None
1,3-Propanediol, 2,2-bis[(benzoyloxy)methyl]-, dibenzoate	None	None	None	None
Rosin, maleated, polymer with Pentaerythritol	None	None	None	None

Engineering controls:	Ensure adequate ventilation. Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
Eye/face protection:	Safety goggles or safety glasses with side shields.
Skin protection:	Use impermeable gloves and protective clothing as necessary to prevent skin contact.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Solid
Color:	Copper
Odor:	None
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	Negligible vapor pressure at ambient temperatures.
Boiling point/range:	Not available.
Melting point/ range:	1,083 °C (1,981.4 °F) (copper)
Specific gravity:	8.9
Vapor density:	Not available.
Flash point:	Product is a solid.
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Insoluble
Partition coefficient (n-octanol/water):	Not available.
VOC content:	0 %; 0 g/l
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under recommended storage conditions.
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Oxides of carbon. Oxides of Metals in Section 3. Irritating fumes.
Incompatible materials:	Acids and bases. Oxidizing agents.
Reactivity:	Not available.
Conditions to avoid:	Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects/Symptoms

Inhalation:	Inhalation of processing fumes may be harmful. Vapor overexposure may cause drowsiness. Dizziness. Fumes evolved at soldering temperatures will irritate the nose, throat and lungs.
Skin contact:	Causes skin irritation. May cause allergic skin reaction.
Eye contact:	Causes eye irritation.
Ingestion:	Not expected under normal conditions of use. Wire strands could cause internal injury

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Copper	None	Allergen, Blood, Central nervous system, Developmental, Gastrointestinal, Immune system, Irritant, Kidney, Liver, Mutagen, Sensory, Skin
1,3-Propanediol, 2,2-bis[(benzoyloxy)methyl]-, dibenzoate	None	Irritant
Rosin, maleated, polymer with Pentaerythritol	None	No Records

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Copper	No	No	No
1,3-Propanediol, 2,2-bis[(benzoyloxy)methyl]-, dibenzoate	No	No	No
Rosin, maleated, polymer with Pentaerythritol	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis.

CERCLA/SARA Section 311/312: Immediate Health, Delayed Health

CERCLA/SARA Section 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Copper (CAS# 7440-50-8).

CERCLA Reportable quantity: Copper (CAS# 7440-50-8) 5,000 lbs. (2,270 kg)

California Proposition 65: No California Proposition 65 listed chemicals are known to be present.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Alicia Griffin, Regulatory Affairs Specialist

Issue date: 04/24/2017

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.