


# 2.54mm Pin Header

## Single Row, Right Angle, Through Hole Type



RoHS  
Compliant




### Specifications

Current Rating	: 3A AC/DC
Voltage Rating	: 250V AC/DC
Contact Resistance	: 20mΩ Max.
Insulation Resistance	: 1000MΩ Min.
Withstanding Voltage	: 600V AC for one minute
Operating Temperature Range	: -40°C to +105°C

### Materials

Insulator	: PBT (UL94V-0)
Insulator Colour	: Black
Contact	: Copper Alloy
Plating	: Gold Plated

### Diagram



Dimensions : Millimetres

### Part Number Table

Description	Part Number
Header, 2.54mm, R/A, 7POS, 1ROW, TH	2211R-07G
Header, 2.54mm, R/A, 9POS, 1ROW, TH	2211R-09G
Header, 2.54mm, R/A, 14POS, 1ROW, TH	2211R-14G

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com  
www.farnell.com  
www.newark.com

