

Data sheet

Connection cable M12 plug angled - free line end
4-pole, D-coded 2.0 m

Page 1/5

P/N

142M1D90020


EAN 4250184174967

2018-13-02


Illustrations



Dimensional drawing



Wiring



See enlarged drawings at the end of document

Product specification

- shielded M12 Ethernet connection cable
- Cat.5e, 4-pole, D-coded (IEC 61076-2-101)
- side 1: M12-plug, angled
- side 2: free line end
- extrusion-coated cable on M12 connector
- 2x2xAWG22/7, tinned with plastic foil
- inner sheath FRNC, aluminum-coated plastic foil
- overall shield: tinned copper braid, approx. 85% covered
- Profinet (WS-GE-BL-OR) wiring
- green cable, PUR
- variants: 1.0 m, 2.0 m, 5.0 m, 10.0 m
- other cable lengths on request



Data sheet

Page 2/5

Connection cable M12 plug angled - free line end 4-pole, D-coded 2.0 m

P/N

142M1D90020

EAN 4250184174967

2018-13-02

Technical Data

General Data

Fields of application

Industrial Ethernet

Design

Ethernet-Connection line

Shielding

shielded

Transmission technology

Copper

Cable Type

SF/FTP

Number of twisting elements

2

Twisting element

Pair

Wiring

Profinet

Color coding fiber/ wire(s)

yellow, white, orange, blue

Color

green

Dimensions

Dimension - Interface 1 (L x W x H)

52.30 x 15.00 x 15.00 mm

Dimension - Interface 1 (L x W x H)

2.059 x 0.591 x 0.591 in.

Cable length (m)

2.00 m

Labeling option

identification label carrier

Transmission characteristics

Category (ISO)

5e

Connections/interfaces

Connector technology interface 1

M12-plug

Coding interface 1

data systems technology tool

Number of positions/contacts interface 1

4

Termination data, stranded wire (min. - max.)

Conductor cross section, stranded wire

AWG 22/7

Conductor diameter, stranded wire (bare copper)

0.75 mm

Conductor diameter, stranded wire (bare copper)

0.03 in.

Cable sheath diameter (min. - max.)

Cable sheath diameter

6.50 mm

Cable sheath diameter

0.236 in.



Data sheet

Page 3/5

Connection cable M12 plug angled - free line end 4-pole, D-coded 2.0 m

P/N

142M1D90020

EAN 4250184174967

2018-13-02

Technical Data

Electrical characteristics

Current carrying capacity	max. 4 A
Through resistance	max. 5 mOhm
Insulation resistance	min. 100 MOhm

Mechanical characteristics

Life - Number of mating cycles	min. 100
Maximum operating bending radius	26 mm
Maximum operating bending radius	1.024 in.
Maximum installation load	52 mm
Maximum installation load	2.047 in.
Shielding braid coverage	85 %

Materials and material properties

Material - Conductor	Cu (copper)
Material - Conductor Insulation	Polyethylen
Material - Cable jacket	PUR
Material - Inner cable jacket	FRNC, with an aluminized film
Material - Body interface 1	Plastics
Material - Contact interface 1	CuZn (brass)
Material - Contact finish interface 1	Au (gold)
Material - Contact carriers interface 1	Plastics
Material - Union nut interface 1	CuZn (brass)
Material - Union nut finish interface 1	Ni (nickel)
Material - Pair shield	plastic film
Material - Pair shield finish	Al (Aluminium)
Material - Main shield	Cu (copper) braid
Material - Main shield finish	Sn (tin)
Flame retardancy	yes
Halogen free	yes
Oil resistance	yes
UV-resistance	yes



Data sheet

Page 4/5

Connection cable M12 plug angled - free line end 4-pole, D-coded 2.0 m

P/N

142M1D90020

EAN 4250184174967

2018-13-02

Technical Data

Environmental conditions

Temperature (min. - max.)	
Temperature - Operating °C	-30 - 90 °C
Temperature - Operating °F	-22 - 194 °F
Particulate ingress interface 1	IP6X when plugged in
Liquid ingress/immersion interface 1	IPX7 when plugged in
Pollution degree interface 1	3

Approvals

RoHS	compliant
------	-----------

The product meets the following standards

Connectors for electronic equipment	
circular connector	DIN EN 61076-2-101
Multi-element metallic cables used in analogue and digital communication and control	DIN EN 50288-2-1
Test for vertical flame propagation for a single insulated wire or cable	DIN EN 60332-1-2

Classifications

ETIM 5.0	EC002599
ETIM 6.0	EC002599

Packing details

Type of packaging	1 pc(s) / plastic bag
-------------------	-----------------------



P | Cabling

Data sheet

Connection cable M12 plug angled - free line end 4-pole, D-coded 2.0 m

Page 5/5

P/N


142M1D90020

EAN 4250184174967

2018-13-02

Illustrations

Dimensional drawing



Wiring

M12 plug

free cable end

