



DO NOT SCALE DRAWING

REVISION

A INITIAL DRAWING 25.01.18



Part Number	ØA	ØB	C
M2 - FANYWA - BG10	2.2 - 2.34	4.7 - 5.0	0.25 - 0.35
M2.5 - FANYWA - BG10	2.7 - 2.84	5.7 - 6.0	0.45 - 0.55
M3 - FANYWA - BG10	3.2 - 3.38	6.64 - 7.0	0.45 - 0.55
M4 - FANYWA - BG10	4.3 - 4.48	8.64 - 9.0	0.7 - 0.9
M5 - FANYWA - BG10	5.3 - 5.48	9.64 - 10.0	0.9 - 1.1
M6 - FANYWA - BG10	6.4 - 6.62	11.57 - 12.0	1.4 - 1.8

NOTES:



DESIGN RIGHT. TR FASTENINGS LTD, 2003  
 UNDER NO CIRCUMSTANCES MUST THIS  
 DRAWING BE COPIED OR DISCLOSED  
 WITHOUT FIRST OBTAINING WRITTEN  
 AUTHORITY.

UNLESS OTHERWISE SPECIFIED:  
 DIMENSIONS ARE IN MM (MILLIMETERS).  
 SURFACE FINISH:  
 TOLERANCES: DIN 125

	NAME	DATE
DRAWN	Darryl Wilson	25.01.18
CHK'D		
APPVD		

MATERIAL:  
 NYLON

HEAT TREATMENT:  
 N/A

FINISH:  
 NATURAL

TITLE:  
 Plain Nylon Washer

DRAWING NUMBER:  
 TR32FANYWA-BG10

A4

