

### Data Sheet

**Total Power:** 2 W  
**Input Voltage:** 5, 12, 24, 48 V  
**# of Outputs:** Single and Dual

### SPECIAL FEATURES

- Ultra compact DIP package (14 x 14 x 8.0 mm; 0.55 x 0.55 x 0.31 inches)
- Efficiency up to 87%
- I/O-isolation 1500 Vdc
- Wide 2:1 input range
- Operating temperature range -40 °C to +85 °C (with derating)
- Three year product warranty
- UL/cUL/IEC/EN 60950-1 Safety Approval, CE Mark

### SAFETY

- cUL/UL 60950-1 recognition
- CE Mark



### Electrical Specifications

Input	
Input range	4.5 - 10 Vdc; 9 - 18 Vdc; 18 - 36 Vdc; 36 - 75 Vdc
Efficiency	87% @ 12 Vo
Output	
Voltage tolerance	±1.5%
Line regulation	±0.2%
Load regulation	1.0%
Noise/ripple	70 mV
Overload protection	170% typ of Io max, foldback
Short circuit protection	Continuous, automatic recovery
Switching frequency	100 kHz
Isolation	
I/O isolation	I/O: 1500 Vdc
Insulation resistance	1000 Mohm
Insulation capacitance	100 pF


### Environmental Specifications

<b>Operating ambient temperature range</b>	-40 °C to +85 °C
<b>Storage temperature</b>	-50 °C to +125 °C
<b>Humidity</b>	5% to 95% non-condensing
<b>MTBF</b>	3.5 Mhrs calculated

## Ordering Information

Part Number	Input Voltage	Output Voltage	Output Current	Efficiency	Power
AYA00F05-L	4.5-10 Vdc	3.3 Vdc	0.4 A	79%	1.3 W
AYA00F12-L	9-18 Vdc	3.3 Vdc	0.4 A	80%	1.3 W
AYA00F24-L	18-36 Vdc	3.3 Vdc	0.4 A	80%	1.3 W
AYA00F48-L	36-75 Vdc	3.3 Vdc	0.4 A	79%	1.3 W
AYA00A05-L	4.5-10 Vdc	5 Vdc	0.4 A	81%	2 W
AYA00A12-L	9-18 Vdc	5 Vdc	0.4 A	83%	2 W
AYA00A24-L	18-36 Vdc	5 Vdc	0.4 A	83%	2 W
AYA00A48-L	36-75 Vdc	5 Vdc	0.4 A	82%	2 W
AYA00AA05-L	4.5-10 Vdc	± 5 Vdc	0.2 A	82%	2 W
AYA00AA12-L	9-18 Vdc	± 5 Vdc	0.2 A	84%	2 W
AYA00AA24-L	18-36 Vdc	± 5 Vdc	0.2 A	84%	2 W
AYA00AA48-L	36-75 Vdc	± 5 Vdc	0.2 A	82%	2 W
AYA00B05-L	4.5-10 Vdc	12 Vdc	0.167 A	85%	2 W
AYA00B12-L	9-18 Vdc	12 Vdc	0.167 A	87%	2 W
AYA00B24-L	18-36 Vdc	12 Vdc	0.167 A	87%	2 W
AYA00B48-L	36-75 Vdc	12 Vdc	0.167 A	86%	2 W
AYA00BB05-L	4.5-10 Vdc	± 12 Vdc	0.083 A	84%	2 W
AYA00BB12-L	9-18 Vdc	± 12 Vdc	0.083 A	86%	2 W
AYA00BB24-L	18-36 Vdc	± 12 Vdc	0.083 A	86%	2 W
AYA00BB48-L	36-75 Vdc	± 12 Vdc	0.083 A	85%	2 W
AYA00C05-L	4.5-10 Vdc	15 Vdc	0.134 A	85%	2 W
AYA00C12-L	9-18 Vdc	15 Vdc	0.134 A	87%	2 W
AYA00C24-L	18-36 Vdc	15 Vdc	0.134 A	87%	2 W
AYA00C48-L	36-75 Vdc	15 Vdc	0.134 A	86%	2 W
AYA00CC05-L	4.5-10 Vdc	± 15 Vdc	0.067 A	85%	2 W
AYA00CC12-L	9-18 Vdc	± 15 Vdc	0.067 A	87%	2 W
AYA00CC24-L	18-36 Vdc	± 15 Vdc	0.067 A	87%	2 W
AYA00CC48-L	36-75 Vdc	± 15 Vdc	0.067 A	85%	2 W

## Mechanical Dimensions



- All dimensions in mm (inches)
- Tolerance: X.X±0.5 (X.XX±0.02)  
X.XX±0.25 (X.XXX±0.01)
- Pin diameter  $\varnothing 0.5 \pm 0.05$  ( $0.02 \pm 0.002$ )

Pin Connections		
Pin	Single Output	Dual Output
1	-Vin	-Vin
4	+Vin	+Vin
5	+Vout	+Vout
6	No pin	Common
7	-Vout	-Vout

## WORLDWIDE OFFICES

### Americas

2900 S.Diablo Way  
Tempe, AZ 85282  
USA  
+1 888 412 7832

### Europe (UK)

Waterfront Business Park  
Merry Hill, Dudley  
West Midlands, DY5 1LX  
United Kingdom  
+44 (0) 1384 842 211

### Asia (HK)

14/F, Lu Plaza  
2 Wing Yip Street  
Kwun Tong, Kowloon  
Hong Kong  
+852 2176 3333

**ARTESYN**<sup>TM</sup>  
EMBEDDED TECHNOLOGIES

[www.artesyn.com](http://www.artesyn.com)

Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. © 2017 Artesyn Embedded Technologies, Inc. All rights reserved. For full legal terms and conditions, please visit [www.artesyn.com/legal](http://www.artesyn.com/legal).

For more information: [www.artesyn.com/power](http://www.artesyn.com/power)  
For support: [productsupport.ep@artesyn.com](mailto:productsupport.ep@artesyn.com)