

PREMIUM CARBON CONDUCTIVE GREASE

8481

Safety Data Sheet

Section 1: Identification

Product Identifier and Other Means of Identification

Product Name: Premium Carbon Conductive Grease

SDS Code: 8481

Related Part # 8481-1, 8481-2, 8481-3, 8481-80G, 8481-1P

Recommended Use and Restriction on Use

Use: Improves connections between electrical contacts without oil bleeding.

Uses Advised Against: Do not process in a manner the material to form mist or dust

Details of Manufacturer or Importer

Manufacturer

MG Chemicals
1210 Corporate Drive
Burlington, Ontario L7L 5R6
CANADA

MG Chemicals (Head Office)
9347-193 Street
Surrey, British Columbia V4N 4E7
CANADA

☎ +1-800-340-0772

FAX +1-800-340-0773

E-MAIL support@mgchemicals.com

WEB www.mgchemicals.com

☎ +1-905-331-1396

FAX +1-905-331-2682

E-MAIL info@mgchemicals.com

E-MAIL (Competent Person): sds@mgchemicals.com

Emergency Phone Number

For hazardous material incidents ONLY—leaks, spills, fires, exposures or accidents

USA or CANADA: Call CHEMTREC ☎: **+1-800-424-9300**

For emergencies involving dangerous goods; Collect 24/7

CANADA: Call CANUTEC ☎: **+1-613-996-6666** or ***666** on cellular phones

PREMIUM CARBON CONDUCTIVE GREASE
8481
Section 2: Hazard(s) Identification
Classification of Hazardous Chemical
GHS Categories

Criteria	Category	Signal Word	Pictograms
Hazardous to the Aquatic Environment Chronic	3	None	None

Note: The degree of severity is ranked within each hazard class from 1 (Highest Severity) to up to 5 (Lowest Severity), which is opposite to HMIS and NFPA conventions. Severity category rankings do not allow comparisons between classes.

Label Elements

Signal Word	<i>No signal word</i>
Pictograms	Hazard Statements
<i>No Symbol Mandated</i>	H412: Harmful to aquatic life with long lasting effects
Prevention	Precautionary Statements
P273	Avoid release to the environment.
Disposal	Precautionary Statements
P501	Dispose of contents/container in accordance to local/regional/international regulations.

Hazards Not Otherwise Classified

Other Criteria	Hazard Statements/Precautionary Statement	Signal Word	Pictograms
None	None	None	None

PREMIUM CARBON CONDUCTIVE GREASE
8481
Section 3: Composition/Information on Ingredients

CAS #	Chemical Name	% (weight)
non-hazardous ^{a)}	synthetic oil	82%
1333-86-4	carbon black	12%
12001-85-3	naphthenic acids, zinc salts	2%
112945-52-5	amorphous fumed silica	0.3%

a) Non-hazardous component under the U.S. OSHA HazCom 2012, the Canadian Controlled Product Regulations (SOR 88-66)

Section 4: First Aid Measures

<i>Exposure Condition</i>	<i>GHS Code/Symptoms/Precautionary Statements</i>
IF INHALED	P304 + P340
Immediate Symptoms	<i>none known</i>
Response	Remove person to fresh air and keep comfortable for breathing.
IF IN EYES	P305 + P351 + P338
Immediate Symptoms	<i>none known</i>
Response	Rinse cautiously with water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
IF ON SKIN	P302 + P352, P332 + P313
Immediate Symptoms	<i>none known</i>
Response	Wash with plenty of water. If skin irritation occurs: Get medical advice/attention.
IF SWALLOWED	P301 + P330 + P331
Immediate Symptoms	<i>none known</i>
Response	Rinse mouth. Do NOT induce vomiting.

PREMIUM CARBON CONDUCTIVE GREASE**8481****Section 5: Fire Fighting Measures**

Extinguishing Media	Use dry chemical, carbon dioxide, chemical foam, or water spray to extinguish. Do not use water jet.
Specific Hazards	Not flammable or combustible, but burns if involved in a fire. Avoid breathing combustion products.
Combustion Products	Produces carbon oxides (CO, CO ₂), oxide of sulfur, and smoke.
Fire-Fighter	Wear self-contained breathing apparatus and full fire-fighting turn-out gear.

Section 6: Accidental Release Measures

Personal Protection	Use personal protection recommended in Section 8.
Precautions for Response	Avoid breathing fumes. Remove or keep away all sources of extreme heat.
Environmental Precautions	Prevent spill from entering drains and waterways.
Containment Methods	Not applicable
Cleaning Methods	Collect paste in a sealable, solvent-resistant container. Sprinkle inert absorbent compound onto spill, then sweep into the container. Wipe up further residue with paper towel and place dirty towels in container. Wash spill area with soap and water to remove the last traces of residue.
Disposal Methods	Dispose of spill waste according to Section 13.

Section 7: Handling and Storage

Prevention	Avoid breathing fumes. Avoid release to the environment.
Handling	Wear protective gloves/eye protection. Wash hands thoroughly after handling.
Storage	No special storage instructions needed. RECOMMENDATION: Keep in a dry and clean area, away from incompatible substances.

PREMIUM CARBON CONDUCTIVE GREASE
8481
Section 8: Exposure Controls/Personal Protection
Substances with Occupational Exposure Limit Values

Chemical Name	Country	Long Term Exposure Limits (PEL)	Short Term Exposure Limits (STEL)
carbon black ^{a)}	ACGIH	3.5 mg/m ³	not established
	U.S.A. OSHA PEL	3.5 mg/m ³	not established
	Canada AB	3.5 mg/m ³	not established
	Canada BC	3 mg/m ³	not established
	Canada ON	3.5 mg/m ³	not established
	Canada QC	3.5 mg/m ³	not established

Note: Ingredients are listed in descending weight contribution order (from greatest to least). The ACGIH¹, OSHA (Table Z-1), and Canadian provinces exposure limits were consulted. Limits from the RTECS database² and from suppliers' SDS were also consulted. Short term exposure limits (STEL) are for 15 min and long term permissible exposure limits (PEL) for 8 h.

a) Respirable airborne particles

Engineering Controls
Ventilation

Keep airborne concentrations below the occupational exposure limits (OEL).

Because the carbon black is bound to the grease matrix, it does not present an airborne hazard under normal use. Ensure adequate ventilation if the product is mechanically misted or aerosolized.

Personal Protective Equipment
Eye protection

Wear appropriate protective eyeglasses or chemical safety goggles.

RECOMMENDATION: Ensure that glasses have side shields for lateral protection.

Skin Protection

For likely contacts, use of protective butyl rubber or other chemically resistant gloves.

Section continued on the next page

PREMIUM CARBON CONDUCTIVE GREASE**8481**

Respiratory Protection In the unlikely event of exposure to mist, wear oil resistant or oil proof particulate respirators or filter masks.

RECOMMENDATION: Consult your local safety supply store to ensure that your respirator has a NIOSH (U.S.) approved filter cartridges appropriate for the ingredients listed in Section 3. The respirator should be fitted to the employee by a professional. Ensure vapor cartridges are stored in sealed plastic bags when not being used.

General Hygiene Considerations

Wash hands thoroughly with water and soap after handling.

Section 9: Physical and Chemical Properties

Physical State	Liquid	Lower Flammability Limit	Not available
Appearance	Black, grease	Upper Flammability Limit	Not available
Odor	Odorless	Vapor Pressure @20 °C	Not available
Odor Threshold	Not applicable	Vapor Density	Not available
pH	Not available	Specific Gravity @25 °C	1.03
Freezing/Melting Point	Not available	Solubility in Water	slightly soluble
Boiling Point	Not available	Partition Coefficient	Not available
Flash Point ^{a)}	285 °C [545 °F]	Auto-ignition Temperature	Not available
Evaporation Rate	Not available	Decomposition Temperature	Not available
Flammability (solid, gas)	Not available	Viscosity @40 °C	610 000 cSt

a) Cleveland Open Cup

PREMIUM CARBON CONDUCTIVE GREASE
8481
Section 10: Stability and Reactivity

Reactivity	Not available
Chemical Stability	Chemically stable at normal temperatures and pressures
Conditions to Avoid	Ignition sources, open flames, excessive heat, and incompatible substances
Incompatibilities	Strong oxidizing agents
Polymerization	Will not occur
Decomposition	Will not decompose under normal conditions. For thermal decomposition, see combustion products in Section 5.

Section 11: Toxicological Information
Routes of Entry

Eye contact, Ingestion, Inhalation, and Skin contact

Eyes	May cause redness and mild irritation.
Skin	May cause mild skin irritation.
Inhalation	None expected under normal conditions. When heated to extreme temperatures, product fumes or combustion gases may result in toxic gas emissions.
Ingestion	No effects known
Chronic	No effects known

Acute Toxicity (Lethal Exposure Concentrations)

Chemical Name	LD50 oral	LD50 dermal	LC50 inhalation
carbon black	>15 g/kg Rat	>3 g/kg Rabbit	Not established
naphthenic acids, zinc salts	4 920 mg/kg Rat	>2 g/kg Rabbit	>11 600 mg/m ³ 4 h Rat
amorphous fumed silica	3 160 mg/kg Rat	≥2 000 mg/kg Rabbit ^{b)}	Not established

Note: Toxicity data from the RTECS² and ECHA database were consulted. The data from supplier (M)SDS were also consulted.

b) Value from supplier (M)SDS

Section continued on the next page

PREMIUM CARBON CONDUCTIVE GREASE**8481****Other Toxicological Effects**

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/irritation Based on available data, the classification criteria are not met.

Sensitization
(allergic reactions) Based on available data, the classification criteria are not met.

Carcinogenicity
(risk of cancer) The carbon black [1333-86-4] is possibly carcinogenic by airborne routes of exposures under WHMIS.

Because the carbon black is bound in the liquid mixture, it is not available as an airborne hazard (dust) under normal use.

Carbon Black [1333-86-4]

IARC Group 2B: Possibly carcinogenic to humans

ACGIH A4: Not classified as a human carcinogen

CA Prop 65: Listed as a carcinogen (airborne, as unbound particles of respirable size)

NTP: Not listed

Reproductive Toxicity
(risk to sex functions) Based on available data, the classification criteria are not met.

Teratogenicity
(risk of fetus malformation) Based on available data, the classification criteria are not met.

Mutagenicity
(risk of heritable genetic effects) Based on available data, the classification criteria are not met.

STOT-single exposure Based on available data, the classification criteria are not met.

STOT-repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Classification criteria are not met: the mixture does not contain Class 1 aspiration toxicant and its viscosity is $>20.5 \text{ mm}^2/\text{s}$ at $40 \text{ }^\circ\text{C}$

PREMIUM CARBON CONDUCTIVE GREASE**8481****Section 12: Ecological Information**

Ecological classifications are based on the IMDG/GHS criteria in conjunction with ecotoxicological data from our suppliers, the European Chemical Agency database (<http://echa.europa.eu>), and other reliable sources.

The synthetic oil is the predominant component and has very low environmental toxicity. The acute fish toxicity has a LL50 (Lethal Loading Levels) >100 mg/L. Similarly, its Daphnia magna acute toxicity is given as EL50 (Effective Load) >100 mg/L. And for the algae, it occurs at a EL50 > 100 mg/L.

The minor zinc naphthenate component has a LC50 96 h of 1.1 mg/L for *Oncorhynchus mykiss* (rainbow trout), an EC50 of 4.6 mg/L *Daphnia magna*, and EC50 0.48 mg/L algae.

Based on available data, carbon black is not classified as environmental hazards according to GHS criteria.

Acute Ecotoxicity

Category 3

Harmful to aquatic life.

Chronic Ecotoxicity

Category 3

Harmful to aquatic life with long lasting effects.

Biodegradability

Not readily biodegradable

Section 13: Disposal Information

Dispose of contents in accordance with all local, regional, national, and international regulations.

Section 14: Transport Information**Ground**

Refer to TDG regulations (Canadian Transportation of Dangerous Goods regulations) and **US DOT 49 CFR** (Parts 100 to 185) **Regulations.**

Not Regulated

Section continued on the next page

PREMIUM CARBON CONDUCTIVE GREASE

8481

Air

Refer to ICAO-IATA Dangerous Goods Regulations.

Not Regulated

Sea

Refer to IMDG Dangerous Goods Regulations.

Not Regulated

Section 15: Regulatory Information

Canada

Domestic Substance List (DSL) / Non-Domestic Substance Lists (NDSL)

All hazardous ingredients are listed on the DSL/NDSL.

Industry and Science Canada

MG Labels products intended for the workplace to conform to WHMIS labeling regulations. Product identification, net quantity declaration, minimum printing type size heights, and packaging of this product are in compliance.


USA

Other Classifications

HMIS® RATING

HEALTH:	0
FLAMMABILITY:	1
PHYSICAL HAZARD:	0
PERSONAL PROTECTION:	

NFPA® 704 CODES



Approximate HMIS and NFPA Risk Ratings Legend:

0 (Low or none); 1 (Slight); 2 (Moderate); 3 (Serious); 4 (Severe)

Section continued on the next page

PREMIUM CARBON CONDUCTIVE GREASE**8481****CAA** (Clean Air Act, USA)

This product does not contain any class 1 ozone depleting substances.

This product does not contain any class 2 ozone depleting substances.

This product does not contain products that are listed as hazardous air pollutants.

EPCRA (Emergency Planning and Right to Know Act, USA, 40 CFR 372.45)

This product contains 2% zinc compounds which is subject to the reporting requirements of section 313 Title III of the SARA of 1986 and 40 CFR part 372.

TSCA (Toxic Substances Control Act of 1976, USA)

All substances are TSCA listed.

California Proposition 65 (Chemicals known to cause cancer or reproductive toxicity, June 06, 2014 revision, USA).

This product contains carbon black, but it is bound and exposures during normal conditions of uses are below the Safe Harbor Threshold.

Europe**RoHS** (Restriction of Hazardous Substances Directive)

This product does not contain any lead, cadmium, mercury, hexavalent chromium, PBB's, or PBDE's, and complies with European RoHS regulations.

WEEE (Waste Electrical and Electronic Equipment Directive)

This product is not a piece of electrical or electronics equipment, and is therefore not governed by this regulation.

Section 16: Other Information

SDS Prepared by	Michel Hachey
Revision Date	15 November 2016
Date of Preparation	23 November 2015
Reason for Changes:	Change to California Proposition 65 statement in section 15.

Reference

1) ACGIH 2013 TLVs and BEIs: Based on the documentation of the threshold limit values for chemical substances and physical agents & biological exposure indices, American Conference of Governmental of Industrial Hygienist Cincinnati, OH (2013).

2) All toxicological data were checked against the RTECS (Registry of Toxic Effects of Chemical Substances®)

Section continued on the next page

PREMIUM CARBON CONDUCTIVE GREASE**8481****Abbreviations**

ACGIH	American Conference of Governmental Industrial Hygienists (USA)
EC50	Half maximal effective concentration
EL50	Half maximal effective loading
NOELR	No observable effect loading ratio
GHS	Globally Harmonized System of Classification of Labeling of Chemicals
LC50	Lethal Concentration 50%
LCLo	Lowest published lethal concentration
LD50	Lethal Dose 50%
OEL	Occupational Exposure Limit
PEL	Permissible Exposure Limit
STEL	Short-Term Exposure Limit
TCLo	Lowest published toxic concentration
TWA	Time Weighted Average
VOC	Volatile Organic Content

Technical Queries Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at www.mgchemicals.com.

Email: support@mgchemicals.com

Mailing Addresses *Manufacturing & Support*
1210 Corporate Drive
Burlington, Ontario, Canada
L7L 5R6

Head Office
9347-193rd Street
Surrey, British Columbia, Canada
V4N 4E7

Disclaimer This material safety data sheet is provided as an information resource only. *M.G. Chemicals, Ltd.* believes the information contained herein is accurate and compiled from reliable sources. It is the responsibility of the user to query and verify any information seeming suspect where doubt on the validity may exist. The buyer assumes all responsibility of using and handling the product in accordance with local, regional, national, and international regulations.