

SAFETY DATA SHEET

Epoxy Resin ER2219

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200

1. Identification

Product identifier

Product name Epoxy Resin ER2219

Product number ER2219, EER221935SL, EER2219B1K, ZE

Recommended use of the chemical and restrictions on use

Application Resin.

Uses advised against No specific uses advised against are identified.

Details of the supplier of the safety data sheet

Supplier

ELECTROLUBE. A division of HK WENTWORTH LTD
 HK WENTWORTH-AMERICA
 PO Box 126257
 Benbrook, Texas 76126
 USA
 info@hkw.us.com
 +1 888-501-9203

Emergency telephone number

Emergency telephone +1 202 464 2554 (USA only)
 +44 1235 239670

2. Hazard(s) identification

Classification of the substance or mixture

Physical hazards Not Classified

Health hazards Skin Irrit. 2 - H315 Eye Irrit. 2A - H319 Skin Sens. 1 - H317

Environmental hazards Aquatic Chronic 2 - H411

Label elements

Pictogram



Signal word

Warning

Hazard statements

H315 Causes skin irritation.
 H317 May cause an allergic skin reaction.
 H319 Causes serious eye irritation.
 H411 Toxic to aquatic life with long lasting effects.

Epoxy Resin ER2219

Precautionary statements	<p>P261 Avoid breathing vapor/ spray.</p> <p>P264 Wash contaminated skin thoroughly after handling.</p> <p>P272 Contaminated work clothing must not be allowed out of the workplace.</p> <p>P273 Avoid release to the environment.</p> <p>P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.</p> <p>P302+P352 If on skin: Wash with plenty of water.</p> <p>P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.</p> <p>P321 Specific treatment (see medical advice on this label).</p> <p>P332+P313 If skin irritation occurs: Get medical advice/ attention.</p> <p>P333+P313 If skin irritation or rash occurs: Get medical advice/ attention.</p> <p>P337+P313 If eye irritation persists: Get medical advice/ attention.</p> <p>P362+P364 Take off contaminated clothing and wash it before reuse.</p> <p>P391 Collect spillage.</p> <p>P501 Dispose of contents/ container in accordance with national regulations.</p>
---------------------------------	--

Contains	<p>Reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700) , 1,3-bis(2,3-epoxypropoxy)-2,2-dimethylpropane, formaldehyde, oligomeric reaction products with 1-chloro-2,3-epoxypropane and phenol, oxirane, mono[(C12-14-alkyloxy)methyl] derivs.</p>
-----------------	---

Other hazards

This product does not contain any substances classified as PBT or vPvB.

3. Composition/information on ingredients

Mixtures

Reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)	30-60%
CAS number: 25068-38-6	
Classification	
Skin Irrit. 2 - H315	
Eye Irrit. 2A - H319	
Skin Sens. 1 - H317	
Aquatic Chronic 2 - H411	
1,3-bis(2,3-epoxypropoxy)-2,2-dimethylpropane	10-30%
CAS number: 17557-23-2	
Classification	
Skin Irrit. 2 - H315	
Skin Sens. 1 - H317	
formaldehyde, oligomeric reaction products with 1-chloro-2,3-epoxypropane and phenol	<1%
CAS number: 9003-36-5	
Classification	
Skin Irrit. 2 - H315	
Skin Sens. 1 - H317	
Aquatic Chronic 2 - H411	

Epoxy Resin ER2219

oxirane, mono[(C12-14-alkyloxy)methyl] derivs. <1%
CAS number: 68609-97-2
Classification Skin Irrit. 2 - H315 Skin Sens. 1 - H317

The full text for all hazard statements is displayed in Section 16.

4. First-aid measures

Description of first aid measures

General information	Get medical attention immediately. Show this Safety Data Sheet to the medical personnel.
Inhalation	Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Place unconscious person on their side in the recovery position and ensure breathing can take place.
Ingestion	Rinse mouth thoroughly with water. Remove any dentures. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Place unconscious person on their side in the recovery position and ensure breathing can take place. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.
Skin Contact	It is important to remove the substance from the skin immediately. In the event of any sensitization symptoms developing, ensure further exposure is avoided. Remove contamination with soap and water or recognized skin cleansing agent. Get medical attention if symptoms are severe or persist after washing.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue. If it is suspected that volatile contaminants are still present around the affected person, first aid personnel should wear an appropriate respirator or self-contained breathing apparatus. Wash contaminated clothing thoroughly with water before removing it from the affected person, or wear gloves. It may be dangerous for first aid personnel to carry out mouth-to-mouth resuscitation.

Most important symptoms and effects, both acute and delayed

General information	See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	Prolonged inhalation of high concentrations may damage respiratory system.
Ingestion	May cause sensitization or allergic reactions in sensitive individuals. May cause irritation.
Skin contact	May cause skin sensitization or allergic reactions in sensitive individuals. Redness. Irritating to skin.
Eye contact	Irritating to eyes.

Indication of immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically. May cause sensitization or allergic reactions in sensitive individuals.
-----------------------------	--

Epoxy Resin ER2219

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

Specific hazards Containers can burst violently or explode when heated, due to excessive pressure build-up.

Hazardous combustion products Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

Advice for firefighters

Protective actions during firefighting Avoid breathing fire gases or vapors. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapors and protect men stopping the leak. Avoid discharge to the aquatic environment. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves will provide a basic level of protection for chemical incidents.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage. Ensure procedures and training for emergency decontamination and disposal are in place. Do not touch or walk into spilled material. Avoid contact with skin and eyes.

Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground. Avoid discharge to the aquatic environment. Large Spillages: Inform the relevant authorities if environmental pollution occurs (sewers, waterways, soil or air).

Methods and material for containment and cleaning up

Methods for cleaning up Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Approach the spillage from upwind. Small Spillages: If the product is soluble in water, dilute the spillage with water and mop it up. Alternatively, or if it is not water-soluble, absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. Large Spillages: If leakage cannot be stopped, evacuate area. Flush spilled material into an effluent treatment plant, or proceed as follows. Contain and absorb spillage with sand, earth or other non-combustible material. Place waste in labeled, sealed containers. Clean contaminated objects and areas thoroughly, observing environmental regulations. The contaminated absorbent may pose the same hazard as the spilled material. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dangerous for the environment. Do not empty into drains. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Epoxy Resin ER2219

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

7. Handling and storage

Precautions for safe handling

Usage precautions

Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimize spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Avoid discharge to the aquatic environment. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

Advice on general occupational hygiene

Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace.

Conditions for safe storage, including any incompatibilities

Storage precautions

Store away from incompatible materials (see Section 10). Store in accordance with local regulations. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage. Utilize retaining walls to prevent soil and water pollution in the event of spillage. The storage area floor should be leak-tight, jointless and not absorbent.

Storage class

Miscellaneous hazardous material storage.

Specific end uses(s)

Specific end use(s)

The identified uses for this product are detailed in Section 1.

8. Exposure Controls/personal protection

Amorphous Silica (CAS: 7631-86-9)

Immediate danger to life and health 3000 mg/m³

Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Personal, workplace environment or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Use process enclosures, local exhaust ventilation or other engineering controls as the primary means to minimize worker exposure. Personal protective equipment should only be used if worker exposure cannot be controlled adequately by the engineering control measures. Ensure control measures are regularly inspected and maintained. Ensure operatives are trained to minimize exposure.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with OSHA 1910.133. Wear tight-fitting, chemical splash goggles or face shield. If inhalation hazards exist, a full-face respirator may be required instead.

Epoxy Resin ER2219

Hand protection	Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with OSHA 1910.138 and be demonstrated to be impervious to the chemical and resist degradation. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.
Other skin and body protection	Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.
Hygiene measures	Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke. Preventive industrial medical examinations should be carried out. Warn cleaning personnel of any hazardous properties of the product.
Respiratory protection	Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Ensure all respiratory protective equipment is suitable for its intended use and is NIOSH approved. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with OSHA 1910.134. Full face mask respirators with replaceable filter cartridges should comply with OSHA 1910.134. Half mask and quarter mask respirators with replaceable filter cartridges should comply with OSHA 1910.134.
Environmental exposure controls	Keep container tightly sealed when not in use. Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

9. Physical and Chemical Properties

Information on basic physical and chemical properties

Appearance	Liquid.
Color	Black.
Odor	Not known.
Odor threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	Not available.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapor pressure	Not available.

Epoxy Resin ER2219

Vapor density	Not available.
Relative density	Not available.
Bulk density	1.16 kg/l
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	22,900 mPa s @ 23°C/73.4°F
Explosive properties	Not considered to be explosive.
Oxidizing properties	Does not meet the criteria for classification as oxidizing.

10. Stability and reactivity

Reactivity	See the other subsections of this section for further details.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	No potentially hazardous reactions known.
Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

11. Toxicological information

Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Irritating.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Respiratory sensitization

Respiratory sensitization Based on available data the classification criteria are not met.

Skin sensitization

Skin sensitization May cause skin sensitization or allergic reactions in sensitive individuals.

Epoxy Resin ER2219

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

Contains a substance which may be potentially carcinogenic. IARC Group 3 Not classifiable as to its carcinogenicity to humans.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development

Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

Prolonged inhalation of high concentrations may damage respiratory system.

Ingestion

May cause sensitization or allergic reactions in sensitive individuals. May cause irritation.

Skin Contact

May cause skin sensitization or allergic reactions in sensitive individuals. Redness. Irritating to skin.

Eye contact

Irritating to eyes.

Route of entry

Ingestion Inhalation Skin and/or eye contact

Target Organs

No specific target organs known.

Medical considerations

Skin disorders and allergies.

12. Ecological Information

Toxicity

Aquatic Chronic 2 - H411 Toxic to aquatic life with long lasting effects.

Persistence and degradability

Persistence and degradability The degradability of the product is not known.

Bioaccumulative potential

Bio-Accumulative Potential No data available on bioaccumulation.

Partition coefficient

Not available.

Mobility in soil

Mobility

No data available.

Other adverse effects

Other adverse effects

None known.

Epoxy Resin ER2219

13. Disposal considerations

Waste treatment methods

General information

The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods

Do not empty into drains. Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labeled with their contents. Incineration or landfill should only be considered when recycling is not feasible.

14. Transport information

General

For limited quantity packaging/limited load information, consult the relevant modal documentation using the data shown in this section.

UN Number

UN No. (TDG)	3082
UN No. (IMDG)	3082
UN No. (ICAO)	3082
UN No. (DOT)	ID8000

UN proper shipping name

Proper shipping name (TDG)	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (CONTAINS Reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700) , formaldehyde, oligomeric reaction products with 1-chloro-2,3-epoxypropane and phenol)
Proper shipping name (IMDG)	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (CONTAINS Reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700) , formaldehyde, oligomeric reaction products with 1-chloro-2,3-epoxypropane and phenol)
Proper shipping name (ICAO)	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (CONTAINS Reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700) , formaldehyde, oligomeric reaction products with 1-chloro-2,3-epoxypropane and phenol)
Proper shipping name (DOT)	CONSUMER COMMODITY

Transport hazard class(es)

DOT hazard class	9
DOT hazard label	9
TDG class	9
TDG label(s)	9
IMDG Class	9
ICAO class/division	9

Epoxy Resin ER2219

Transport labels



DOT transport labels



Packing group

TDG Packing Group III

IMDG packing group III

ICAO packing group III

Environmental hazards

Environmentally Hazardous Substance



Special precautions for user

Always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

EmS F-A, S-F

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

15. Regulatory information

US Federal Regulations

SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities

None of the ingredients are listed or exempt.

CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)

None of the ingredients are listed or exempt.

SARA Extremely Hazardous Substances EPCRA Reportable Quantities

None of the ingredients are listed or exempt.

SARA 313 Emission Reporting

None of the ingredients are listed or exempt.

CAA Accidental Release Prevention

None of the ingredients are listed or exempt.

FDA - Essential Chemical

None of the ingredients are listed or exempt.

FDA - Precursor Chemical

None of the ingredients are listed or exempt.

Epoxy Resin ER2219

SARA (311/312) Hazard Categories

None of the ingredients are listed or exempt.

OSHA Highly Hazardous Chemicals

None of the ingredients are listed or exempt.

US State Regulations

California Proposition 65 Carcinogens and Reproductive Toxins

The following ingredients are listed or exempt:

Amphorous Silica

Known to the State of California to cause cancer.

California Air Toxics "Hot Spots" (A-I)

The following ingredients are listed or exempt:

Amphorous Silica

California Air Toxics "Hot Spots" (A-II)

None of the ingredients are listed or exempt.

California Directors List of Hazardous Substances

The following ingredients are listed or exempt:

Amphorous Silica

Massachusetts "Right To Know" List

The following ingredients are listed or exempt:

Amphorous Silica

Rhode Island "Right To Know" List

None of the ingredients are listed or exempt.

Minnesota "Right To Know" List

The following ingredients are listed or exempt:

Amphorous Silica

New Jersey "Right To Know" List

None of the ingredients are listed or exempt.

Pennsylvania "Right To Know" List

The following ingredients are listed or exempt:

Amphorous Silica

Inventories

US - TSCA

The following ingredients are listed or exempt:

Reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)

1,3-bis(2,3-epoxypropoxy)-2,2-dimethylpropane

oxirane, mono[(C12-14-alkyloxy)methyl] derivs.

formaldehyde, oligomeric reaction products with 1-chloro-2,3-epoxypropane and phenol

Amphorous Silica

US - TSCA 12(b) Export Notification

None of the ingredients are listed or exempt.

Epoxy Resin ER2219

16. Other information

Classification abbreviations and acronyms	Eye Irrit. = Eye irritation Skin Irrit. = Skin irritation Skin Sens. = Skin sensitisation Aquatic Chronic = Hazardous to the aquatic environment (chronic)
Training advice	Read and follow manufacturer's recommendations. Only trained personnel should use this material.
Issued by	Emily Kirk
Revision date	9/26/2017
Revision	0
SDS No.	2159
Hazard statements in full	H315 Causes skin irritation. H317 May cause an allergic skin reaction. H319 Causes serious eye irritation. H411 Toxic to aquatic life with long lasting effects.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.