Industrial RS-232 to RS-422/485 Converter

485DRCi





PRODUCT FEATURES

- Data rates up to 115.2 kbps
- Three-way 2,000V optical isolation (input, output, power)
- Wide (-40 to +80 °C) operating temperature
- UL Class 1/Division 2
- Modbus ASCII/RTU, Allen-Bradley® DH-485 compatible
- 10–48 VDC input power range

Model 485DRCi industrial-grade isolated serial converter changes RS-232 signals to RS-422 for increased range, or to RS-485 for increased range plus multi-drop capability.

Designed for rugged industrial use, the 485DRCi is UL approved and certified for operation in Class 1/Division 2 environments and also offers 2,000V 3-way optical isolation on input, output, and power lines. In addition to optical isolation, the unit has surge suppression on the RS-422/485 lines. This DIN rail mountable converter optically isolates and converts unbalanced, full or half-duplex, RS-232 signals to balanced RS-422/485 signals at baud rates up to 115.2 kbps. Configuration is made via a 12-position DIP switch on the bottom of the converter.

Featuring Automatic Send Data Control circuitry, the converter does not require special software control of handshake signals in RS-485 mode. Removable terminal blocks for power and RS-422/485 signals make wiring easy. It is powered by a supply voltage of 10 to 48 VDC which is isolated from all data and signal ground lines. The 485DRCi may be suitable for use in Modbus and Allen-Bradley® DH-485 applications.

IN THE FIELD

Resolving Electrical Substation Data Glitches

Industry: Energy & Natural Resources
Utilities
Product: Optically Isolated Converter

ORDERING INFORMATION

MODEL NUMBER	RS-232 CONNECTOR	RS-422/485 CONNECTOR	ISOLATION
485DRCi	DB9 Female (DCE)	Removable Terminal Block	2,000 V

ACCESSORIES

MDR-20-24 - DIN rail mount power supply 24VDC, 1.0 A output power

EK-CLIP-MPC - Replacement DIN Rail Clip

TBKT1 - Replacement Terminal Block, 2 position 5.08mm

TBKT2 - Replacement Terminal Block, 5 position 5.08mm

31D1-28100 - Null Modem Adapter (Allen-Bradley® applications)

Automatic Send Data Control Explained

As operating systems become more complex, it is increasingly difficult to control an RS-485 driver with standard software and the RTS line. This is especially true in Windows and multi-tasking operating systems. With B+B SmartWorx' Automatic Send Data Control circuit, driver control is in the converter hardware, so you do not have to work with software at all

The circuit monitors data flow and enables the driver during transmission and automatically disables it when no data is being sent. There is no need to rework software or install new drivers. Most B+B SmartWorx RS-232 to RS-485 converters and RS-485 serial cards include Automatic Send Data Control.

Allen-Bradley® 1761-NET-AIC

The 485DRCi can be used as a replacement for the Allen-Bradley® Advanced Interface Converter (AIC+) in some applications. The 31D1-28100 null modem adapter accessory is required for these applications. Contact B+B SmartWorx Technical Support for assistance regarding your specific installation needs. A White Paper is also available at the B+B SmartWorx online technical library.

Industrial RS-232 to RS-422/485 Converter

485DRCi



SPECIFICATIONS

SPECIFICATIONS		
SERIAL TECHNOLOGY		
Data Rate	1.2 to 115.2 kbps	
RS-232		
Connector	DB9 female (DCE)	
Signals	TD, RD, GND	
RS-422/485		
Connector	Removable terminal block, 28 to 14 AWG	
RS-485, 2-wire	Data A(-), Data B(+), GND	
RS-422/485, 4-wire	TDA(-), TDB(+), RDA (-), RDB(+), GND	
ISOLATION		
Rating	2,000 V	
Lines Protected	3-way (input, output, power lines)	
Method	Optical	
SURGE SUPPRESSION		
Lines Protected	Data lines	
Rating	600W peak power dissipation	
Clamping/Response Time	< 1 pico-second	
INDUSTRIAL BUS		
Modbus	ASCII/RTU	
DH-485	Allen-Bradley® Data Highway 485 (DH-485)	
POWER		
Connector	Removable terminal block, 28 to 14 AWG	
Voltage	10-48 VDC	
Consumption	960 mW	
Source	External	
MECHANICAL		
LED Indicators	Transmit, Receive, and Power	
Dimensions	11.4 x 3.3 x 12.4 cm (4.5 x 1.3 x 4.9 in)	
Enclosure	35mm DIN mount, plastic, IP30	
Weight	204.12 g (0.45 lb)	

ENVIRONMENTAL			
Operating Temperature	-40 to +80 °C (-40 to +176 °F)		
Storage Temperature	-40 to +85 °C (-40 to +185 °F)		
Operating Humidity	0 to 95% non-condensing		
MTBF	254617 hours		
MTBF Calculation Method	Parts Count Reliability Prediction		
CLASS 1/DIVISION 2 WIRING			
Туре	Solid copper only		
Size	28 to 14 AWG		
Temperature	105 °C (221 °F) minimum		
Terminal Torque	0.5 Nm (Newton-meters)		
APPROVALS / CERTIFICATIONS - 485DRCI			
cUL 508, File Number: E222870 (C1 D2 E245458)			
FCC Part 15, EN 55022: 20	110 + AC Class B Emissions		
CE			
EN 61000-6-1: Generic Standards for Residential, Commercial and Light-Indus			
Enviro	nments		
EN 61000-4-2: Electro-			
	EN 61000-4-3: +A2 Radiated Field Immunity		
	EN 61000-4-4: Electrical Fast Transients-Burst Immunity		
EN 61000-4-6: Conduc	cted Immunity		



