Industrial Isolated Converter

Model 485LDRC9



www.advantech-bb.com



PRODUCT FEATURES

- Extend data up to 1.2 km (4,000 ft.)
- 2 kV optical isolation on input/output
- Wide operating temperature (-40 to +80 °C)
- 115.2 kbps data rate
- Modbus compatible
- UL Recognized, NEMA TS2
- Automatic Send Data Control

The 485LDRC9 is an optically isolated RS-232 to RS-422/485 converter. RS-232 signals interface through a DB9 female connector or a terminal block. RS-422/485 signals and power inputs connect to the terminal block. Terminal blocks are arranged to allow easy wiring inside a control panel.

Built-in Automatic Send Data Control circuitry allows quick set-up and eliminates the need for external software drivers to control handshake signals. The converter operates on externally sourced 10-30 VDC power.

Optically isolated data lines (2,000 V on input/output) with 500W surge suppression ensure that connected equipment is protected even in the harshest environments. DIN rail mount design snaps on standard 35mm rail and a small form factor fits neatly into tight cabinets.

The 485LDRC9 is ideal for critical industrial communications, factory automation, in-cabinet conversion, warehouse automation, security, and many other applications.

ORDERING INFORMATION

MODEL NUMBER	RS-232 CONNECTOR	RS-422/485 CONNECTOR
485LDRC9	DB9 Female or Terminal Block	Terminal Blocks

ACCESSORIES

ODEOLEIO ATIONIO

MDR-20-24 - PS, DIN, SLIM, PLASTIC, 24W, 24V

9PAMF6 - 6 ft. (1.8 m) 232 DB9 male to DB9 female serial cable

SPECIFICATIONS		
ERIAL TECHNOLOGY		
Data Rate	115.2 kbps	
RS-232 - 2 options		
Option 1: Connector	DB9 Female (DCE)	
Option 1: Signals	TD, RD, GND	
Option 2: Connector	Terminal block	
Option 2: Signals	TD, RD, GND	
RS-422		
Connector	Terminal block	
Signals	TDA(-), TDB(+), RDA(-), RDB(+), GND	
Termination	120 (switchable)	
RS-485		
Connector	Terminal block	
Signals	TDA(-), TDB(+), RDA(-), RDB(+), GND	
Modes	2-wire and 4-wire	
Termination	120 Ohm (switchable)	
SOLATION		
ines Protected	Data lines	
Method	Optical	
Rating	2,000 V	
SURGE SUPPRESSION		
ines Protected	Data lines	
Method	TVS	
Rating	7.5V bi-directional avalache breakdown device 500W peak power dissipation	
Response Time	< 1 pico-second	
NDUSTRIAL BUS		
Modbus	ASCII/RTU	

All product specifications are subject to change without notice. 485LDRC9_3316ds



Industrial Isolated Converter

Model 485LDRC9



SPECIFICATIONS - CONTINUED		
POWER		
Connector	Terminal block	
Voltage	10-30 VDC	
Consumption	0.5 W	
Source	External powering required	
TERMINAL BLOCKS		
Wire Size	24 to 14 AWG	
Torque	4 kfg-cm	
LED INDICATORS		
Power (RED)	On when power applied	
TD (RED)	Flashes when RS-422/485 data is transmitted	
RD (RED)	Flashes when RS-422/485 data is received	
ENCLOSURE		
Material	Plastic	
IP Rating	20	
Dimensions	2.5 x 7.9 x 9.5 cm (1.0 x 3.1 x 3.7 in)	
Mounting	35 mm DIN rail (panel mount adapter available)	

ENVIRONMENTAL		
Operating Temperature	-40 to +80 °C (-40 to +176 °F)	
Storage Temperature	-40 to +85 °C (-40 to +185 °F)	
Operating Humidity	0 to 95% non-condensing	
MTBF, 485LDRC9	257448 hours	
MTBF Calculation Method	MIL 217F Parts Count Reliability Prediction	
APPROVALS / CERTIFICATIONS - 485LDRC9		
cULus Recognized, File Number: E222870, NEMA TS2		
2004/108/EC	Electromagnetic Compatibility Directive	
2011/65/EU	Reduction of Hazardous Sustances Directive	
EN 55022: +AC	Information technology equipment - Class A RF Emissions	
EN 55024	Information technology equipment - Immunity (Light-industrial Environments)	
EN 61000-4-2	ESD Immunity	
EN 61000-4-3: +A2	Radiated Field Immunity (RFI)	
EN 61000-4-4	EFT/Burst Immunity	
EN 61000-4-5	RF Conducted Immunity	

MECHANICAL DIAGRAM

