

97 53 14

Self-Adjusting Crimping Pliers for End Sleeves (ferrules) with lateral access



PAT. PEND.



- Narrow handle width and improved ergonomics
- For crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of end sleeves (ferrules) required
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Chrome vanadium electric steel in special quality, oil-hardened
- Expanded capacity of hexagonal crimping up to 10 mm²
- Hexagonal compression for confined connection dimensions
- Suitable in particular for all twin end sleeves (ferrules) up to 2 x 4 mm² or 2 x AWG 10

The small crimping pliers for end sleeves (ferrules) with two major advantages for the user: - Automatic adjustment to the end sleeves used: This makes work easier for the professional and offers reliable and fast crimping. - Expanded range of applications

Article No.	97 53 14
EAN	4003773041474
Pliers	burnished
Handles	with multi-component grips
Applications	End Sleeves (ferrules)
Capacity in square millimetres mm ²	0,08 - 10,0
Number of crimping positions	1
AWG	28 - 7
Length mm	180
Net weight g	404

technical change and errors excepted



Spare Parts

Article No.	EAN	
97 59 30	4003773053965	Extension spring for 97 53 4/5/8/9/14
97 59 31	4003773053972	Extension spring for 97 53 4/5/8/9/14
97 59 32	4003773053989	Circlips for model 97 53 for 97 53 xx