

OMNI-BEAM

Q45

UPGRADABLE
Photoelectric Sensor

Q45 The sensor you'll use today. The sensor you must have tomorrow.

A basic low-cost sensor. The standard Q45 is a basic on-off sensor available at a very low price. But even in its most basic form, the Q45 makes your job easier with a host of advanced standard features including three LED's for "power", "signal" and "output" indication, plus patented diagnostics that alert you of output overloads, output short circuits and marginal sensing conditions. The Q45 even measures exact signal strength with Banner's exclusive AID™ system, so you'll be better informed on how your sensors are performing.

An advanced, full-featured sensor. Because of its unique, upgradable design, the Q45 can instantly become the most advanced photoelectric sensor you can buy. Simply raise the unit's built-in, hinged cover, and insert circuit board modules for advanced functions including timers, logic, bus systems and Banner's patented, 7-segment, LED bargraph display of received signal strength. And you can also add any other functions you need to meet your specific requirements.




A sensor compatible with every fieldbus. Specify the Q45, and you can stop worrying about whether the photoelectrics you buy today will be compatible with the fieldbus you need tomorrow. And you don't need to feel pressured by the fieldbus suppliers to specify their sensors and their bus. With the Q45, you can instantly upgrade it, at any time, to any sensor/actuator bus, including DeviceNet™, SDS™, Seriplex™, CAN, ASI, PROFIBUS™ and others. You're not boxed in.

A sensor compatible with the future. Because of its patented design, the Q45 is the only photoelectric sensor with an eye on the future. As new technologies are available, the Q45 will be able to accommodate them. New circuit board modules will continually be developed to meet your sensing needs. To meet your unique control requirements, custom circuit board modules can also be developed for your special applications. This makes the Q45 the best sensor investment you can make.



Q45 A sensor so advanced, it will accommodate technologies yet to be invented.



A board for every function you need, today and tomorrow. Circuit board modules instantly plug in for delay and one-shot timers and numerous fieldbuses including DeviceNet™, SDS™ and Seriplex™ and others.

Advanced diagnostics display. Banner's patented, 7-segment, LED bargraph display of received signal strength continually tells you how your sensor is performing, making your sensitivity and alignment adjustments faster and more precise. Banner's advanced, diagnostic bargraph display can be purchased separately or combined on the same module with logic functions.

A slot for the future. Rapidly changing control technologies can be easily accommodated in the Q45 allowing an instant upgrade in performance by simply installing the latest circuit board module in the Q45's patented expansion slot. Custom modules can also be developed for your special requirements.

Patented diagnostic LED's, standard.

- Raised LED's indicate "power", "signal" and "output" operation.
- "Power" indicator flashes in the event of an output overload or output short circuit.
- "Signal" LED pulses at a rate proportional to the strength of the received light signal, making setup and maintenance easier. Operator is immediately alerted of a weakened signal due to operational or environmental factors.

Electrical interfaces.

- 0-30V dc sensors have both NPN (sinking) and PNP (sourcing) solid-state outputs.
- NAMUR intrinsically-safe DC models for potentially-explosive environments.
- 90-250V ac sensors have protected solid state relay output or economical SPDT electromechanical relay output for high switching capacity.

Hinged VISI-DOME™ Cover.

Transparent, hinged Lexan® cover opens to adjust sensitivity and logic, and to insert circuit board modules. Raised dome makes LED's visible from all sides. Cover is O-ring sealed allowing the unit to be rated NEMA 6P (IEC IP67), withstanding washdowns to 1200 psi.

Q45 Down to earth features that save you money on the factory floor.



All sensing modes. Choose from five sensing modes including:

- Opposed (beam break) mode for long ranges up to 200 feet or heavy contamination.
- Regular or polarized retroreflective mode for medium ranges up to 30 feet using a retroreflector.
- Laser retroreflective for ranges up to 150 feet.
- Short or long-range diffuse (proximity) mode for ranges to 18 inches or 6 feet.
- Convergent mode for precise sensing distances of 1.5 or 4 inches.
- Fiber optic mode for use with glass or plastic fibers.

Prewired or “plug and play” quick disconnects. Q45

sensors are available with 6 1/2 or 30 foot attached cable or easy to install, 4-pin quick disconnect (QD) connector. QD connectors save time in installation and wiring, eliminating wire terminations and wiring errors. Mating cables are available in straight or right angle designs in mini, euro and micro styles.

Easier setup, alignment and monitoring. Advanced features are standard on all Q45 sensors. Patented AID™ system gives the operator a constant visual indication of received signal strength during installation and operation. Operator is alerted immediately of a weakened signal due to operational or environmental factors. Three, raised LED's give the following indications:

- Power On
- Output Energized
- Signal Received
- Signal Strength
- Output Overload
- Output Short Circuit

Flexible, modular timing functions.

Timing modules can be added at any time and four simple switches on the module program the output logic function, the timing range and the output state. Accurate timing adjustments are assured by precise 15-turn clutched potentiometer. Timing functions include:

- On-delay
- Off-delay
- On/Off delay
- One-shot
- Delayed One-shot



Output Protection. Q45 sensors offer complete protection against many common electrical problems including the following conditions:

- False Pulse on Powerup
- Inductive Load Transients
- Polarity Reversal
- Output Overload
- Short Circuited Output



Q45 A sensor that meets your specific application requirements.

Glass and plastic fiber optics.

Banner has the widest range of fiber optics available, and they can all be used with the Q45. Reach places inaccessible to conventional sensors, withstand high temperatures, corrosive materials, extreme moisture, high vibration, and electrical noise. Inexpensive plastic fibers can be easily cut to length during installation, and are extremely flexible, allowing use for applications requiring articulated or reciprocating motion.

Rugged, NEMA 6P environmental protection. Q45 sensors feature rugged VALOX® thermoplastic polyester housings and O-ring sealed Lexan® top covers to withstand severe



environments including heavy washdown exceeding 1200 psi pressure. Unit is rated NEMA 6P and IEC IP67.



NAMUR intrinsically safe models.

Q45 NAMUR sensors are ideal for potentially explosive environments. These special sensor models meet DIN 19 234 safety requirements, and are available in all sensing modes. They are designed to be used with approved switching amplifiers with intrinsically-safe input circuits, and can eliminate the need for extremely heavy, explosion-proof enclosures.



Long range, ultra-precise laser sensors. Special Q45 sensors with Class II laser diode combine the easy alignment of a visible-light sensor with the extremely long-range and very narrow, precise sensing beam of a laser light source. Now you can sense very small objects at long range with complete precision.

Flexible mounting options. A wide variety of mounting options for the Q45 provide the best access to your applications.

- Through hole mounting uses the Q45's threaded base and mounting nuts.
- Swivel mount allows positioning the sensor at any angle.
- Split clamp bracket mounts flat without swivel.
- Angled bracket has curved mounting slots for versatility in mounting and orientation.



Q45 Opposed Mode Sensors




OPPOSED MODE ■ DC ■ NAMUR ■ AC

Sensor Model	Function	Termination: Cable or quick disconnect (QD)	Supply Voltage	Receiver Output				Emitter Beam	Sensing Range										
				Type	Rating	Response	Repeatability												
Q456E Q456EQ Q456EQ5 Q45BB6R Q45BB6RQ Q45BB6RQ5	Emitter Emitter Emitter Receiver Receiver Receiver	4-wire 6-ft cable [†] 4-pin mini QD 4-pin euro QD 4-wire 6-ft cable [†] 4-pin mini QD 4-pin euro QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.25 ms	Infrared LED 880nm	200 feet (60 m)										
*Q45X6EQ *Q45XB6RQ	Emitter Receiver	5-pin mini QD 5-pin mini QD																	
Q459E Q459EQ Q45AD9R Q45AD9RQ	Emitter Emitter Receiver Receiver	2-wire 6-ft cable [†] 4-pin euro QD 2-wire 6-ft cable [†] 4-pin euro QD								5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	2 ms	0.25 ms	Infrared LED 880nm	20 feet (6 m)			
Q452E Q452EQ Q452EQ1 Q45VR2R Q45VR2RQ Q45BW22R Q45BW22RQ Q45BW22RQ1	Emitter Emitter Emitter Receiver Receiver Receiver Receiver Receiver	2-wire 6-ft cable [†] 3-pin mini QD 4-pin micro QD 5-wire 6-ft cable [†] 5-pin mini QD 3-wire 6-ft cable [†] 3-pin mini QD 4-pin micro QD								90 to 250V ac	SPDT e/m relay	5 A max.	15 ms	0.25 ms	Infrared LED 880nm	200 feet (60 m)			
																	SPST solid-state relay	300 mA max.	2 ms



*NOTE: Q45X models may be used on sensor bus networks with addition of an optional plug-in expansion card. †NOTE: 30-foot cables are available.

Q45 Expansion Cards



Card Model	Function	Card Model	Sensor bus protocol
45LM5	Delay logic: on-delay, off-delay, or on/off delay	45AS1	ASI
45LM8	Pulse logic: one-shot or delayed one-shot	45DN1	DeviceNet™
45LM5D	Delay logic, plus signal strength display	45SD1	SDS™
45LM8D	Pulse logic, plus signal strength display	45SP1	Seriplex®
45LMD	Signal strength display, only (no timing function)		

Q45 Retroreflective Mode Sensors



Sensor Model	Termination: Cable or quick disconnect (QD)	Supply Voltage	Output				Beam	Sensing Range					
			Type	Rating	Response	Repeatability							
Q45BB6LL Q45BB6LLQ	5-wire 6-ft cable † 5-pin mini QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.5 ms	Visible red laser 670nm	9 in to 150 ft. (0,2 to 45m) with 3" dia. reflector					
Q45BB6LV Q45BB6LVQ Q45BB6LVQ5 *Q45XB6LVQ	4-wire 6-ft cable † 4-pin mini QD 4-pin euro QD 5-pin mini QD							Visible red LED 680nm	3 in to 30 ft. (0,08 to 9m) with 3" dia. reflector				
Q45AD9LV Q45AD9LVQ	2-wire 6-ft cable † 4-pin euro QD						5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	5 ms	0.5 ms	Visible red LED 680nm	3 in to 30 ft. (0,08 to 9m) with 3" dia. reflector
Q45VR2LV Q45VR2LVQ Q45BW22LV Q45BW22LVQ Q45BW22LVQ1	5-wire 6-ft cable † 5-pin mini QD 3-wire 6-ft cable † 3-pin mini QD 4-pin micro QD						90 to 250V ac	SPDT e/m relay	5 A max.	15 ms	0.5 ms	Visible red LED 680nm	3 in. to 30 ft. (0,08 to 9m) with 3" dia. reflector
								SPST solid-state relay	300 mA max.	2 ms			



POLARIZED RETROREFLECTIVE MODE

■ DC ■ NAMUR ■ AC

Sensor Model	Termination: Cable or quick disconnect (QD)	Supply Voltage	Output				Beam	Sensing Range					
			Type	Rating	Response	Repeatability							
Q45BB6LLP Q45BB6LLPQ	5-wire 6-ft cable † 5-pin mini QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.5 ms	Visible red laser 670nm	9 in to 100 ft. (0,2 to 30m) with 3" dia. reflector					
Q45BB6LP Q45BB6LPQ Q45BB6LPQ5 *Q45XB6LPQ	4-wire 6-ft cable † 4-pin mini QD 4-pin euro QD 5-pin mini QD							Visible red LED 680nm	6 in to 20 ft. (0,15 to 6m) with 3" dia. reflector				
Q45AD9LP Q45AD9LPQ	2-wire 6-ft cable † 4-pin euro QD						5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	5 ms	0.5 ms	Visible red LED 680nm	6 in to 20 ft. (0,15 to 6m) with 3" dia. reflector
Q45VR2LP Q45VR2LPQ Q45BW22LP Q45BW22LPQ Q45BW22LPQ1	5-wire 6-ft cable † 5-pin mini QD 3-wire 6-ft cable † 3-pin mini QD 4-pin micro QD						90 to 250V ac	SPDT e/m relay	5 A max.	15 ms	0.5 ms	Visible red LED 680nm	6 in. to 20 ft. (0,15 to 6m) with 3" dia. reflector
								SPST solid-state relay	300 mA max.	2 ms			

*NOTE: Q45X models may be used on sensor bus networks with addition of an optional plug-in expansion card. †NOTE: 30-foot cables are available.

Q45 Diffuse Mode Sensors



SHORT-RANGE DIFFUSE (Proximity) MODE

DC NAMUR AC

Sensor Model	Termination: Cable or quick disconnect (QD)	Supply Voltage	Output				Beam	Sensing Range
			Type	Rating	Response	Repeatability		
Q45BB6D Q45BB6DQ Q45BB6DQ5 *Q45XB6DQ	4-wire 6-ft cable † 4-pin mini QD 4-pin euro QD 5-pin mini QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.5 ms	Infrared LED 880nm	18 in. (45 cm) using 90% reflectance test card
Q45AD9D Q45AD9DQ	2-wire 6-ft cable † 4-pin euro QD	5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	5 ms	0.5 ms	Infrared LED 880nm	12 in. (30 cm) using 90% reflectance test card
Q45VR2D Q45VR2DQ Q45BW22D Q45BW22DQ Q45BW22DQ1	5-wire 6-ft cable † 5-pin mini QD 3-wire 6-ft cable † 3-pin mini QD 4-pin micro QD	90 to 250V ac	SPDT e/m relay SPST solid-state relay	5 A max. 300 mA max.	15 ms 2 ms	0.5 ms	Infrared LED 880nm	18 in. (45 cm) using 90% reflectance test card



LONG-RANGE DIFFUSE (Proximity) MODE

DC NAMUR AC

Sensor Model	Termination: Cable or quick disconnect (QD)	Supply Voltage	Output				Beam	Sensing Range
			Type	Rating	Response	Repeatability		
Q45BB6DL Q45BB6DLQ Q45BB6DLQ5 *Q45XB6DLQ	4-wire 6-ft cable † 4-pin mini QD 4-pin euro QD 5-pin mini QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.5 ms	Infrared LED 880nm	6 ft. (1.8m) using 90% reflectance test card
Q45AD9DL Q45AD9DLQ	2-wire 6-ft cable † 4-pin euro QD	5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	5 ms	0.5 ms	Infrared LED 880nm	42 in. (107 cm) using 90% reflectance test card
Q45VR2DL Q45VR2DLQ Q45BW22DL Q45BW22DLQ Q45BW22DLQ1	5-wire 6-ft cable † 5-pin mini QD 3-wire 6-ft cable † 3-pin mini QD 4-pin micro QD	90 to 250V ac	SPDT e/m relay SPST solid-state relay	5 A max. 300 mA max.	15 ms 2 ms	0.5 ms	Infrared LED 880nm	6 ft. (1.8m) using 90% reflectance test card

*NOTE: Q45X models may be used on data bus networks with addition of an optional plug-in expansion card. †NOTE: 30-foot cables are available.

Q45 Convergent Mode Sensors



CONVERGENT BEAM MODE: 1.5-inch focus

■ DC ■ NAMUR ■ AC

Sensor Model	Termination: Cable or quick disconnect (QD)	Supply Voltage	Output				Beam	Sensing Range
			Type	Rating	Response	Repeatability		
Q45BB6CV Q45BB6CVQ Q45BB6CVQ5 *Q45XB6CVQ	4-wire 6-ft cable† 4-pin mini QD 4-pin euro QD 5-pin mini QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.5 ms	Visible red LED 680nm	Peak excess gain at 1.5 inches (38 mm)
Q45AD9CV Q45AD9CVQ	2-wire 6-ft cable† 4-pin euro QD	5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	5 ms	0.5 ms	Visible red LED 680nm	Peak excess gain at 1.5 inches (38 mm)
Q45VR2CV Q45VR2CVQ Q45BW22CV Q45BW22CVQ Q45BW22CVQ1	5-wire 6-ft cable† 5-pin mini QD 3-wire 6-ft cable† 3-pin mini QD 4-pin micro QD	90 to 250V ac	SPDT e/m relay SPST solid-state relay	5 A max. 300 mA max.	15 ms 2 ms	0.5 ms	Visible red LED 680nm	Peak excess gain at 1.5 inches (38 mm)





CONVERGENT BEAM MODE: 4-inch focus

■ DC ■ NAMUR ■ AC

Sensor Model	Termination: Cable or quick disconnect (QD)	Supply Voltage	Output				Beam	Sensing Range
			Type	Rating	Response	Repeatability		
Q45BB6CV4 Q45BB6CV4Q Q45BB6CV4Q5 *Q45XB6CV4Q	4-wire 6-ft cable† 4-pin mini QD 4-pin euro QD 5-pin mini QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.5 ms	Visible red LED 680nm	Peak excess gain at 4 inches (100 mm)
Q45AD9CV4 Q45AD9CV4Q	2-wire 6-ft cable† 4-pin euro QD	5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	5 ms	0.5 ms	Visible red LED 680nm	Peak excess gain at 4 inches (100 mm)
Q45VR2CV4 Q45VR2CV4Q Q45BW22CV4 Q45BW22CV4Q Q45BW22CV4Q1	5-wire 6-ft cable† 5-pin mini QD 3-wire 6-ft cable† 3-pin mini QD 4-pin micro QD	90 to 250V ac	SPDT e/m relay SPST solid-state relay	5 A max. 300 mA max.	15 ms 2 ms	0.5 ms	Visible red LED 680nm	Peak excess gain at 4 inches (100 mm)

*NOTE: Q45X models may be used on sensor bus networks with addition of an optional plug-in expansion card. †NOTE: 30-foot cables are available.

Q45 Fiber Optic Mode Sensors



Curves do not apply to NAMUR sensors.

FIBER OPTIC MODE: Glass fibers

■ DC ■ NAMUR ■ AC

Sensor Model	Termination: Cable or quick disconnect (QD)	Supply Voltage	Output				Beam	Sensing Range
			Type	Rating	Response	Repeatability		
Q45BB6F Q45BB6FQ Q45BB6FQ5 *Q45XB6FQ	4-wire 6-ft cable † 4-pin mini QD 4-pin euro QD 5-pin mini QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.5 ms	Infrared LED 880nm	Opposed to 54 in. (1.4m) using (2) IT23S fibers Diffuse to 4 in. (10 cm) using BT23S fiber
Q45AD9F Q45AD9FQ	2-wire 6-ft cable † 4-pin euro QD	5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	5 ms	0.5 ms	Infrared LED 880nm	Opposed to 22 in. (56 cm) Diffuse to 1.8 in. (5 cm)
Q45VR2F Q45VR2FQ Q45BW22F Q45BW22FQ Q45BW22FQ1	5-wire 6-ft cable † 5-pin mini QD 3-wire 6-ft cable † 3-pin mini QD 4-pin micro QD	90 to 250V ac	SPDT e/m relay SPST solid-state relay	5 A max. 300 mA max.	15 ms 2 ms	0.5 ms	Infrared LED 880nm	Opposed to 54 in. (1.4m) using (2) IT23S fibers Diffuse to 4 in. (10 cm) using BT23S fiber

FIBER OPTIC MODE: Plastic fibers

■ DC ■ NAMUR ■ AC

Sensor Model	Termination: Cable or quick disconnect (QD)	Supply Voltage	Output				Beam	Sensing Range
			Type	Rating	Response	Repeatability		
Q45BB6FP Q45BB6FPQ Q45BB6FPQ5 *Q45XB6FPQ	4-wire 6-ft cable † 4-pin mini QD 4-pin euro QD 5-pin mini QD	10 to 30V dc	Bipolar: NPN + PNP	250 mA each output	2 ms	0.5 ms	Visible red LED 660nm	Opposed to 5 in. (13 cm) using .040 in. dia. fibers Diffuse to 1.7 in. (4.4 cm) using .040 in. dia. fiber
Q45AD9FP Q45AD9FPQ	2-wire 6-ft cable † 4-pin euro QD	5 to 15V dc	NAMUR	≤1.1 mA to ≥2.1 mA	5 ms	0.5 ms	Visible red LED 660nm	Opposed to 3.5 in. (9 cm) Diffuse to 1.2 in. (3 cm)
Q45VR2FP Q45VR2FPQ Q45BW22FP Q45BW22FPQ Q45BW22FPQ1	5-wire 6-ft cable † 5-pin mini QD 3-wire 6-ft cable † 3-pin mini QD 4-pin micro QD	90 to 250V ac	SPDT e/m relay SPST solid-state relay	5 A max. 300 mA max.	15 ms 2 ms	0.5 ms	Visible red LED 660nm	Opposed to 5 in. (13 cm) using .040 in. dia. fibers Diffuse to 1.7 in. (4.4 cm) using .040 in. dia. fiber

*NOTE: Q45X models may be used on sensor bus networks with addition of an optional plug-in expansion card. †NOTE: 30-foot cables are available.

Q45 General Specifications & Dimensions

CONSTRUCTION: Molded VALOX® thermoplastic polyester housing. Molded acrylic lenses, stainless steel hardware. O-ring sealed transparent Lexan® top cover. NEMA 6P (IEC IP67) rated (1200 psi washdown).


CABLE: Sensors may be supplied with either a PVC-covered cable, or an integral quick-disconnect connector (see selection tables).

ADJUSTMENTS: Multi-turn sensitivity (GAIN) adjustment. Internal switch for selection of LIGHT or DARK operate mode (except NAMUR). Optional logic modules have adjustable timing (except NAMUR).

STATUS INDICATORS: POWER (green) LED lights with power applied. SIGNAL (red) LED with AID™ system (except NAMUR) lights when sensor sees its modulated light source, and pulses at a rate proportional to received signal strength. LOAD (yellow) LED (except NAMUR) lights when output is energized. Optional 7-element signal strength display (except NAMUR).


DIMENSIONS: Cabled sensors shown. Add 0.5" (12mm) to overall height for models with quick-disconnect cable fitting.

Models Q45...CV and Q45...CV4




Models Q45...D, Q45...DL, Q45...R, Q45...LV and Q45...E*


*Q456E emitters have POWER LED only, and no additional adjustments.




Model Q45...LP



Model Q45...F for glass fiber optics



Model Q45...FP for plastic fiber optics



Banner. The preferred photoelectric sensor.

More engineers prefer to purchase Banner Photoelectric Controls than any other brand, by a wide margin*. Why? There are several reasons. Banner is the world's most capable photoelectric company offering the broadest line of products and solutions in the industry. Banner can handle any size order utilizing the most advanced manufacturing capabilities. We can deliver any of more than 10,000 different sensors in just three days—most can ship within hours! And Banner has the best applications engineers in the industry, backed by the most knowledgeable distributors and sales engineers available, worldwide. We're close by wherever you're located, and we're ready to help you with your applications. When you add it all up, you'll find more value in Banner Photoelectrics.

*Source: Control Engineering Manufacturer Recognition Study, 15th Edition.



The Banner Catalog.

The industry's most complete catalog; over 350 pages of detailed product and technical information on over 10,000 sensors. Simple selection charts make specifying the correct photoelectric sensor easier than ever. Additional technical information includes product selection charts, beam patterns, excess gain curves, hook-up diagrams and application notes, plus complete specifications, glossary of terms and data reference. Call or write for your copy today.



The Photoelectric Handbook.

The most authoritative book on photoelectric sensing available; an in-depth deskside reference manual including over 240 pages of valuable information. Includes complete textbook discussion of sensing theory and in-depth technical information on sensor selection, including sensing modes, sensor sizes and types, plus electrical and environmental considerations. Call or write for your copy today.



BANNER[®]
the photoelectric specialist

Banner Engineering Corporation
P.O. Box 9414
Minneapolis, MN 55440
Phone (612) 544-3164
FAX (612) 544-3213