

Safety Data Sheet



SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Multicomp D-Limonene
Product number MC002237, ZP

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.
Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier Premier Farnell plc
150 Armley Road
Leeds
LS12 2QQ
+44 (0) 870 129 8608

1.4. Emergency telephone number

Emergency telephone +44 1865 407333

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Flam. Liq. 3 - H226

Health hazards Skin Irrit. 2 - H315 Skin Sens. 1 - H317 Asp. Tox. 1 - H304

Environmental hazards Aquatic Chronic 2 - H411

2.2. Label elements

Pictogram



Signal word Danger

Hazard statements H226 Flammable liquid and vapour.
H304 May be fatal if swallowed and enters airways. H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H411 Toxic to aquatic life with long lasting effects.

Precautionary statements P102 Keep out of reach of children.
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.
No smoking.
P261 Avoid breathing vapour/ spray.

Contains	P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P302+P352 IF ON SKIN: Wash with plenty of water. P501 Dispose of contents/ container in accordance with national regulations.
Detergent labelling	Orange Terpenes
Supplementary precautionary statements	≥ 30% perfumes P233 Keep container tightly closed. P240 Ground and bond container and receiving equipment. P241 Use explosion-proof electrical equipment. P242 Use non-sparking tools. P243 Take action to prevent static discharges. P264 Wash contaminated skin thoroughly after handling. P272 Contaminated work clothing should not be allowed out of the workplace. P273 Avoid release to the environment. P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor. P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower. P321 Specific treatment (see medical advice on this label). P331 Do NOT induce vomiting. P332+P313 If skin irritation occurs: Get medical advice/ attention. P333+P313 If skin irritation or rash occurs: Get medical advice/ attention. P362+P364 Take off contaminated clothing and wash it before reuse. P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog to extinguish. P391 Collect spillage. P403+P235 Store in a well-ventilated place. Keep cool.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.1. Mixtures

Orange Terpenes

60-100%

CAS number: 8028-48-6

Classification

Flam. Liq. 3 - H226

Skin Irrit. 2 - H315

Skin Sens. 1 - H317

Asp. Tox. 1 - H304

Aquatic Chronic 2 - H411

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.

Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if symptoms are severe or persist.
Ingestion	Do not induce vomiting. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention immediately.
Skin contact	It is important to remove the substance from the skin immediately. In the event of any sensitisation symptoms developing, ensure further exposure is avoided. Remove contamination with soap and water or recognised skin cleansing agent. Get medical attention if symptoms are severe or persist after washing.
Eye contact	Rinse with water. Get medical attention if any discomfort continues.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known.
Ingestion	May cause sensitisation or allergic reactions in sensitive individuals. May cause irritation. Aspiration hazard if swallowed. Entry into the lungs following ingestion or vomiting may cause chemical pneumonitis.
Skin contact	May cause skin sensitisation or allergic reactions in sensitive individuals. Redness. Irritating to skin.
Eye contact	No specific symptoms known. May be slightly irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically. May cause sensitisation or allergic reactions in sensitive individuals.
-----------------------------	--

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up. Flammable liquid and vapour. Vapours may be ignited by a spark, a hot surface or an ember. Vapours may form explosive mixtures with air. Fire-water run-off in sewers may create fire or explosion hazard.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has
---	---

not ignited, use water spray to disperse vapours and protect men stopping the leak. Avoid discharge to the aquatic environment. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.

Special protective equipment for firefighters

Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions

Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Evacuate area. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Promptly remove any clothing that becomes contaminated. Avoid contact with skin and eyes.

6.2. Environmental precautions

Environmental precautions

Avoid discharge into drains or watercourses or onto the ground. Avoid discharge to the aquatic environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up

Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Eliminate all ignition sources if safe to do so. No smoking, sparks, flames or other sources of ignition near spillage. Do not allow material to enter confined spaces, due to the risk of explosion. Absorb small quantities with paper towels and evaporate in a safe place. Once evaporation is complete, place paper in a suitable waste disposal container and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dangerous for the environment. Do not empty into drains. For waste disposal, see Section 13.

6.4. Reference to other sections

Reference to other sections

For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions

Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. The product is flammable. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Avoid discharge to the aquatic environment. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

Advice on general occupational hygiene

Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions

Store locked up. Keep away from oxidising materials, heat and flames. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.

Storage class

Flammable liquid storage.

7.3. Specific end use(s)

Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

NA

8.2. Exposure controls

Protective equipment



Appropriate engineering controls Eye/face protection

Provide adequate ventilation.

Avoid contact with eyes. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

Hand protection

Wear protective gloves. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with European Standard EN374. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

Other skin and body protection

May cause skin sensitisation or allergic reactions in sensitive individuals. Wear appropriate clothing to prevent repeated or prolonged skin contact.

Hygiene measures

Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.

Respiratory protection

No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.

Environmental exposure controls

Keep container tightly sealed when not in use. Avoid release to the environment.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance

Liquid.

Colour

Water-white. Yellowish.

Odour	Characteristic.
Odour threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	176°C @
Flash point	48°C
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	1.4 mm Hg @ °C
Vapour density	Not available.
Relative density	0.835 to 0.855
Bulk density	Not available.
Solubility(ies)	Insoluble in water. Soluble in the following materials: Ethanol.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Kinematic viscosity ≤ 20.5 mm ² /s. Explosive properties Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information NA

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions The following materials may react strongly with the product: Oxidising agents.

10.4. Conditions to avoid

Conditions to avoid Avoid heat, flames and other sources of ignition. Containers can burst violently or explode when heated, due to excessive pressure build-up. Static electricity and formation of sparks must be prevented.

10.5. Incompatible materials

Materials to avoid Oxidising materials. Acids - oxidising.

10.6. Hazardous decomposition products

Hazardous

decomposition products

Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀)

Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀)

Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀)

Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data

Irritating.

Serious eye damage/irritation

Serious eye damage/irritation

Based on available data the classification criteria are not met.

Respiratory sensitisation

Respiratory sensitisation

Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation

May cause skin sensitisation or allergic reactions in sensitive individuals.

Germ cell mutagenicity

Genotoxicity - in vitro

Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity

Based on available data the classification criteria are not met.

IARC carcinogenicity

None of the ingredients are listed or exempt.

Reproductive toxicity

Reproductive toxicity - fertility

Based on available data the classification criteria are not met.

Reproductive

toxicity - development

Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure

Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure

Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard	Asp. Tox. 1 - H304 May be fatal if swallowed and enters airways. Pneumonia may be the result if vomited material containing solvents reaches the lungs.
Aspiration hazard	
General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known.
Ingestion	May cause sensitisation or allergic reactions in sensitive individuals. May cause irritation. Aspiration hazard if swallowed. Entry into the lungs following ingestion or vomiting may cause chemical pneumonitis.
Skin contact	May cause skin sensitisation or allergic reactions in sensitive individuals. Redness. Irritating to skin.
Eye contact	No specific symptoms known.
Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target organs	No specific target organs known.
Medical considerations	Skin disorders and allergies.

Toxicological information on ingredients.

Orange Terpenes

Acute toxicity - oral	
Notes (oral LD ₅₀)	LD ₅₀ 4400 mg/kg, Oral, Rat
Acute toxicity - dermal	
Notes (dermal LD ₅₀)	LD ₅₀ >2000 mg/kg, Dermal, Rabbit

SECTION 12: Ecological Information

12.1. Toxicity

Toxicity Aquatic Chronic 2 - H411 Toxic to aquatic life with long lasting effects.

12.2. Persistence and degradability

Persistence and degradability The degradability of the product is not known.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not available.

Ecological information on ingredients.

Orange Terpenes

Bioaccumulative potential Potentially bioaccumulating.

12.4. Mobility in soil

Mobility No data available.

12.5. Results of PBT and vPvB assessment

Ecological information on ingredients.

Orange Terpenes

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects None known.

Ecological information on ingredients.

Orange Terpenes

Other adverse effects Dangerous for the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information

The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods

Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

14.1. UN number

UN No. (ADR/RID) 2319

UN No. (IMDG) 2319

UN No. (ICAO) 2319

UN No. (ADN) 2319

14.2. UN proper shipping name

Proper shipping name (ADR/RID) TERPENE HYDROCARBONS, N.O.S.

Proper shipping name (IMDG) TERPENE HYDROCARBONS, N.O.S.

Proper shipping name (ICAO) TERPENE HYDROCARBONS, N.O.S.

Proper shipping name (ADN) TERPENE HYDROCARBONS, N.O.S.

14.3. Transport hazard class(es)

ADR/RID class 3

ADR/RID classification code F1

ADR/RID label 3

Safety Data Sheet



IMDG class 3

ICAO class/division 3

ADN class 3

Transport labels



14.4. Packing group

ADR/RID packing group III

IMDG packing group III

ADN packing group III

ICAO packing group III

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant No.

14.6. Special precautions for user

EmS F-E, S-D

ADR transport category 3

Emergency Action Code 3Y

Hazard Identification

Number(ADR/RID) 30

Tunnel restriction code (D/E)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

NA

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations Health and Safety at Work etc. Act 1974 (as amended).
The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716).

Safety Data Sheet



The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"]. EH40/2005 Workplace exposure limits.

EU legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).

Commission Regulation (EU) No 453/2010 of 20 May 2010.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

Dangerous Preparations Directive 1999/45/EC.

Dangerous Substances Directive 67/548/EEC.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Classification procedures according to Regulation (EC) 1272/2008

Asp. Tox. 1 - H304: Skin Irrit. 2 - H315: Skin Sens. 1 - H317: : Calculation method.

Aquatic Chronic 2 - H411: : Calculation method. Flam. Liq. 3 - H226: : Expert judgement.

Hazard statements in full

H226 Flammable liquid and vapour.

H304 May be fatal if swallowed and enters airways.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H411 Toxic to aquatic life with long lasting effects.

Part Number

MC002237

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com

