


# PCIE-1730 PCIE-1730H

## 32-Ch TTL, 32-Ch Isolated Digital I/O PCIe Card

## 32-Ch TTL, 32-Ch Isolated Digital I/O PCIe Card with Digital Filter and Interrupt Function

NEW



### Features

- 32-ch isolated DI/O (16-ch digital input, 16-ch digital output)
- 32-ch TTL DI/O (16-ch digital input, 16-ch digital output)
- High output driving capacity
- Interrupt handling capability
- Selectable digital filter time
- D-type connector for isolated input and output channels
- High-voltage isolation on output channels (2,500 V<sub>DC</sub>)

### Introduction

PCIE-1730/1730H feature 32 TTL digital I/O channels and 32 digital I/O channels with up to 2,500 V<sub>DC</sub> isolation protection, making them ideal for industrial applications that require high-voltage isolation. For PCIE-1730H, all signals can be used as interrupt request signals and to disable/enable the interrupt function for every channel, as well as to support the input signal edge, which generates interrupts. All PCIE-1730 digital input channels have a digital filter to prevent inaccurate recognition of input signals that contain noise or chattering.

### Specifications

#### Digital Input

- **Channels** 16
- **Compatibility** 5 V/TTL
- **Input Voltage** Logic 0: 0.8 V max.  
Logic 1: 2.0 V min.
- **Interruptible Channels** PCIE-1730: 2 (IDIO, IDI8)  
PCIE-1730H: 16

#### Isolated Digital Input

- **Channels** 16
- **Input Voltage** Logic 0: 3 V max.  
Logic 1: 10 V min. (30 V max.)
- **Interruptible Channels** PCIE-1730: 2 (IDIO, IDI8)  
PCIE-1730H: 16
- **Isolation Protection** 2,500 V<sub>DC</sub>
- **Opto-Isolator Response** 50 μs
- **Input Resistance** 2.7 kΩ @ 1 W
- **Digital Filter Time (PCIE-1730H only)**

Setting Data (n)	Digital Filter Time	Setting Data (n)	Digital Filter Time	Setting Data (n)	Digital Filter Time
0 (00h)	The filter function is not used.	7 (07h)	16μsec	14 (0Eh)	2.048msec
1 (01h)	0.25μsec	8 (08h)	32μsec	15 (0Fh)	4.096msec
2 (02h)	0.5μsec	9 (09h)	64μsec	16 (10h)	8.192msec
3 (03h)	1μsec	10 (0Ah)	128μsec	17 (11h)	16.384msec
4 (04h)	2μsec	11 (0Bh)	256μsec	18 (12h)	32.768msec
5 (05h)	4μsec	12 (0Ch)	512μsec	19 (13h)	65.536msec
6 (06h)	8μsec	13 (0Dh)	1.024msec	20 (14h)	131.072msec

#### Digital Output

- **Channels** 16
- **Compatibility** 5 V/TTL
- **Output Voltage** Logic 0: 0.5V max.  
Logic 1: 2.4V min.
- **Output Capability** Sink: 24mA @ 0.5V  
Source: 15mA @ 2.4V

#### Isolated Digital Output

- **Channels** 16
- **Output Type** Sink type (NPN)
- **Isolation Protection** 2,500 V<sub>DC</sub>
- **Output Voltage** 5 ~ 40 V<sub>DC</sub>
- **Sink Current** 500 mA max./channel
- **Opto-Isolator Response** 50 μs

#### General

- **Bus Type** PCI Express V1.0
- **I/O Connectors** 1 x DB37, female  
4 x 20-pin box header
- **Dimensions (L x H)** 168 x 100 mm (6.6" x 3.9")
- **Power Consumption** Typical: 3.3 V @ 280 mA, 12 V @ 330 mA  
Max.: 3.3 V @ 420 mA, 12 V @ 400 mA
- **Operating Temperature** 0 ~ 60 °C (32 ~ 140 °F)
- **Storage Temperature** -25 ~ 85 °C (-13 ~ 185 °F)
- **Storage Humidity** 5 ~ 95% RH, non-condensing

### Ordering Information

- **PCIE-1730-AE** 32-ch TTL and 32-ch isolated digital I/O PCIe card
- **PCIE-1730H-AE** 32-ch TTL and 32-ch isolated digital I/O PCIe card with digital filter and interrupt function

#### Accessories

- **PCL-10120-1E** 20-pin flat cable, 1 m
- **PCL-10120-2E** 20-pin flat cable, 2 m
- **ADAM-3920-AE** 20-pin DIN rail flat cable wiring board
- **PCLD-782-BE** 16-ch isolated DI board w/1 m, 20-pin flat cable
- **PCLD-885-AE** 16-ch power relay board w/20-pin and 50-pin flat cables
- **PCLD-785-BE** 16-ch relay board w/1 m, 20-pin flat cable
- **ADAM-3937-BE** DB37 DIN rail wiring board
- **PCL-10137-1E** DB37 cable, 1 m
- **PCL-10137-2E** DB37 cable, 2 m
- **PCL-10137-3E** DB37 cable, 3 m