

LQW15DN100M00#

“#” indicates a package specification code.

New
In Production
General
85 °C max.
Wound (Ferrite)
Reflow OK
RoHS
REACH

< List of part numbers with package codes >
 LQW15DN100M00D , LQW15DN100M00B

Shape

L size	1.10 ±0.1 mm
W size	0.65 ±0.1 mm
T size	0.6 ±0.1 mm
Size code in inch (mm)	0402 (1005)

Notes

When applied Rated current to the Products, Inductance will be within ±30% of nominal Inductance value.
 When applied Rated current to the Products, temperature rise caused by self-generated heat shall be limited to 40 °C max.

References

Packaging code	Specifications	Minimum quantity
D	φ 180mm Paper taping	8000
B	Packing in bulk	500

Mass (Typ.)	
1 piece	0.002g

Specifications

Inductance	10μH ±20%
Inductance test frequency	10MHz
Rated current (I _{sat}) (Based on Inductance change)	120mA
Rated current (I _{temp}) (Based on Temperature rise)	120mA
Max. of DC resistance	5.405Ω
Avg. of DC resistance	4.7Ω ±15%
Self resonance frequency (min.)	20MHz
Operating temperature range	-40~85°C
Class of magnetic shield	Magnetic Resin
Series	LQW15DN_00

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.