



Revision Number: 005.0

Issue date: 04/17/2017

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>LOCTITE STYCAST 4850 known as STYCAST 4850 DUMMY KIT</b>	<b>IDH number:</b>	1633713
<b>Product type:</b>	Encapsulant	<b>Region:</b>	United States
<b>Restriction of Use:</b>	None identified	<b>Contact information:</b>	
<b>Company address:</b>	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	Telephone:	(860) 571-5100
		MEDICAL EMERGENCY Phone:	Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711
		TRANSPORT EMERGENCY Phone:	CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887
		Internet:	www.henkeln.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**WARNING:** CAUSES SERIOUS EYE IRRITATION.

**HAZARD CLASS**

EYE IRRITATION

**HAZARD CATEGORY**

2A

**PICTOGRAM(S)**



**Precautionary Statements**

<b>Prevention:</b>	Wash affected area thoroughly after handling. Wear eye and face protection.
<b>Response:</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.
<b>Storage:</b>	Not prescribed
<b>Disposal:</b>	Not prescribed

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

**3. COMPOSITION / INFORMATION ON INGREDIENTS**

Hazardous Component(s)	CAS Number	Percentage*
Aluminium oxide	1344-28-1	40 - 50
Limestone	1317-65-3	10 - 20
Tetraethyl silicate	78-10-4	0.1 - 1

\* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

#### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
<b>Skin contact:</b>	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. If symptoms develop and persist, get medical attention. Wash clothing before reuse.
<b>Eye contact:</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
<b>Symptoms:</b>	See Section 11.

#### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
<b>Unusual fire or explosion hazards:</b>	Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
<b>Hazardous combustion products:</b>	Oxides of carbon. Oxides of silicon. Irritating organic vapours. Thermal decomposition may produce formaldehyde.

#### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Remove all sources of ignition. Ensure adequate ventilation. Isolate area. Keep unnecessary personnel away. Surfaces may become slippery after spillage. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a closed container until ready for disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

#### 7. HANDLING AND STORAGE

<b>Handling:</b>	Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Refer to Section 8.
<b>Storage:</b>	Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Aluminium oxide	1 mg/m <sup>3</sup> TWA Respirable fraction.	5 mg/m <sup>3</sup> PEL Respirable fraction. 15 mg/m <sup>3</sup> PEL Total dust. 50 MPPCF TWA Total dust. 15 MPPCF TWA Respirable fraction. 15 mg/m <sup>3</sup> TWA Total dust. 5 mg/m <sup>3</sup> TWA Respirable fraction.	None	None
Limestone	10 mg/m <sup>3</sup> TWA Total dust.	5 mg/m <sup>3</sup> PEL Respirable fraction. 15 mg/m <sup>3</sup> PEL Total dust.	None	None
Tetraethyl silicate	10 ppm TWA	100 ppm (850 mg/m <sup>3</sup> ) PEL	None	None

<b>Engineering controls:</b>	Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
<b>Respiratory protection:</b>	Use a NIOSH approved air-purifying respirator if the potential to exceed established exposure limits exists.
<b>Eye/face protection:</b>	Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
<b>Skin protection:</b>	Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	Liquid
<b>Color:</b>	White
<b>Odor:</b>	Slight
<b>Odor threshold:</b>	Not available.
<b>pH:</b>	Not available.
<b>Vapor pressure:</b>	Not applicable
<b>Boiling point/range:</b>	Not available.
<b>Melting point/ range:</b>	Not available.
<b>Specific gravity:</b>	1.66
<b>Vapor density:</b>	> 1 (Air = 1)
<b>Flash point:</b>	> 93.3 °C (> 199.94 °F) no method
<b>Flammable/Explosive limits - lower:</b>	Not available.
<b>Flammable/Explosive limits - upper:</b>	Not available.
<b>Autoignition temperature:</b>	Not available.
<b>Flammability:</b>	Not applicable
<b>Evaporation rate:</b>	Not available.
<b>Solubility in water:</b>	Insoluble
<b>Partition coefficient (n-octanol/water):</b>	Not available.
<b>VOC content:</b>	< 2.1 g/l
<b>Viscosity:</b>	Not available.
<b>Decomposition temperature:</b>	Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	None under normal processing.
<b>Hazardous decomposition products:</b>	Oxides of carbon. Oxides of silicon. Irritating organic vapours. Thermal decomposition may produce formaldehyde.
<b>Incompatible materials:</b>	Strong acids. Strong bases. Oxidizing agents.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	High temperatures. Avoid moisture. Store away from incompatible materials. Heat, flames, sparks and other sources of ignition.

## 11. TOXICOLOGICAL INFORMATION

**Relevant routes of exposure:** Skin, Inhalation, Eyes, Ingestion

### Potential Health Effects/Symptoms

<b>Inhalation:</b>	May cause respiratory tract irritation.
<b>Skin contact:</b>	May cause skin irritation.
<b>Eye contact:</b>	Causes serious eye irritation.
<b>Ingestion:</b>	May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Aluminium oxide	None	Irritant, Nuisance dust, Corrosive
Limestone	None	Nuisance dust
Tetraethyl silicate	None	Central nervous system, Irritant, Kidney, Liver, Lung

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Aluminium oxide	No	No	No
Limestone	No	No	No
Tetraethyl silicate	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.

**Hazardous waste number:** Not a RCRA hazardous waste.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### Water Transportation (IMO/IMDG)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

## 15. REGULATORY INFORMATION

### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

**TSCA 12 (b) Export Notification:** None above reporting de minimis

**CERCLA/SARA Section 302 EHS:** None above reporting de minimis.

**CERCLA/SARA Section 311/312:** Immediate Health, Delayed Health

**CERCLA/SARA Section 313:** This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Aluminium oxide (CAS# 1344-28-1).

**California Proposition 65:** This product contains a chemical known in the State of California to cause cancer.

### Canada Regulatory Information

**CEPA DSL/NDSL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

## 16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: 3

**Prepared by:** Debbie Friday, Regulatory Affairs Specialist

**Issue date:** 04/17/2017

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.