



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 9

LOCTITE LB 8065 known as Loctite 8065

SDS No. : 153550
V005.0

Revision: 25.08.2015

printing date: 06.12.2017

Replaces version from: 01.07.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE LB 8065 known as Loctite 8065

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Lubricant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

|| The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

|| The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Supplemental information

EUH210 Safety data sheet available on request.

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****General chemical description:**

Lubricant

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Copper 7440-50-8	231-159-6 01-2119480154-42	10- 20 %	Aquatic Acute 1 H400 Aquatic Chronic 3 H412
Mineral oil light naphthenic hydrotreat. <3% DMSO 64742-53-6	265-156-6 01-2119480375-34	10- 20 %	Asp. Tox. 1 H304

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

Carbon dioxide, foam, powder

5.2. Special hazards arising from the substance or mixture

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well-ventilated areas.

Prolonged or repeated skin contact should be avoided

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

Keep away from heat and direct sunlight.

7.3. Specific end use(s)

Lubricant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Copper 7440-50-8 [COPPER, FUME]		0,2	Time Weighted Average (TWA):		EH40 WEL
Copper 7440-50-8 [COPPER, INHALABLE DUSTS AND MISTS (AS CU)]		1	Time Weighted Average (TWA):		EH40 WEL
Copper 7440-50-8 [COPPER, INHALABLE DUSTS AND MISTS (AS CU)]		2	Short Term Exposure Limit (STEL):		EH40 WEL
Graphite 7782-42-5 [GRAPHITE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Graphite 7782-42-5 [GRAPHITE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Quartz (SiO ₂) 14808-60-7 [SILICA, RESPIRABLE CRYSTALLINE]		0,1	Time Weighted Average (TWA):		EH40 WEL

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Distillates (petroleum), hydrotreated heavy naphthenic 64742-52-5 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL
Distillates (petroleum), hydrotreated heavy naphthenic 64742-52-5 [MINERAL OIL USED IN METAL WORKING, INHALABLE FRACTION]		0,2	Time Weighted Average (TWA):		IR_OEL
Copper 7440-50-8 [COPPER (AS CU), DUSTS AND MISTS]		1	Time Weighted Average (TWA):		IR_OEL
Copper 7440-50-8 [COPPER (AS CU), FUME]		0,2	Time Weighted Average (TWA):		IR_OEL
Copper 7440-50-8 [COPPER (AS CU), DUSTS AND MISTS]		2	Short Term Exposure Limit (STEL):		IR_OEL
Graphite 7782-42-5 [GRAPHITE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Graphite 7782-42-5 [GRAPHITE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Distillates (petroleum), hydrotreated light naphthenic 64742-53-6 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL
Distillates (petroleum), hydrotreated light		0,2	Time Weighted Average		IR_OEL

naphthenic 64742-53-6 [MINERAL OIL USED IN METAL WORKING, INHALABLE FRACTION]			(TWA):		
Quartz (SiO ₂) 14808-60-7 [QUARTZ, RESPIRABLE DUST (SEE CRYSTALLINE SILICA)]		0,1	Time Weighted Average (TWA):		IR_OEL

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	solid light brown
Odor	mild
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	Product is a solid. Burn Rate: Approx 14 mm/2 minutes
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	1,18 g/cm ³
(ρ)	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Insoluble
(Solvent: Water)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable

Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

No decomposition if used according to specifications.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

Irritating organic vapours.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

May cause irritation to the digestive tract.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Copper 7440-50-8	LD50	584 mg/kg	oral		rat	
Mineral oil light naphthenic hydrotreat. <3% DMSO 64742-53-6	LD50	> 5.000 mg/kg	oral			

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

12.2. Persistence and degradability**Persistence and Biodegradability:**

The product is not biodegradable.

12.3. Bioaccumulative potential / 12.4. Mobility in soil**Mobility:**

Cured adhesives are immobile.

Bioaccumulative potential:

No data available.

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
Copper 7440-50-8	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Mineral oil light naphthenic hydrotreat. <3% DMSO 64742-53-6	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Disposal must be made according to official regulations.

Waste code

06 04 05 - wastes containing other heavy metals

SECTION 14: Transport information**14.1. UN number**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	3077
IATA	Not dangerous goods

14.2. UN proper shipping name

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Copper)
IATA	Not dangerous goods

14.3. Transport hazard class(es)

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	9
IATA	Not dangerous goods

14.4. Packing group

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	III
IATA	Not dangerous goods

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	Severe marine pollutant
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	No dangerous good according to ADR/RID/ADN. Carriage in accordance with 1.1.4.2.1 ADR/RID/ADN.
IATA	No dangerous good according to ADR/RID/ADN. Carriage in accordance with 1.1.4.2.1 ADR/RID/ADN.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**VOC content < 3 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H304 May be fatal if swallowed and enters airways.

H400 Very toxic to aquatic life.

H412 Harmful to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.