

## LED PIPE 1500

LED PIPE 1500 1000LM 11W L600 4000K

**0051020**



### Product features

- LED Batten T5 1500lm per metre, 1000LM, 11W, L600, 4000K, 120 degree beam angle, includes switch, includes stripped cable (75cm), white polycarbonate body, dimensions length 582mm, width 24mm, height 36mm, includes standard and tilting brackets, linkable up to 10m.

## PRODUCT OVERVIEW

<b>Certifications</b>	CE
<b>Colour temperature (K)</b>	4000
<b>Colour</b>	White
<b>CRI (Ra)</b>	80
<b>EAN code</b>	5410288510200
<b>Luminous flux (lm)</b>	1000
<b>Housing</b>	Polycarbonate
<b>IP rating</b>	IP20
<b>Light colour</b>	Cool white
<b>LOR (%)</b>	100
<b>Mount</b>	Surface mounted
<b>Ordering number</b>	0051020
<b>Efficacy (Rated) (lm/w)</b>	91
<b>Average life (h) - L70/B50</b>	30000
<b>Technology</b>	LED
<b>Voltage (V)</b>	100-240
<b>Included lamp</b>	Integrated LED

## DATA TABLE

### General data

<b>Certifications</b>	CE
<b>EAN code</b>	5410288510200
<b>Environment</b>	Internal
<b>General application</b>	Residential & Consumer
<b>Housing</b>	Polycarbonate
<b>Mount</b>	Surface mounted
<b>Ordering number</b>	0051020
<b>Product name</b>	LED PIPE 1500 1000LM 11W L600 4000K
<b>Average life (h) - L70/B50</b>	30000
<b>Technology</b>	LED

## LED PIPE 1500

LED PIPE 1500 1000LM 11W L600 4000K

**0051020**

<b>Product features</b>	LED Batten T5 1500lm per metre, 1000LM, 11W, L600, 4000K, 120 degree beam angle, includes switch, includes stripped cable (75cm), white polycarbonate body, dimensions length 582mm, width 24mm, height 36mm, includes standard and tilting brackets, linkable up to 10m.
-------------------------	---

**What temperature Life is measured at (°C):** 25

### Optical data

<b>Colour temperature (K)</b>	4000
<b>CRI (Ra)</b>	80
<b>Distribution type</b>	Direct
<b>Luminous flux (lm)</b>	1000
<b>Light colour</b>	Cool white
<b>LOR (%)</b>	100

### Physical data

<b>Colour</b>	White
<b>Diffuser finish</b>	Frosted
<b>Height (mm)</b>	36
<b>IP rating</b>	IP20
<b>Lamp included</b>	Integrated
<b>Length (mm)</b>	582
<b>Width (mm)</b>	24
<b>Included lamp</b>	Integrated LED

### Electrical data


<b>Electrical protection</b>	CLASS 2
<b>Efficacy (Rated) (lm/w)</b>	91
<b>Total power consumption (W)</b>	11
<b>Voltage (V)</b>	100-240

## PHOTOMETRY

## LED PIPE 1500

LED PIPE 1500 1000LM 11W L600 4000K

**0051020**




Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	10.58 1.60	866	84.8°	85	0
1.0	21.16 3.20	216	84.8°	18	0
1.5	31.74 4.80	96	84.8°	7	0
2.0	42.32 6.40	54	84.8°	4	0
2.5	52.89 8.00	36	84.8°	3	0
3.0	63.47 9.60	24	84.8°	2	0

Distance [m]      Cone diameter [m]      Illuminance [lx]  
 — C0 - C180 (Half beam angle: 116.0°)  
 — C90 - C270 (Half beam angle: 159.2°)

## TECHNICAL DRAWINGS

Size	L1	L2	W	H
4/6W	270mm	282mm	24mm	36mm
7/11W	570mm	582mm	24mm	36mm
10/17W	870mm	882mm	24mm	36mm
14/22W	1170mm	1182mm	24mm	36mm





## LED PIPE 1500

LED PIPE 1500 1000LM 11W L600 4000K


**0051020**


**SYLVANIA** 0051020

 This luminaire contains built in LED lamps.


 } **LED**


The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built in LED lamps.

The lamps cannot be changed in the luminaire.

 } **LED**

**SYLVANIA** 0051020  874/2012