

Acer P1150(MR.JPK11.002)

P1150,DLP 3D,SVGA Projector,3600Lm,20000/1,2xHDMI ,Bag,2.25kg,EURO/UK Power EMEA

Acer Essential series projectors are best value projectors ideal for everyday use,at work or home. Make your presentations more compelling and entertainment more exciting with high brightness,high contrast and DLP 3D Ready,while adhering to your bottom line.



Key Selling Points

- Auto ceiling mount correction
- Acer ColorSafe
- Acer DynamicBlack
- Wireless projection
- 3D
- Acer EcoProjection

Product Features

Auto ceiling mount correction

This feature automatically flips the projected image over if the projector is turned upside down.

Acer ColorSafe

This technology ensures this device will deliver great color reproduction,even after years of intensive use.

Acer DynamicBlack

Improves image contrast by dynamically adjusting dark scenes to optimal black levels.

Wireless projection

Project content without bothersome cables. Say goodbye to cable clutter and manual connecting of devices.

3D

Experience the most immersive entertainment there is - in your home! Use with 3D glasses to make visuals come alive.

Acer EcoProjection

This device is designed to help the planet by automatically reducing standby power consumption by as much as 80%.

Main Specifications

Product Description	Acer P1150 - DLP projector - portable - 3D
Device Type	DLP projector
3D Capable	Yes (3D glasses sold separately)
Built-in Devices	Speaker
Brightness	3600 lumens
Contrast Ratio	20000:1 (dynamic)
Resolution	SVGA (800 x 600)
Native Aspect Ratio	4:3
Colour Support	1.07 billion colours
Bulb type	P-VIP 203 Watt
Bulb life cycle	Up to 5000 hour(s) / up to 15000 hour(s) (economic mode)
Video Input	RGB,composite video (PAL-B/G,PAL-N,PAL-M,PAL-I,NTSC 4.43,NTSC 3.58,PAL-D,SECAM L,PAL-H,SECAM K1,SECAM D/K,SECAM B/G)
Video Modes	480p,720p,1080i,1080p,480i,576i,576p
Speakers	Speaker(s) - integrated
Power	AC 120/230 V
Power Consumption Operational	260 Watt

Dimensions (WxDxH)	29.95 cm x 22 cm x 10.51 cm
Weight	2.4 kg

Extended Specification

General

Device Type	DLP projector
3D Capable	Yes (3D glasses sold separately)
Built-in Devices	Speaker

Projector

Brightness	3600 lumens
Brightness (Reduced)	2880 lumens
Contrast Ratio	20000:1 (dynamic)
Image Size	56 cm - 762 cm
Projection Distance	1 m - 12 m
Throw Ratio	1.96 - 2.15:1
Uniformity	85 %
Digital Zoom Factor	2x
Resolution	SVGA - SVGA (800 x 600) (native) / 1920 x 1200 (resized)
Native Aspect Ratio	4:3
Colour Support	1.07 billion colours
Max Sync Rate (V x H)	120 Hz x 100 kHz
Bulb type	P-VIP 203 Watt
Bulb life cycle	Up to 5000 hour(s) / up to 15000 hour(s) (economic mode)

Features Instant Pack Technology, DLP 3D Ready, Auto Vertical Keystone, SmartFormat Technology, 16:9 aspect ratio support, EcoProjection Technology, Auto Power Off, Acer ColorSafe II Technology, Quick-Start, ColorBoost 3D Technology

Lens

Focus Type	Manual
Lens Aperture	F/2.56-2.68
Zoom Type	Manual
Zoom Factor	1.1x
Keystone Correction Direction	Vertical
Vertical Keystone Correction	-40 / +40

Video Input

TV System	PAL-B/G, PAL-N, PAL-M, PAL-I, NTSC 4.43, NTSC 3.58, PAL-D, SECAM L, PAL-H, SECAM K1, SECAM D/K, SECAM B/G
Analogue video Signal	RGB, composite video
Video Interfaces	VGA, HDMI, composite video, MHL
Video Modes	480p, 720p, 1080i, 1080p, 480i, 576i, 576p

Speakers

Type	Integrated
------	------------

Sound Output Mode	Mono
Output Power / Channel	3 Watt
Speakers	1 x mixed channel

Expansion / Connectivity

Interfaces	<ul style="list-style-type: none"> 1 x HDMI - 19 pin HDMI Type A 1 x Mobile High-Definition Link (MHL) / HDMI 2 x VGA input - 15 pin HD D-Sub (HD-15) 1 x VGA output - 15 pin HD D-Sub (HD-15) 1 x serial RS-232 1 x USB - 4 pin mini-USB Type B (management) 1 x USB - 4 pin USB Type A 1 x audio line-in - mini-phone 3.5 mm 1 x audio line-out - mini-phone 3.5 mm 1 x composite video input - RCA
------------	---

Power

Power Source	AC
Nominal Voltage	AC 120/230 V
Power Consumption Operational	260 Watt
Power Consumption Stand by	0.5 Watt

Dimensions &Weight

Width	29.95 cm
Depth	22 cm
Height	10.51 cm
Weight	2.4 kg

Environmental Parameters

Min Operating Temperature	0 °C
Max Operating Temperature	40 °C
Humidity Range Operating	90%
Sound Emission	30 dBA
Sound Emission (Economic Mode)	26 dBA

Product data is provided by CNET, we do not warrant the accuracy and completeness of the material contained in this data sheet