

# Product data sheet

## Characteristics

# P11VT3

## APC Performance SurgeArrest 11 Outlet with Phone (Splitter) and Coax Protection, 120V



### Overview

|                      |  |
|----------------------|--|
| Model Name           | APC Performance SurgeArrest 11 Outlet with Phone (Splitter) and Coax Protection, 120V  |
| Includes             | Coaxial cable , Telephone Cable , User Manual  |
| Standard Lead Time   | Usually in Stock   |
| Product Distribution | Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Guatemala , Haiti , Honduras , Jamaica , Mexico , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES) |

### Output

|                   |            |
|-------------------|------------|
| Number of Outlets | 11         |
| Receptacle Style  | NEMA 5-15R |

### Input

|                                |                      |
|--------------------------------|----------------------|
| Nominal Input Voltage          | 120V                 |
| Input Power                    | 0 W                  |
| Input Frequency                | 50/60 Hz             |
| Input Connections              | NEMA 5-15P           |
| Maximum Line Current per phase | 0.0 A                |
| Cord Length                    | 8 feet (2.44 meters) |
| Maximum Input Current          | 0 A                  |

### Surge Protection and Filtering

|   |  |
|---|--|
| Surge energy rating                         | 3020 Joules  |
| EMI/RFI Noise rejection (100 kHz to 10 MHz) | 70.0 dB  |
| Peak Current Common Mode                    | 0.0 kA   |
| NM Surge Response Time (ns)                 | 1.0 NS   |
| Data Line Protection                        | Analog phone line for phone/fax/modem/DSL (RJ-11 connector) , Coaxial cable for-CATV/SATV/modem/Audio-Video (coax connector) |
| Data Lines Protected<br />(multi-line only) | 1-4  |
| Let Through Voltage Rating                  | 40   |

### Physical

|                 |                         |
|-----------------|-------------------------|
| Net Weight      | 2.33 lbs (1.06 kg)      |
| Maximum Height  | 1.57 inches (40.0 mm)   |
| Maximum Width   | 4.7 inches (119.0 mm)   |
| Maximum Depth   | 11.89 inches (302.0 mm) |
| Shipping Weight | 2.97 lbs (1.35 kg)      |
| Shipping Height | 2.36 inches (60.0 mm)   |
| Shipping Width  | 7.56 inches (192.0 mm)  |
| Shipping Depth  | 13.58 inches (345.0 mm) |

|  |                    |
|--|--------------------|
| Master Carton Units                                | 6.0                |
| Master Carton Dimensions (Length x Width x Height) | 15 x 8 x 15 inches |
| Master Carton Weight                               | 8.9 kg             |
| SCC Codes  | 1073130424903 7    |
| Color  | Black              |
| Units per Pallet                                   | 0.0                |

### Environmental

|                             |                               |
|-----------------------------|-------------------------------|
| Operating Environment       | 5 - 113 °F (-15 - 45 °C)      |
| Operating Relative Humidity | 0 - 95 %                      |
| Operating Elevation         | 0-10000 feet (0-3000 meters)  |
| Storage Temperature         | 5 - 113 °F (-15 - 45 °C)      |
| Storage Relative Humidity   | 0 - 95 %                      |
| Storage Elevation           | 0-50000 feet (0-15000 meters) |

### Conformance

|                             |                         |
|-----------------------------|-------------------------|
| Approvals                   | CSA , UL 1363 , UL 1449 |
| Standard warranty           | Lifetime                |
| Equipment protection policy | Lifetime : \$100000     |