



3.5 HDD DATA SHEET

The Power of Agility for Home, SOHO and SMB NAS Enclosures



IronWolf™ is designed for everything NAS. Get used to tough, ready and scalable 24x7 performance that can handle multi-drive environments across a wide range of capacities.



Best-Fit Applications

- 1- to 8-bay network attached storage (NAS)
- Desktop RAID and servers
- Multimedia server storage
- Private cloud



Key Advantages

Optimised for NAS with AgileArray.™ AgileArray enables dual-plane balancing and RAID optimisation in multi-bay environments, with the most advanced power management possible.

Actively protect your NAS with IronWolf Health Management focusing on prevention, intervention and recovery.¹

High performance means no lag time or downtime for users during workload traffic for the NAS. Seagate leads the competition with the highest-performing NAS drive portfolio.²

Rotational Vibration (RV) sensors. First in its class of drives to include RV sensors to maintain high performance in multi-drive NAS enclosures.³

Range of capacities up to 12 TB. More capacity options means more choices that will fit within the budget. Seagate provides a scalable solution for any NAS use-case scenario.

Do more in multi-user environments. IronWolf provides a workload rate of 180 TB/year. Multiple users can confidently upload and download data to the NAS server, knowing IronWolf can handle the workload, whether you are a creative professional or a small business.

Designed for always-on, always-accessible 24x7 performance. Access data on your NAS any time, remotely or on site.

1 M hours MTBF, 3-year limited warranty represents an improved total cost of ownership (TCO) over desktop drives with reduced maintenance costs.

¹ Contact your Seagate sales representative for further information.

² Performance may vary depending on user's hardware configuration and operating system.

³ Included on 4, 6, 8, 10 and 12 TB models.



Specifications	12TB	10TB	8TB	6TB	4TB
Standard Model Numbers	ST12000VN0007	ST10000VN0004	ST8000VN0022	ST6000VN0033	ST4000VN008
Interface	SATA 6Gb/s	SATA 6Gb/s	SATA 6Gb/s	SATA 6Gb/s	SATA 6Gb/s
Features and Performance					
Drive Bays Supported	1 – 8 Bays	1 – 8 Bays	1 – 8 Bays	1 – 8 Bays	1 – 8 Bays
Multi-User Technology	180 TB/year	180 TB/year	180 TB/year	180 TB/year	180 TB/year
Rotational Vibration (RV) Sensor	Yes	Yes	Yes	Yes	Yes
Dual-Plane Balance	Yes	Yes	Yes	Yes	Yes
Error Recovery Control	Yes	Yes	Yes	Yes	Yes
Max. Sustained Transfer Rate OD (MB/s)	210MB/s	210MB/s	210MB/s	210MB/s	180MB/s
Spindle Speed (RPM)	7,200	7,200	7,200	7,200	5,900
Cache (MB)	256	256	256	256	64
Reliability					
Load/Unload Cycles ¹	600,000	600,000	600,000	600,000	600,000
Non-recoverable Read Errors Rate, Max	1 per 10E15	1 per 10E15	1 per 10E15	1 per 10E15	1 per 10E14
Power-on Hours	8,760	8,760	8,760	8,760	8,760
Workload Rate Limit (WRL)	180	180	180	180	180
Mean Time Between Failures (MTBF, hours)	1,000,000	1,000,000	1,000,000	1,000,000	1,000,000
Limited Warranty (years)	3	3	3	3	3
Power Management					
Startup Current, Typical (12V, A)	1.8	1.8	1.8	1.8	1.8
Average Operating Power (W)	7.8 W	7.8 W	8.8 W	8.1 W	4.8 W
Idling Average (W)	5 W	5 W	7.6 W	7.2 W	3.95 W
Standby Mode/Sleep Mode, Typical (W)	0.8/0.8	0.8/0.8	0.6/0.6	0.6/0.6	0.5/0.5
Voltage Tolerance, Inc. Noise (5 V)	±5%	±5%	±5%	±5%	±5%
Voltage Tolerance, Inc. Noise (12 V)	±10%	±10%	±10%	±10%	±10%
Environmental/Temperature					
Operating (ambient, min °C)	5	5	5	5	5
Operating (drive case, max °C) ²	70	70	70	70	70
Non-operating (ambient, min °C)	-40	-40	-40	-40	-40
Non-operating (ambient max °C)	70	70	70	70	70
Halogen-free	Yes	Yes	Yes	Yes	Yes
Environmental/Shock					
Shock, Operating/Non-operating: 2 ms (max)	70Gs/250Gs	70Gs/250Gs	70Gs/250Gs	70Gs/250Gs	80Gs/300Gs
Environmental/Acoustics					
Idle (typical) ³	2.8 bels	2.8 bels	2.7 bels	2.7 bels	2.3 bels
Operating (typical)	3.2 bels	3.2 bels	2.8 bels	2.8 bels	2.5 bels
Physical					
Height (mm/in)	26.11 mm/1.028 in	26.11 mm/1.028 in	26.11 mm/1.028 in	26.11 mm/1.028 in	26.11 mm/1.028 in
Width (mm/in, max)	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in
Depth (mm/in, max)	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in
Weight (g/lb, typical)	705 g/1.55 lb	705 g/1.55 lb	780 g/1.72 lb	705 g/1.55 lb	610 g/1.345 lb
Carton Unit Quantity	20	20	20	20	20
Cartons per Pallet / Cartons per Layer	40/8	40/8	40/8	40/8	40/8

¹ Load/unload tested to 600,000 cycles.

² Seagate does not recommend operating at sustained case temperatures above 60°C. Operating at higher temperatures will reduce useful life of the product.

³ Idle measured in Idle1 state.



Specifications	3TB	2TB	1TB
Standard Model Numbers	ST3000VN007	ST2000VN004	ST1000VN002
Interface	SATA 6Gb/s	SATA 6Gb/s	SATA 6Gb/s
Features and Performance			
Drive Bays Supported	1 – 8 Bays	1 – 8 Bays	1 – 8 Bays
Multi-User Technology	180 TB/year	180 TB/year	180 TB/year
Rotational Vibration (RV) Sensor	No	No	No
Dual-Plane Balance	Yes	Yes	Yes
Error Recovery Control	Yes	Yes	Yes
Max. Sustained Transfer Rate OD (MB/s)	180MB/s	180MB/s	180MB/s
Spindle Speed (RPM)	5,900	5,900	5,900
Cache (MB)	64	64	64
Reliability			
Load/Unload Cycles ¹	600,000	600,000	—
Non-recoverable Read Errors Rate, Max	1 per 10E14	1 per 10E14	1 per 10E14
Power-on Hours	8,760	8,760	8,760
Workload Rate Limit (WRL)	180	180	180
Mean Time Between Failures (MTBF, hours)	1,000,000	1,000,000	1,000,000
Limited Warranty (years)	3	3	3
Power Management			
Startup Current, Typical (12V, A)	2	2	1.2
Average Operating Power (W)	4.8 W	4.3 W	3.76 W
Idling Average (W)	4.8 W	3.56 W	2.5 W
Standby Mode/Sleep Mode, Typical (W)	0.5/0.5	0.5/0.5	0.5/0.5
Voltage Tolerance, Inc. Noise (5 V)	±5%	±5%	±5%
Voltage Tolerance, Inc. Noise (12 V)	±10%	±10%	±10%
Environmental/Temperature			
Operating (ambient, min °C)	5	5	5
Operating (drive case, max °C) ²	70	70	70
Non-operating (ambient, min °C)	-40	-40	-40
Non-operating (ambient max °C)	70	70	70
Halogen-free	Yes	Yes	Yes
Environmental/Shock			
Shock, Operating/Non-operating: 2 ms (max)	80Gs/300Gs	80Gs/300Gs	80Gs/300Gs
Environmental/Acoustics			
Idle (typical) ³	2.3 bels	1.9 bels	2.1 bels
Operating (typical)	2.5 bels	2.1 bels	2.3 bels
Physical			
Height (mm/in)	26.11 mm/1.028 in	26.11 mm/1.028 in	20.2 mm/0.795 in
Width (mm/in, max)	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in
Depth (mm/in, max)	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in
Weight (g/lb, typical)	610 g/1.345 lb	535 g/1.18 lb	415 g/0.915 lb
Carton Unit Quantity	20	20	25
Cartons per Pallet / Cartons per Layer	40/8	40/8	40/8

¹ Load/unload tested to 600,000 cycles.

² Seagate does not recommend operating at sustained case temperatures above 60°C. Operating at higher temperatures will reduce useful life of the product.

³ Idle measured in Idle1 state.

AMERICAS	Seagate Technology LLC 10200 South De Anza Boulevard, Cupertino, California 95014, United States, 408-658-1000
ASIA/PACIFIC	Seagate Singapore International Headquarters Pte. Ltd. 7000 Ang Mo Kio Avenue 5, Singapore 569877, 65-6485-3888
EUROPE, MIDDLE EAST AND AFRICA	Seagate Technology SAS 16-18, rue du Dôme, 92100 Boulogne-Billancourt, France, 33 1-4186 10 00

© 2017 Seagate Technology LLC. All rights reserved. Seagate, Seagate Technology and the Spiral logo are registered trademarks of Seagate Technology LLC in the United States and/or other countries. AgileArray and IronWolf are either trademarks or registered trademarks of Seagate Technology LLC or one of its affiliated companies in the United States and/or other countries. All other trademarks or registered trademarks are the property of their respective owners. When referring to drive capacity, one gigabyte, or GB, equals one billion bytes; and one terabyte, or TB, equals one trillion bytes. Your computer's operating system may use a different standard of measurement and report a lower capacity. In addition, some of the listed capacity is used for formatting and other functions, and thus will not be available for data storage. Actual data rates may vary depending on operating environment and other factors. Seagate reserves the right to change, without notice, product offerings or specifications. DS1904.9-1707 GB July 2017