

James Briggs Ltd

Salmon Fields, Royton, Oldham OL2 6HZ UK

Tel: 0161 627 0101 Fax: 0161 627 0971

www.jamesbriggs.co.uk

TECHNICAL DATA SHEET

ETCH PRIMER

XUK433

1. Introduction

A grey modified acrylic primer based upon a speciality resin designed primarily to key onto non-ferrous metals, and to provide a tough, durable coating suitable for subsequent application of the HYCOTE range of standard gloss, satin and matt finishes, and matched colour paints.

2. Where to use

On non-ferrous metals including galvanised, anodised and zinc coated steel, aluminium.

3. Where not to use

- Not recommended for use on copper or brass

4. Benefits

- Excellent covering power
- Excellent adhesion to most non-ferrous surfaces.
- Suitable for use on many rigid plastics including glass reinforced polyester [See Section 6].
- Suitable for use on fully cured and aged paint finishes [See Section 6].

5. Physical properties [Etch Primer base except where stated].

| | |
|--------------------------------------|--|
| Appearance | Grey liquid with a characteristic paint solvent odour. |
| pH | Not applicable |
| Specific Gravity | 1.20 – 1.25 |
| Viscosity | 500 – 1,500cPs |
| Non Volatiles % m/m | 40 -50 |
| Active Content % m/m, as supplied | 15 - 20 |
| Flammability, as supplied | Extremely Flammable, flash point below -20°C |
| Composition Data, as supplied | A solvent based solution of a modified acrylic resin containing pigments, extenders, plasticizer, thixotropes and wetting agents dispersed in a butane/propane/isobutane based propellant. |
| Volatile Organic Content as supplied | Compliant with EU Directive 2004/42/CE |
| Service Temperatures | Up to 80°C |
| Application Temperatures | 15 - 25°C |

6. Application Details

Prepare the area to be treated, ensuring freedom from dust, grime, greases, oils etc, using a detergent solution followed by rinsing thoroughly and drying. Any corrosion, other surface contamination, and loosely adhering matter should be removed with an appropriate grade of wet and dry abrasive cloth. Following preparation the surfaces should be further treated with a solvent wipe using HYCOTE BRAKE CLEANER, [XUK302], white spirit, or thinners and allowed to dry.

If in doubt about the composition of the substrate, undertake a small test application on an inconspicuous area prior to use to ensure suitability.

This information is provided in good faith based upon data and sources believed to be reliable and correct. Conditions of use, outside the control of the Company, dictate that no responsibility can be assumed for the ultimate performance of this product.



James Briggs Ltd

Salmon Fields, Royton, Oldham OL2 6HZ UK

Tel: 0161 627 0101 Fax: 0161 627 0971

www.jamesbriggs.co.uk

TECHNICAL DATA SHEET

ETCH PRIMER

XUK433

Shake the can thoroughly for at least two minutes. Repeat shaking at regular intervals during use.

Apply sparingly from a distance of 20 – 25cm. Apply 2 to 3 light coats to achieve total and even coverage, leaving at least 15 minutes between each application.

Allow at least 24 hours between application of final coating and preparation for any subsequent finishes that may be required.

On completion of use, invert can and depress actuator for a few seconds to prevent nozzle blockage.

7. Availability

400 ml aerosols.

B047179 ,RJB, August 2017.