

**Part Number: 1673J**

50 Ohm Microwave, RG402, #19 SPCCS, PVC Jacket



## Product Description

RG-402/U type, 19 AWG solid .036" silver-plated copper-covered steel conductor, TFE Teflon® Insulation, copper-tin composite shield (100% coverage), PVC jacket.

## Technical Specifications

### Product Overview

Environmental Space:	Indoor/Outdoor
----------------------	----------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
19	Solid	SPCCS - Silver Plated Copper Covered Steel	0.036 in	1

Conductor Count:	1
AWG Size:	19

#### Insulation

Material	Material Trade Name	Nominal Diameter
TFE - Tetrafluoroethylene	Teflon®	0.116 in

#### Outer Shield Material

Type	Layer	Material	Coverage [%]
Tape	1	Copper Foil	100 %
Braid	2	Tin-Filled Composite	100 %

#### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.178 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
20.5 Ohm/1000ft	20.5 Ohm/1000ft		4.5 Ohm/1000ft	4.5 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
29.5 pF/ft

#### Inductance

Nominal Inductance
0.07 µH/ft

#### Impedance

Nominal Characteristic Impedance
50 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
-----------------	---------------------

500 MHz	8 dB/100ft
1000 MHz	12 dB/100ft
2000 MHz	18.1 dB/100ft
3000 MHz	22.9 dB/100ft
5000 MHz	31 dB/100ft
7000 MHz	37.8 dB/100ft
10000 MHz	46.6 dB/100ft
15000 MHz	59.1 dB/100ft
18000 MHz	65.8 dB/100ft
20000 MHz	70 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.46 ns/ft	69.5 %

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
500 MHz	9.5 dB/100ft
1000 MHz	14.5 dB/100ft
3000 MHz	26.5 dB/100ft
5000 MHz	36 dB/100ft
10000 MHz	54 dB/100ft
20000 MHz	84 dB/100ft

#### Power Rating

Frequency [MHz]	Max. Power Rating [W]	Nominal Power Rating [W]
500 MHz	600 W	600 W
1,000 MHz	401 W	401 W
2,000 MHz	268 W	268 W
3,000 MHz	211 W	211 W
5,000 MHz	157 W	157 W
7,000 MHz	129 W	129 W
10,000 MHz	105 W	105 W
15,000 MHz	83 W	83 W
18,000 MHz	74 W	74 W
20,000 MHz	70 W	70 W

#### Voltage

Non-UL Voltage Rating	UL Voltage Rating
1900 V RMS	30 V RMS

#### VSWR

Element	Frequency [MHz]	Max. VSWR
Ramp Function, End Points	500 MHz	1.1
	20000 MHz	1.3

#### Temperature Range

Non-UL Temp Rating:	105°C
UL Temp Rating:	105°C
Operating Temp Range:	-40°C To +105°C

#### Mechanical Characteristics

Bulk Cable Weight:	32 lbs/1000ft
Max Recommended Pulling Tension:	70 lbs
Min Bend Radius (Overall):	1.5 in
Min Bend Radius During Installation:	0.25 in
Min Bend Radius/Installation:	0.25 in
Min Flexing Radius:	0.75 in

#### Standards

UL AWM Style:	UL Style 10245
RG Type:	RG-402/U Type

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

## Flammability, LSOH, Toxicity Testing

Other Flammability:	Horizontal Wire
---------------------	-----------------

## Part Number

Plenum (Y/N):	No
---------------	----

## Variants

Item #	Color	Footnote
1673J 010100	BLACK	C
1673J 010500	BLACK	C V

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	V - 250' PUT-UP EXACT LENGTH MAXIMUM OF 3 PIECES, MINIMUM LENGTH 50'. 500' PUT-UP EXACT LENGTH MAXIMUM OF 5 PIECES, MINIMUM LENGTH 50'. 1000' PUT-UP EXACT LENGTH MAXIMUM OF 8 PIECES, MINIMUM LENGTH 50'.

## Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.