



Part Number: 6100UE

Security & Sound, 2 Conductor 14 AWG BC, CL2P

Product Description

Security & Commercial Audio Cable, 2 Conductor 14 AWG stranded (19x27) bare copper conductors with Flamarrest® insulation, CL2P, Flamarrest® jacket with ripcord.

Technical Specifications

Product Overview

Environmental Space:	Indoor - Plenum
Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
14	19x27	TC - Tinned Copper	2

Conductor Count:	2
AWG Size:	14

Insulation

Material	Material Trade Name	Nominal Wall Thickness
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.011 in

Color Chart

Number	Color
1	Black
2	White

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness	Ripcord
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.226 in	0.015 in	Yes

Construction and Dimensions

Cabling

Lay Length	Lay Direction	Twists
3.75 in	Left Hand	3.2 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
2.53 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor

36 pF/ft

Inductance

Nominal Inductance

0.145 μ H/ft

Current

Element	Max. Recommended Current [A]
10C Temperature Rise	Per conductor @ 25°C ambient: 8 A

Voltage

UL Voltage Rating

150V RMS

Temperature Range

Installation Temp Range:	0°C To +75
UL Temp Rating:	75°C
Operating Temp Range:	-10°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	38 lbs/1000ft
Max Recommended Pulling Tension:	95 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC Articles:	725
NEC/(UL) Specification:	CL2P
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
------------------	----------

Part Number

Plenum (Y/N):	Yes
Non-Plenum Number:	5100UH

Variants

Item #	Color	Footnote
6100UE 010U1000	BLACK	
6100UE 010500	BLACK	C
6100UE 008U1000	GRAY	
6100UE 8771000	NATURAL	C
6100UE 877500	NATURAL	
6100UE 8775000	NATURAL	
6100UE 877U1000	NATURAL	
6100UE 009U1000	WHITE	

6100UE 009U250	WHITE	
6100UE 009U500	WHITE	
6100UE 009U500	WHITE	
6100UE 004U1000	YELLOW	

Footnote: C - CRATE REEL PUT-UP.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.