

Conan® 1.00mm Connector System

SECURE, HIGH SPEED DESIGN FOR HARSH ENVIRONMENTS

Amphenol ICC's Conan® 1.00mm is a mezzanine connector designed for industrial applications and harsh environments. Its unique design with an audible "click" sound enhances the security and ease of use.

- New right angle configuration in 4 pin counts
- Right angle configurations has compact size of 8.5mm depth and 5.3mm height on PCB after mating
- Enables perpendicular stacking application



FEATURES

- Vertical configuration
- 9 to 69 positions
- 4.15mm to 7.0mm stack heights increment
- Right angle configuration
- 31, 41, 51, 69 position increment
- Vertical housing and terminal profile guarantees support of up to 5Gb/s
- Vertical versus vertical mating configuration
- Vertical receptacle versus RA header mating configuration
- Audible "click" sound during mating
- Polarization feature of housing
- Multiple packaging options available
- Locating pegs option
- Metal hold down option
- RoHS compliant and lead free

BENEFITS

- Comprehensive range of sizes and stack heights support diverse electronic packaging schemes
- Comprehensive solution to satisfy all customers needs
- Compatible with PCIe® Gen high speed performance on selected stack heights
- Useful for parallel board stacking application
- Useful for perpendicular stacking application
- Ensures secure mating interconnection
- Prevents mismating
- Meets various feeding processing needs
- Facilitates ease and accuracy during manual assembly
- Enables better retention on to the PCB
- Meets environmental, health and safety requirements

TECHNICAL INFORMATION

MATERIAL

• Contact Base Metal

• Header: Phosphor Bronze

• Receptacle: Copper Alloy, High Spring

Contact Area Finish: Gold or GXT®

■ Solder Tail Area: Pure Tin over 1.27µm Nickel

Housing Material: Cream-colored LCP (UL94V-0)

MECHANICAL PERFORMANCE

• Mating Force: 125g per contact max.

• Unmating Force: 25g per contact min.

• Retention Force (connector to PCB): 44N min.

- Contact Wipe: 0.64mm

Durability: 30 mating cycles

ELECTRICAL PERFORMANCE

• Insulation Resistance: $1000M\Omega$ min.

■ Contact Resistance: 30MΩ max.

• Withstanding Voltage: 500VAC RMS 60Hz

 Current Rating: 1.0A continuous (per contact, all contacts powered)

 Signal Integrity (differential pairs, connector only)

• Impedance: 100Ω +/- 10 @ 50 ps edge (10-90%)

• Insertion Loss: < 1.5dB up to 5GHz</p>

■ NEXT: ≤ 3.5% for a 50 ps edge (10-90%)

FEXT: ≤ 2.5% for a 50 ps edge (10-90%)

ENVIRONMENTAL

 IMFG per EIA 364-65 class 2a without SO2, 20 days mated

• High Temperature Life: 105°C

SPECIFICATIONS

■ Product Specification: GS-12-006

PACKAGING

• Tape and reel with vacuum pickup caps

TARGET MARKETS/APPLICATIONS



Communications and Networking Equipment




Electronic Security
Energy Controller/Module/Display
Machine-to-Machine (M2M) Office
Equipment
Point-of-Sale Equipment, Scanning
Portable Meter/Instrument



Medical Diagnostics

PART NUMBER SELECTOR


VERTICAL



Recommended packaging combinations:

For production: Connector with pick and place cap packaged in tape and reel (XXXX1-3XXXX) For proto-typing: Connector without pick and place cap packaged in tubes (XXXX0-2XXXX) For commercial applications see print 10118744

MODULE



Mated connector max. width: 5.59mm

RIGHT ANGLE

Description	Part Numbers
Conan® right angle header, 31 positions	10138400-111131LF
Conan® right angle header, 41 positions	10138400-111141LF
Conan® right angle header, 51 positions	10138400-111151LF
Conan® right angle header, 69 positions	10138400-111169LF

