

1. Identification of the substance/preparation and of the company/undertaking

1.1. Identification of the substance or preparation:

Synonyms: Tubing: VFFC (Versafit)

CAS no. : N.A. Reference : RAY/3122E Revision 6

EC index No. : N.A. NFPA code : N.D. EINECS No. : N.A. Molecular weight : N.A. RTECS No. : N.A. Formula : N.A.

1.2. Use of the substance or the preparation:

Heat-Shrinkable Polymeric Products

1.3. Company/undertaking identification:

Premier Farnell plc 150 Armley Road Leeds LS12 2QQ +44 (0) 870 129 8608

1.4. Telephone number for emergency:

+44 1865 407333

2. Composition/information on ingredients

Plastic materials may be based on polyethylene and olefin copolymers, chloropolymers, polyamides or silicones. Products may be coated with, or used in conjunction with adhesives/mastics based on polyamides and/or olefin copolymer

3. Hazards identification

This Safety Data Sheet applies to a group of products which are not hazardous as supplied in accordance with directives 67/548/EEC and 1999/45/EEC

Products may emit hazardous thermal decomposition products if overheated or burnt (see section 10.3)

4. First aid measures

4.1. Eye contact:

If molten material contacts the eye:

Rinse immediately with plenty of water for 15 minutes

Consult a doctor/medical service if irritation persists

4.2. Skin contact:

If molten material contacts the skin:

Immediately flush with cold water for 15 minutes

Do not attempt to remove material stuck to the skin

Treat as a burn

Consult a doctor/medical service

4.3. After inhalation:

If exposed to fumes from overheated or burnt material:

Remove the victim into fresh air

Keep warm and at rest





Consult a doctor/medical service if breathing problems develop

4.4. After ingestion:

Not applicable

5. Fire-fighting measures

5.1. Suitable extinguishing media:

Water spray Polyvalent foam ABC powder Carbon dioxide

5.2. Unsuitable extinguishing media:

No data available

5.3. Special exposure hazards:

Toxic decomposition products may be evolved in a fire (see section 10.3)

5.4. Instructions:

Not applicable

5.5. Special protective equipment for firefighters:

Self-contained breathing apparatus with full face piece Protective clothing for exposure to chemicals

6. Accidental release measures

6.1. Personal protection/precautions: see headings 8.1/8.3/10.3

6.2. Environmental precautions:

Not applicable

6.3. Clean-up:

Pick up for continued use or disposal

7. Handling and storage

7.1. Handling:

Refer product installation instructions

Avoid overheating the product after shrinkage has occurred

Stop heating immediately if the product blisters, chars or shows other signs of degradation

Avoid inhaling fumes which may be released and ventilate the area thoroughly before resuming work

Avoid contact with molten material

Wash hands before eating, drinking or smoking

Practice good standards of personal and industrial hygiene

7.2. Storage:

Store in a dry area

Store in a cool area

Product should be stored at temperatures below 40°C to avoid pre-recovery of expanded product

Store in the original packaging

Keep away from: heat sources







Storage temperature : < 40°C

Quantity limits : N.D. kg

Storage life : N.D.

Materials for packaging : -

Suitable : No data available
To avoid : No data available

7.3. Specific uses:

See information supplied by the manufacturer

8. Exposure controls/Personal protection

8.1. Exposure limit values:

Not applicable

Sampling methods:

No data available

8.2. Exposure controls:

8.2.1 Occupational exposure controls:

Work under local exhaust/ventilation

When using gas torches in confined spaces ensure an adequate supply of fresh air to avoid oxygen depletion

8.2.2 Environmental exposure controls: see heading 13

8.3. Personal protection:

8.3.1 Respiratory protection:

Not required for normal conditions of use

Approved respirator or self contained breathing apparatus for installations in confined/unventilated areas

8.3.2 Hand Protection:

Heat resistant gloves if handling hot products after installation

Suitable materials : No data available

Breakthrough time : N.D.

8.3.3 Eye Protection:

Safety glasses with side shield, goggles or face shield depending on application

8.3.4 Skin Protection: Protective clothing

Suitable materials : No data available

9. Physical and chemical properties

9.1. General information:

Appearance (at 20°C) : Plastic tubing and moulded parts

Odour : Almost odourless Colour : Variable in colour

9.2. Important health, safety and environmental information:

pH value : N.D.

Boiling point/boiling range : N.D. °C

Flashpoint : N.D. °C

Explosion limits : N.D. vol% (°C)





Vapour pressure (at 20°C) : N.D. hPa
Vapour pressure (at 50°C) : N.D. hPa
Relative density (at 20°C) : 0.9/2.2
Water solubility : Insoluble
Soluble in : N.D.
Relative vapour density : N.D.
Viscosity : N.D. Pa.s

Partition coëfficient

n-octanol/water : N.D.

Evaporation rate

ratio to butyl acetate : N.D. ratio to ether : N.D.

9.3. Other information:

Melting point/melting range : 70/170°C (Adhesives)

Auto-ignition point : N.D. °C Saturation concentration : N.D. g/m³

10. Stability and reactivity

10.1. Conditions to avoid/reactivity:

Stable under normal conditions

10.2. Materials to avoid:

Keep away from: heat sources

10.3. Hazardous decomposition products:

Thermal decomposition is not significant when products are used in accordance with product installation instructions. At higher temperatures and if materials burn, thermal decomposition products will depend on the base polymer used and may include, but are not limited to: alcohols, aldehydes, carbon monoxide, carbon dioxide, hydrocarbons, hydrogen bromide, hydrogen chloride, silicon dioxide and oxides of nitrogen, phosphorus and sulphur

11. Toxicological information

11.1. Acute toxicity:

LD50 oral rat : N.D. mg/kg
LD50 dermal rat : N.D. mg/kg
LD50 dermal rabbit : N.D. mg/kg
LC50 inhalation rat : N.D. mg/l/4 h
LC50 inhalation rat : N.D. ppm/4 h

11.2. Chronic toxicity:

EC carc. cat. : Not listed EC muta. cat. : Not listed EC repr. cat. : Not listed Carcinogenicity (TLV) : Not listed IARC classification : Not listed





11.3. Routes of exposure:

Inhalation of thermal decomposition products

11.4. Acute effects/symptoms:

AFTER INHALATION

Overheating products during installation may produce vapours/fumes that can cause irritation of the respiratory tract Symptoms may include coughing, headache, dizziness, nausea and in the absence of ventilation, possible asphyxiation

AFTER SKIN CONTACT

Contact with molten material may cause thermal burns

AFTER EYE CONTACT

Overheating products during installation may produce vapours/fumes that can cause irritation and redness of the eye tissue

AFTER INGESTION

Not a normal route of exposure

11.5. Chronic effects:

None known

12. Ecological information

12.1. Ecotoxicity:

No data available

12.2. Mobility:

Volatile organic

compounds (VOC) : N.D.

Insoluble in water

For other physicochemical properties see heading 9

12.3. Persistence and degradability:

Biodegradation BOD₅ : N.D. % ThOD

Water : - Not readily biodegradable in water

test : OECD

Soil : T ½: N.D. days

12.4. Bioaccumulative potential:

 $\begin{array}{ll} \log \mathsf{P}_{\mathsf{OW}} & : \mathsf{N.D.} \\ \mathsf{BCF} & : \mathsf{N.D.} \end{array}$

12.5. Other adverse effects:

WGK : N.D.

Effect on the ozone layer : Not dangerous for the ozone layer (1999/45/EC)

Greenhouse effect : No data available

Effect on waste

water purification : No data available

13. Disposal Considerations

13.1. Provisions relating to waste:

Waste material code (75/442/EEC, Council Decision 2001/118/EC, O.J. L47 of 16/2/2001): 07 02 13 (waste plastic)

13.2. Disposal methods:

Landfill or incinerate at an approved site in accordance with national and local regulations

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk



26/06/18 V1.0



Recycle/reuse

Remove to an authorized dump (Class II)

For incineration use a high temperature incinerator equipped with secondary combustion chamber and acid gas scrubber Do not discharge to wastewater treatment installation

13.3. Packaging/Container:

No available data

14. Transport information

14.1. Classification of the substance in compliance with UN Recommendations

UN number :CLASS ::
SUB RISKS ::
PACKING ::
PROPER SHIPPING NAME ::

14.2. ADR (transport by road)

CLASS : NOT SUBJECT

PACKING or CLASSIFICATION CODE :
DANGER LABEL TANKS :
DANGER LABEL PACKAGES :

14.3. RID (transport by rail)

CLASS : NOT SUBJECT

PACKING or CLASSIFICATION CODE

DANGER LABEL TANKS

DANGER LABEL PACKAGES

14.4. ADNR (transport by inland waterways)

CLASS : NOT SUBJECT

PACKING or CLASSIFICATION CODE :
DANGER LABEL TANKS :
DANGER LABEL PACKAGES :

14.5. IMDG (maritime transport)

CLASS : NOT SUBJECT

SUB RISKS : PACKING : PACKING : MFAG : EMS : MARINE POLLUTANT : SUB RISKS : MARINE POLLUTANT : SUB RISKS : SUB RIS

14.6. ICAO (air transport)

CLASS : NOT SUBJECT

SUB RISKS :
PACKING :
PACKING INSTRUCTIONS PASSENGER AIRCRAFT :
PACKING INSTRUCTIONS CARGO AIRCRAFT :





14.7. Special precautions in connection with transport

Not restricted for any mode of international transport

15. Regulatory information

Classification according to directives 67/548/EEC and 1999/45/EC NOT APPLICABLE

16. Other information

Users are advised that they may have additional disclosure obligations under other national and local laws. Users are advised to ensure that this information is brought to the attention of all employees, agents, and contractors handling this product. Users of the products should make their own evaluation to determine the suitability of each such product for the specific application and to establish safe handling and installation procedures. Distributors of this product are advised to forward this document, or the information contained herein, to every purchaser of this product.

The product makes no warranties as to the accuracy or completeness of this information and disclaims any liability in connection with its use. The obligations shall be only as set forth in standard terms and conditions of sale for this product.

N.A. = NOT APPLICABLE N.D. = NOT DETERMINED

* = INTERNAL CLASSIFICATION

Exposure limits:

TLV: Threshold Limit Value - ACGIH USA

OES : Occupational Exposure Standards - United Kingdom

MEL : Maximum Exposure Limits - United Kingdom
MAK : Maximale Arbeitsplatzkonzentrationen - Germany
TRK : Technische Richtkonzentrationen - Germany

MAC : Maximale aanvaarde concentratie - The Netherlands
VME : Valeurs limites de Moyenne d'Exposition - France
VLE : Valeurs limites d'Exposition à court terme - France
GWBB : Grenswaarde beroepsmatige blootstelling - Belgium
GWK : Grenswaarde kortstondige blootstelling - Belgium

EC : Indicative occupational exposure limit values - directive 2000/39/EC

Part Number
VFFC-1/16-0-STK
VFFC-3/32-0-STK
VFFC-1/8-0STK
VFFC-3/16-0-STK

Part Number
VFFC-1/4-0-STK
VFFC-3/8-0-STK
VFFC-1/2-0-STK
VFFC-3/4-0-STK

	Part Number
V	/FFC-1-0-STK
	VFFC-1/16-0
	VFFC-1/8-0
	VFFC-3/16-0

Part Number
VFFC-1/4-0
VFFC-3/8-0
VFFC-1/2-0
VFFC-3/4-0

Part Number	
VFFC-1-0	
VFFC-3/32-0	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

